



[Click Here to Request a Large Quantity Quote](#)

[RV09AF Series Audio Linear Potentiometers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2272199	Taiwan Alpha	RV09AF-40-20K-B1K	1000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25
2269879	Taiwan Alpha	RV09AF-40-20K-A2K	2000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Audio	9 mm	RV09AF	50 V	\$1.15
2269887	Taiwan Alpha	RV09AF-20-20K-A5K	5000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Audio	9 mm	RV09AF	50 V	\$1.15
2272535	Taiwan Alpha	RV09AF-40-20K-B5K	5000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25
2272247	Taiwan Alpha	RV09AF-20-20K-B5K	5000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25
2269351	Taiwan Alpha	RV09AF-40-20K-A10K	10000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Audio	9 mm	RV09AF	50 V	\$1.15
2269383	Taiwan Alpha	RV09AF-20-20K-A10K	10000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Audio	9 mm	RV09AF	50 V	\$1.15
2272207	Taiwan Alpha	RV09AF-40-20K-B10K	10000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25
2272255	Taiwan Alpha	RV09AF-20-20K-B10K	10000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25
2272215	Taiwan Alpha	RV09AF-40-20K-B50K	50000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25
2272263	Taiwan Alpha	RV09AF-20-20K-B50K	50000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.15
2269359	Taiwan Alpha	RV09AF-40-20K-A100K	100000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Audio	9 mm	RV09AF	50 V	\$1.15
2272223	Taiwan Alpha	RV09AF-40-20K-B100K	100000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25
2272271	Taiwan Alpha	RV09AF-20-20K-B100K	100000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25
2269903	Taiwan Alpha	RV09AF-40-20K-A500K	500000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Audio	9 mm	RV09AF	50 V	\$1.15
2269375	Taiwan Alpha	RV09AF-20-20K-A500K	500000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Audio	9 mm	RV09AF	50 V	\$1.15
2272231	Taiwan Alpha	RV09AF-40-20K-B500K	500000	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2269895	Taiwan Alpha	RV09AF-20-20K-A1M	1 Meg	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Audio	9 mm	RV09AF	50 V	\$1.15
2272239	Taiwan Alpha	RV09AF-40-20K-B1M	1 Meg	0.05 W	20	Knurled	0.787"	PCB, Snap-In	Linear	9 mm	RV09AF	50 V	\$1.25