



[Click Here to Request a Large Quantity Quote](#)

[RV24 Series: Audio Taper Potentiometers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2265703	Taiwan Alpha	RV24AF-10-15F-A1K	1000	0.25 W	20	D	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
2269295	Taiwan Alpha	RV24AF-10-15R1-A1K	1000	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
2181458	Taiwan Alpha	RV24BF-10-15R1-A1K	1000	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24BF	250 V	\$4.29
2236383	Taiwan Alpha	RV24AF-10-15F-A5K	5000	0.25 W	20	D	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
2269303	Taiwan Alpha	RV24AF-10-15R1-A5K	5000	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
2269319	Taiwan Alpha	RV24AF-10-15F-A10K	10000	0.25 W	20	D	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
255426	Taiwan Alpha	RV24AF-10-15R1-A10K	10000	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
2181466	Taiwan Alpha	RV24BF-10-15R1-A10K	10000	0.5 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24BF	250 V	\$4.29
2236341	Taiwan Alpha	RV24AF-10-15F-A50K	50000	0.25 W	20	D	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
255434	Taiwan Alpha	RV24AF-10-15R1-A50K-3	50000	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	500 V	\$1.79
2269327	Taiwan Alpha	RV24AF-10-15F-A100K	100000	0.25 W	20	D	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
255442	Taiwan Alpha	RV24AF-10-15R1-A100K	100000	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	500 V	\$1.79
2181474	Taiwan Alpha	RV24BF-10-15R1-A100K	100000	0.5 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24BF	250 V	\$4.29
2236295	Taiwan Alpha	RV24AF-10-15F-A250K	250000	0.25 W	20	D	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
2269335	Taiwan Alpha	RV24BF-10-15R1-A250K	250000	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24BF	250 V	\$4.29

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2236359	Taiwan Alpha	RV24AF-10-15F-A500K	500000	0.25 W	20	D	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
255451	Taiwan Alpha	RV24AF-10-15R1-A500K	500000	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	500 V	\$1.79
2272495	Taiwan Alpha	RV24BF-10-15R1-A500K	500000	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24BF	250 V	\$4.29
2272359	Taiwan Alpha	RV24AF-10-15F-A1M	1 Meg	0.25 W	20	D	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	250 V	\$1.79
255469	Taiwan Alpha	RV24AF-10-15R1-A1M	1 Meg	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24AF	500 V	\$1.79
2272487	Taiwan Alpha	RV24BF-10-15R1-A1M	1 Meg	0.25 W	20	Round	0.590"	Solder, Panel Mount	Audio	24 mm	RV24BF	250 V	\$4.29