



[Click Here to Request a Large Quantity Quote](#)

[Miscellaneous Potentiometers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2268855	Taiwan Alpha	RV24YN-20S-B501	500	0.4 W	20	Round Slotted	0.787"	Solderable Lug	Linear	24 mm	RV24YN	350 V	\$1.95
2268863	Taiwan Alpha	RD901-20-15R1-B5K	5000	0.05 W	20	Round	0.590"	PCB, Horizontal	Audio	9 mm	RD901	50 V	\$0.99
2276599	Taiwan Alpha	RV16A03F-20-15K-B5K	5000	0.2 W	20	Knurled Slotted	0.787"	PCB, Panel Mount	Linear	16 mm	RV16A	200 V	\$1.55
2276543	BI Technologies	P260T-D2AS5DB5K	5000	0.5 W	20	D	1.020"	PCB Terminal	Linear		P260T	350 V	\$1.95
2276551	BI Technologies	P260T-D2AS6DB5K	5000	0.5 W	20	D	1.330"	PCB Terminal	Linear		P260T	350 V	\$1.95
2172826	Precision Electronics	K1716	5000	2 W	20	Round Slotted	0.984"	Solder, Panel Mount	Linear	28 mm	RV4	500 V	\$6.95
2286391	Clarostat/Honeywell	RV6NAYSD103A	10000	0.5 W	10	Round Slotted	0.510"	Solder, Panel Mount	Linear	13 mm	RV6N	350 V	\$8.95
2276607	Taiwan Alpha	RV16A03F-20-15K-B50K	50000	0.2 W	20	Knurled Slotted	0.787"	PCB, Panel Mount	Linear	16 mm	RV16A	200 V	\$1.55
2269423	Taiwan Alpha	31XT601/RV161S-10-02J-B1M	1 Meg	0.01 W	20	Threaded	0	Solderable Lug	Linear	16 mm	RV16	200 V	\$1.25
2268815	Taiwan Alpha	RV16A03-10-15R1-B1M	1 Meg	0.2 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16A	150 V	\$1.55
2227031	Tocos	RV24YN20SC105	1 Meg	0.25 W	10	Round Slotted	0.787"	Solder, Panel Mount	Audio	24 mm	RV24YN	500 V	\$2.95