



[Click Here to Request a Large Quantity Quote](#)

[Trimmer Potentiometers 3296 Series & Equivalents](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
769266	Bourns	3290W-1-201 (RT24C2W201)	3290	W	200	1 W	5	25	Top Slot	Side	\$19.95
2180560	Spectrol/Vishay Corporation	64P500 (3296P-1-500)	3296	P	50	0.5 W	10	25	Side Slot	Side	\$1.95
2180615	Spectrol/Vishay Corporation	64P201 (3296P-1-201)	3296	P	200	0.5 W	10	25	Side Slot	Side	\$1.95
2180551	Spectrol/Vishay Corporation	64P501/67PR500 (3296P-1-)	3296	P	500	0.5 W	10	25	Side Slot	Side	\$1.95
2037982	BI Technologies	67PR102 (3296P-1-102)	3296	P	1000	0.5 W	10	20	Side Slot	Side	\$1.95
2180607	Spectrol/Vishay Corporation	64P202/3296P-1-202VP	3296	P	2000	0.5 W	10	25	Side Slot	Side	\$1.95
2194363	BI Technologies	3296P-1-202K (RJR24FP202P)	3296	P	2000	0.5 W	10	25	Side Slot	Side	\$1.95
2180623	Spectrol/Vishay Corporation	64P252 (3296P-1-252)	3296	P	2500	0.5 W	10	25	Side Slot	Side	\$1.95
769354	Spectrol/Vishay Corporation	64P502 (3296P-1-502)	3296	P	5000	0.5 W	10	25	Side Slot	Side	\$1.95
853513	Spectrol/Vishay Corporation	64P/67PR103/3296P-1-103	3296	P	10000	0.5 W	10	25	Side Slot	Side	\$1.95
769338	Spectrol/Vishay Corporation	64P203/67PR20K (3296P-1-)	3296	P	20000	0.5 W	10	25	Side Slot	Side	\$1.95
2180586	Spectrol/Vishay Corporation	64P253 (3296P-1-253)	3296	P	25000	0.5 W	10	25	Side Slot	Side	\$1.95
769362	Clarostat/Honeywell	364P503 (3296P-1-503)	3296	P	50000	0.5 W	10	25	Side Slot	Side	\$1.95
2180578	Spectrol/Vishay Corporation	64P254 (3296P-1-254)	3296	P	250000	0.5 W	10	25	Side Slot	Side	\$1.95
2038002	Clarostat/Honeywell	364R504 (3296P-1-504)	3296	P	500000	0.5 W	10	25	Side Slot	Side	\$1.95
769320	Spectrol/Vishay Corporation	64P105 (3296P-1-105)	3296	P	1 Meg	0.5 W	10	25	Side Slot	Side	\$1.95
769371	Clarostat/Honeywell	364W10 (3296W-1-100)	3296	W	10	0.5 W	10	25	Top Slot	Top	\$1.95
1946421	BI Technologies	67WR50R (3296W-1-500)	3296	W	50	0.5 W	20	20	Top Slot	Top	\$1.95

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
853530	Spectrol/Vishay Corporation	64W101/364W101 (3296W-1-	3296	W	100	0.5 W	10	25	Top Slot	Top	\$1.95
1156787	BI Technologies	67WR200 (3296W-1-201)	3296	W	200	0.5 W	10	20	Top Slot	Top	\$1.95
853759	BI Technologies	67WR500 (3296W-1-501)	3296	W	500	0.5 W	10	20	Top Slot	Top	\$1.95
853556	Weston Electronics	850W1K (3296W-1-102)	3296	W	1000	0.5 W	10	25	Top Slot	Top	\$1.75
853652	BI Technologies	67WR2K/3296W-1-202VP	3296	W	2000	0.5 W	10	20	Top Slot	Top	\$1.95
853775	BI Technologies	67WR5K/3296W-1-502VP	3296	W	5000	0.5 W	10	20	Top Slot	Top	\$1.95
853572	Bourns	3296W-1-103LF	3296	W	10000	0.5 W	10	25	Top Slot	Top	\$2.29
241146	Jameco Valuepro	3296W-1-103VP	3296	W	10000	0.5 W	10	25	Top Slot	Top	\$1.95
853679	Spectrol/Vishay Corporation	3296W-1-203 (64W203/67WR20K)	3296	W	20000	0.5 W	10	25	Top Slot	Top	\$1.95
853716	Bourns	3296W-1-253 (67WR25K)	3296	W	25000	0.5 W	10	25	Top Slot	Top	\$1.95
853791	Bourns	3296W-1-503LF(67WR50K)	3296	W	50000	0.5 W	10	25	Top Slot	Top	\$1.95
853599	BI Technologies	67WR100K/64T104/3296W-1	3296	W	100000	0.5 W	10	20	Top Slot	Top	\$1.95
853695	BI Technologies	67WR200K (3296W-1-204)	3296	W	200000	0.5 W	10	20	Top Slot	Top	\$1.95
1967248	Bourns	67WR250K (3296W-1-254)	3296	W	250000	0.5 W	10	25	Top Slot	Top	\$1.95
853610	BI Technologies	67WR1MEG (3296W-1-105)	3296	W	1 Meg	0.5 W	10	20	Top Slot	Top	\$1.95
769514	Spectrol/Vishay Corporation	64X100 (3296X-1-100)	3296	X	10	0.5 W	10	25	Side Slot	Side	\$1.95
2195139	BI Technologies	67XR50 (3296X-1-500)	3296	X	50	0.5 W	20	20	Side Slot	Side	\$1.95
769531	Spectrol/Vishay Corporation	64X201 (3296X-1-201)	3296	X	200	0.5 W	10	25	Side Slot	Side	\$1.95
853960	Spectrol/Vishay Corporation	64X501 (3296X-1-501)	3296	X	500	0.5 W	10	25	Side Slot	Side	\$1.95
1156921	Spectrol/Vishay Corporation	3296X-1-205/64X205	3296	X	500	0.5 W	10	25	Side Slot	Side	\$1.95
853855	BI Technologies	67XR1K/364X1K(3296X-1-102	3296	X	1000	0.5 W	10	20	Side Slot	Side	\$1.95
769549	Spectrol/Vishay Corporation	64X2K (3296X-1-202)	3296	X	2000	0.5 W	10	25	Side Slot	Side	\$1.95
853986	Spectrol/Vishay Corporation	64X502 (3296X-1-502)	3296	X	5000	0.5 W	10	25	Side Slot	Side	\$1.95
853871	BI Technologies	67XR10K/364X10K/3296X-1VP	3296	X	10000	0.5 W	10	20	Side Slot	Side	\$1.95
853951	Spectrol/Vishay Corporation	64X203 (3296X-1-203)	3296	X	20000	0.5 W	10	25	Side Slot	Side	\$1.95

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
1967264	Spectrol/Vishay Corporation	64X253/3296X-1-253VP	3296	X	25000	0.5 W	10	25	Side Slot	Side	\$1.95
854006	Spectrol/Vishay Corporation	64X50K (3296X-1-503)	3296	X	50000	0.5 W	10	25	Side Slot	Side	\$1.95
853898	Spectrol/Vishay Corporation	364/64X100K/3296X-1-104LF	3296	X	100000	0.5 W	10	25	Side Slot	Side	\$1.95
769557	Spectrol/Vishay Corporation	64X200K (3296X-1-204)	3296	X	200000	0.5 W	10	25	Side Slot	Side	\$1.95
769565	Spectrol/Vishay Corporation	64X254 (3296X-1-254)	3296	X	250000	0.5 W	10	25	Side Slot	Side	\$1.95
853919	Spectrol/Vishay Corporation	64X105 (3296X-1-105)	3296	X	1 Meg	0.5 W	10	25	Side Slot	Side	\$1.95
240338	Spectrol/Vishay Corporation	64Y100/3296Y-1-100LF	3296	Y	10	0.5 W	10	25	Top Slot	Top	\$1.95
240725	BI Technologies	67YR100 /64Y100/3296Y-1-1	3296	Y	100	0.5 W	10	25	Top Slot	Top	\$1.95
240733	BI Technologies	67YR200 (3296Y-1-201)	3296	Y	200	0.5 W	10	20	Top Slot	Top	\$1.95
240389	Spectrol/Vishay Corporation	64Y501 (3296Y-1-501)	3296	Y	500	0.5 W	10	25	Top Slot	Top	\$1.95
240398	BI Technologies	67YR1K(3296Y-1-102VP)	3296	Y	1000	0.5 W	10	20	Top Slot	Top	\$1.75
240750	Jameco Valuepro	3296Y-1-102-VP/LF	3296	Y	1000	0.5 W	10	25	Top Slot	Top	\$1.95
240769	Mepco	3296Y-1-202VP(8024E202)	3296	Y	2000	0.5 W	10	25	Top Slot	Top	\$1.95
240777	BI Technologies	3296Y-1-502VP/LF	3296	Y	5000	0.5 W	10	25	Top Slot	Top	\$1.95
240427	BI Technologies	67YR10K/3296Y-1-103VP/LF	3296	Y	10000	0.5 W	10	25	Top Slot	Top	\$1.75
240426	Bourns	3296Y-1-103LF	3296	Y	10000	0.5 W	10	25	Top Slot	Top	\$1.95
240434	BI Technologies	64Y203/67XR20K (3296Y-1-2	3296	Y	20000	0.5 W	10	25	Top Slot	Top	\$1.95
240813	BI Technologies	67YR50K (3296Y-1-503)	3296	Y	50000	0.5 W	10	25	Top Slot	Top	\$1.95
769573	Clarostat/Honeywell	364Y200K (3296Y-1-204)	3296	Y	200000	0.5 W	10	25	Top Slot	Top	\$1.95
240493	Spectrol/Vishay Corporation	64Y1MEG (3296Y-1-105)	3296	Y	1 Meg	0.5 W	10	25	Top Slot	Top	\$1.95
1157026	Spectrol/Vishay Corporation	64Z100 (3296Z-1-100)	3296	Z	10	0.5 W	10	25	Side Slot	Side	\$1.95
769637	Spectrol/Vishay Corporation	64Z500R (3296Z-1-501)	3296	Z	500	0.5 W	10	25	Side Slot	Side	\$1.95
854049	BI Technologies	3296Z-1-102 (67ZR1K)	3296	Z	1000	0.5 W	10	25	Side Slot	Side	\$1.95

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
854081	Spectrol/Vishay Corporation	64Z5K (3296Z-1-502)	3296	Z	5000	0.5 W	10	25	Side Slot	Side	\$1.95
854065	BI Technologies	3296Z-1-103VP(67ZR10K)	3296	Z	10000	0.5 W	10	25	Side Slot	Side	\$1.95
769645	Spectrol/Vishay Corporation	64Z504 (3296Z-1-504)	3296	Z	500000	0.5 W	10	25	Side Slot	Side	\$1.95