



[Click Here to Request a Large Quantity Quote](#)

[Trimmer Potentiometers 3006 Series & Equivalents](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
241234	BI Technologies	89PR10 (3006P-1-100-VP)	3006	P	10	0.75 W	10	20	Side Slot	Side	\$1.09
2287599	BI Technologies	89PR20 (3006P-1-200VP)	3006	P	20	0.75 W	10	20	Side Slot	Side	\$1.09
768811	Spectrol/Vishay Corporation	43P500 (3006P-1-500)	3006	P	50	0.75 W	10	15	Side Slot	Side	\$1.19
695990	BI Technologies	89PR100/43W101 (3006P-1-1	3006	P	100	0.75 W	10	20	Side Slot	Side	\$1.09
2195593	BI Technologies	90PR100 (3006P-1-101)	3006	P	100	0.75 W	10	20	Side Slot	Side	\$1.09
241242	BI Technologies	89PR200/43P201 (3006P-1-2	3006	P	200	0.75 W	10	20	Side Slot	Side	\$1.09
2195614	BI Technologies	90PR250 (3006P-1-251)	3006	P	250	0.75 W	10	20	Side Slot	Side	\$1.09
41937	Jameco Valuepro	3006P-1-501(43P501/8035EK500	3006	P	500	0.75 W	10	15	Side Slot	Side	\$1.49
241269	Murata	2103P1K/3007P/3006P-1-102	3006	P	1000	0.75 W	10	15	Side Slot	Side	\$1.19
2195585	BI Technologies	90PR1K/89PR1K(3006P-1-1K)	3006	P	1000	0.75 W	10	20	Side Slot	Side	\$1.09
41865	Spectrol/Vishay Corporation	43P202 (3006P-1-202)	3006	P	2000	0.75 W	10	15	Side Slot	Side	\$1.19
696052	Bourns	3006P-1-202Z	3006	P	2000	0.75 W	10	15	Side Slot	Side	\$0.99
2198364	Bourns	3006P-1-202VP (79PR2K)	3006	P	2000	0.75 W	10	15	Side Slot	Side	\$1.49
41890	Murata	2103P5K(3006P-1-502LF)	3006	P	5000	0.75 W	10	15	Side Slot	Side	\$1.49
696095	BI Technologies	89PR5K(3006P-1-502LF)	3006	P	5000	0.75 W	10	20	Side Slot	Side	\$1.09
41822	Jameco Valuepro	3006P-1-103VP/LF	3006	P	10000	0.75 W	10	15	Side Slot	Side	\$1.49
41873	Spectrol/Vishay Corporation	3006P-1-203VP (43P203/961-20)	3006	P	20000	0.75 W	10	15	Side Slot	Side	\$1.49
2195606	BI Technologies	90PR20K (3006P-1-203)	3006	P	20000	0.75 W	10	20	Side Slot	Side	\$1.09
2198372	BI Technologies	79PR20K (3006P-1-203)	3006	P	20000	0.75 W	10	20	Side Slot	Side	\$1.49
241314	Spectrol/Vishay Corporation	43P253 (3006P-1-253)	3006	P	25000	0.75 W	10	15	Side Slot	Side	\$1.19
241323	Jameco Valuepro	3006P-1-503VP	3006	P	50000	0.75 W	10	15	Side Slot	Side	\$1.49
41849	Jameco Valuepro	3006P-1-104VP	3006	P	100000	0.75 W	10	15	Side Slot	Side	\$1.49
2198356	BI Technologies	79PR100K (3006P-1-104)	3006	P	100000	0.75 W	10	20	Side Slot	Side	\$1.49

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
63001	Spectrol/Vishay Corporation	43P204/89PR200 (3006P-1-)	3006	P	200000	0.75 W	10	15	Side Slot	Side	\$1.19
41953	BI Technologies	89PR500K (3006P-1-504)	3006	P	500000	0.75 W	10	20	Side Slot	Side	\$1.09
2195631	BI Technologies	90PR500K (3006P-1-504)	3006	P	500000	0.75 W	10	20	Side Slot	Side	\$1.19
241374	Jameco Valuepro	89PR1MEG/3006P-1-105VP	3006	P	1 Meg	0.75 W	10	20	Side Slot	Side	\$1.09
2162901	BI Technologies	89PR2MEG/343P2M (3006P-1)	3006	P	2 Meg	0.75 W	10	20	Side Slot	Side	\$1.09
2291655	Vishay	43W100 (3006W-I-100VP)	3006	W	10	0.75 W	10	15	Side Slot	Side	\$1.49
2178401	Spectrol/Vishay Corporation	43W200 (3006W-1-200)	3006	W	20	0.75 W	10	15	Side Slot	Side	\$1.49
2178380	BI Technologies	89WR100/43W101 (3006W-1-101)	3006	W	100	0.75 W	10	20	Side Slot	Side	\$1.09
2178419	Spectrol/Vishay Corporation	43W201 (3006W-1-201)	3006	W	200	0.75 W	10	15	Side Slot	Side	\$1.49
2178460	Spectrol/Vishay Corporation	43W501 (3006W-1-501)	3006	W	500	0.75 W	10	15	Side Slot	Side	\$1.49
2291647	Jameco Valuepro	3006W-1-102VP/LF	3006	W	1000	0.75 W	10	15	Side Slot	Side	\$1.49
2198399	BI Technologies	77PR2K (3006W-1-202)	3006	W	2000	0.75 W	10	20	Side Slot	Side	\$1.09
1967037	Bourns	3006W-1-103LF	3006	W	10000	0.75 W	10	15	Side Slot	Side	\$1.49
2178443	Spectrol/Vishay Corporation	43W253/3006W-1-253LF	3006	W	25000	0.75 W	10	15	Side Slot	Side	\$1.49
2178427	Spectrol/Vishay Corporation	43W204/89WHR200K (3006W-1)	3006	W	200000	0.75 W	10	15	Side Slot	Side	\$1.49
2198381	BI Technologies	77PR1MEG (3006W-1-105)	3006	W	1 Meg	0.75 W	10	20	Side Slot	Side	\$1.09
2178435	Spectrol/Vishay Corporation	43W205 (3006W-1-205)	3006	W	2 Meg	0.75 W	10	15	Side Slot	Side	\$1.49
2180501	Spectrol/Vishay Corporation	43Y500 (3006Y-1-500)	3006	Y	50	0.75 W	10	15	Side Slot	Side	\$1.49
2180463	Spectrol/Vishay Corporation	43Y101 (3006Y-1-101)	3006	Y	100	0.75 W	10	15	Side Slot	Side	\$1.49
2180480	Spectrol/Vishay Corporation	89XR200/43Y201 (3006Y-1-	3006	Y	200	0.75 W	10	15	Side Slot	Side	\$1.49
768853	Bourns	3006Y-1-102	3006	Y	1000	0.75 W	10	15	Side Slot	Side	\$1.95
2180471	Spectrol/Vishay Corporation	43Y502 (3006Y-1-502)	3006	Y	5000	0.75 W	10	15	Side Slot	Side	\$1.95

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
241293	Spectrol/Vishay Corporation	43Y103 (3006Y-1-103-VP)	3006	Y	10000	0.75 W	10	15	Side Slot	Side	\$1.95
2195551	BI Technologies	89XR50K (3006Y-1-503)	3006	Y	50000	0.75 W	10	20	Side Slot	Side	\$1.49
2180498	Spectrol/Vishay Corporation	43Y204 (3006Y-1-204)	3006	Y	200000	0.75 W	10	15	Side Slot	Side	\$1.49
2180455	Spectrol/Vishay Corporation	43Y254 (3006Y-1-254)	3006	Y	250000	0.75 W	10	15	Side Slot	Side	\$1.49
2180447	Spectrol/Vishay Corporation	43Y205 (3006Y-1-205)	3006	Y	2 Meg	0.75 W	10	15	Side Slot	Side	\$1.49