



[Click Here to Request a Large Quantity Quote](#)

[Trimmer Pots - Vertical & Horizontal, Single Turn](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Resistance (Ohms)	Power Rating	Tolerance (%)	Product Type	Size - mm	Number of Turns	Actuator Type	Termination Style	Price 1
94693	Jameco Valuepro	201XR102B	201	1000	0.25 W	20	Trimmer Vertical	15	1	15mm Knurled Thumbwheel	Pins	\$0.69
35503	Jameco Valuepro	X201R252B	201	2500	0.25 W	20	Trimmer Vertical	15	1	15mm Knurled Thumbwheel	Pins	\$0.69
94706	Jameco Valuepro	201XR502B	201	5000	0.25 W	20	Trimmer Vertical	15	1	15mm Knurled Thumbwheel	Pins	\$0.69
94714	Jameco Valuepro	201XR103B	201	10000	0.25 W	20	Trimmer Vertical	15	1	15mm Knurled Thumbwheel	Pins	\$0.69
94722	Jameco Valuepro	201XR503B	201	50000	0.25 W	20	Trimmer Vertical	15	1	15mm Knurled Thumbwheel	Pins	\$0.69
94731	Jameco Valuepro	201XR104B	201	100000	0.25 W	20	Trimmer Vertical	15	1	Thumbwheel	Pins	\$0.69
2194443	BI Technologies	23CR1K	23	1000	0.25 W	20	Trimmer Horizontal	4	1	Top Slot	Pins	\$0.39
2194540	BI Technologies	23CR100K	23	100000	0.25 W	20	Trimmer Horizontal	4	1	Top Slot	Pins	\$0.59
2276535	Sichuan Qixing Electronics	CE9H2.5-10K	CE9	10000	0.15 W	10	Trimmer Vertical	9.5	1	Side Hex	Pins	\$0.39
2190611	Jameco Valuepro	M8-310-25L-100	M8-310	100	0.5 W	20	Trimmer Horizontal	8	1	6mm Knurl Shaft	Pins	\$0.39
2190629	Jameco Valuepro	M8-310-25L-1K	M8-310	1000	0.5 W	20	Trimmer Horizontal	8	1	6mm Knurl Shaft	Pins	\$0.39
2276591	Piher	PT15B-2K	PT-15	2000	0.25 W	20	Trimmer Vertical	15	1	Side Arrow	Pins	\$0.49
2295791	Amphenol	PT10MH01-501A2020S	PT10	500	0.15 W	20	Trimmer Vertical	10	1	Side Slot	Pins	\$0.45
2295807	Amphenol	PT10MV10-253A2020S	PT10	25000	0.15 W	20	Trimmer Horizontal	10	1	Side Slot	Pins	\$0.59
2295815	Amphenol	PT10MV10-473A2020S	PT10	47000	0.15 W	20	Trimmer Horizontal	10	1	Side Slot	Pins	\$0.45

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Resistance (Ohms)	Power Rating	Tolerance (%)	Product Type	Size - mm	Number of Turns	Actuator Type	Termination Style	Price 1
2295783	Amphenol	PT10MH01-473A2020S	PT10	47000	0.15 W	20	Trimmer Vertical	10	1	Side Slot	Pins	\$0.45
2295759	Amphenol	PT10MH01-104A2020S	PT10	100000	0.15 W	20	Trimmer Vertical	10	1	Side Slot	Pins	\$0.45
2295775	Amphenol	PT10MH01-224A2020S	PT10	220000	0.15 W	20	Trimmer Vertical	10	1	Side Slot	Pins	\$0.59
2295767	Amphenol	PT10MH01-105A2020S	PT10	1 Meg	0.15 W	20	Trimmer Vertical	10	1	Side Slot	Pins	\$0.59
2295799	Amphenol	PT10MH01-505A2020S	PT10	5 Meg	0.15 W	20	Trimmer Vertical	10	1	Side Slot	Pins	\$0.49
2307783	Piher	PT15NB-101	PT15	100	0.25 W	20	Trimmer Horizontal	15	1	Screwdriver Adjustment	Pins 8.8 (2)	\$0.69
2307775	Piher	PT15NB-5K	PT15	5000	0.25 W	20	Trimmer Horizontal	15	1	Screwdriver Adjustment	Pins 4.4 (3)	\$0.69
2312663	Piher	PT15NV02-502A	PT15	5000	0.25 W	20	Trimmer Vertical	15	1	Screwdriver Adjustment	Pins 4.4 (3)	\$0.69
2307815	Piher	PT15NV15-10K	PT15	10000	0.25 W	20	Trimmer Horizontal	15	1	Screwdriver Adjustment	Pins 10 (3)	\$0.69
2307791	Piher	PT15ND-10K	PT15	10000	0.25 W	20	Trimmer Horizontal	15	1	Screwdriver Adjustment	Pins 8.8 (2)	\$0.69
2307839	Piher	PT15YD-25K	PT15	25000	0.25 W	20	Trimmer Horizontal	15	1	Screwdriver Adjustment	Pins 8.8 (2)	\$0.69
2307807	Piher	PT15ND-25K	PT15	25000	0.25 W	20	Trimmer Horizontal	15	1	Screwdriver Adjustment	Pins 8.8 (2)	\$0.69
2307831	Piher	PT15YD-100K	PT15	100000	0.25 W	20	Trimmer Horizontal	15	1	Screwdriver Adjustment	Pins 8.8 (2)	\$0.69
2307823	Piher	PT15NVH5-1MEG	PT15	1 Meg	0.25 W	20	Trimmer Horizontal	15	1	4.8mm Knurled Shaft	Pins 5 (3)	\$0.69
2312175	Piher	PT15YD-2MEG	PT15	2 Meg	0.25 W	30	Trimmer Horizontal	15	1	15mm Thumbwheel	Pins 8.8 (2)	\$0.69
2307799	Piher	PT15ND-2.5MEG	PT15	2.5 Meg	0.25 W	30	Trimmer Horizontal	15	1	Screwdriver Adjustment	Pins 8.8 (2)	\$0.69
2295863	Jameco Valuepro	PTC10LV10-103A2020	PTC10	100000	0.33 W	20	Trimmer Horizontal	10	1	Top Slot	Pins	\$0.89
2280055	Piher	T18AI-2-103B2020	T18	10000	0.25 W	20	Trimmer Horizontal	18	1	18.6mm Thumbwheel Knob with Switch	Pins	\$0.59