



[Click Here to Request a Large Quantity Quote](#)

[Trimmer Potentiometers 3352 Series & Equivalents](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Type	Number of Turns	Actuator Type	Price 1
<a href="#">2195729</a>	BI Technologies	91ER500 (3352E-1-501)	3352	E	500	0.5 W	20	3/8" Round	1	Top Cross	\$0.79
<a href="#">2195681</a>	BI Technologies	91ER2K (3352E-1-202)	3352	E	2000	0.5 W	20	3/8" Round	1	Top Cross	\$0.79
<a href="#">2195702</a>	BI Technologies	91ER25K (3352E-1-253)	3352	E	25000	0.5 W	20	3/8" Round	1	Top Cross	\$0.79
<a href="#">2195711</a>	BI Technologies	91ER250K (3352E-1-254)	3352	E	250000	0.5 W	20	3/8" Round	1	Top Cross	\$0.79
<a href="#">2195673</a>	BI Technologies	91BR50 (3352P-1-500)	3352	P	50	0.5 W	20	3/8" Round	1	Top Cross	\$1.29
<a href="#">770321</a>	Bourns	91BR200 (3352P-1-201)	3352	P	200	0.5 W	20	3/8" Round	1	Thumb/Slot	\$0.79
<a href="#">770339</a>	BI Technologies	91BR500 (3352P-1-501)	3352	P	500	0.5 W	20	3/8" Round	1	Thumb/Slot	\$0.79
<a href="#">2291679</a>	Bourns	3352P-1-102 (91BR1K)	3352	P	1000	0.5 W	20	3/8" Round	1	Top Slot	\$1.59
<a href="#">2200612</a>	BI Technologies	91BR2K (3352P-1-202)	3352	P	2000	0.5 W	20	3/8" Round	1	Top Cross	\$1.59
<a href="#">2281279</a>	Bourns	3352P-1-50LF	3352	P	5000	0.5 W	20	3/8" Round	1	Thumb/Slot	\$1.59
<a href="#">2291687</a>	Bourns	3352P-1-103 (91BR10K)	3352	P	10000	0.5 W	20	3/8" Round	1	Top Slot	\$1.59
<a href="#">2235372</a>	BI Technologies	91BR50K(3352P-1-503)	3352	P	50000	0.5 W	20	3/8" Round	1	Top Cross	\$1.59
<a href="#">2195665</a>	BI Technologies	91AR10 (3352T-1-100)	3352	T	10	0.5 W	20	3/8" Round	1	Top Cross	\$1.09
<a href="#">2200621</a>	BI Technologies	91AR20 (3352T-1-200)	3352	T	20	0.5 W	20	3/8" Round	1	Top Cross	\$1.09
<a href="#">2035805</a>	Bourns	91AR50 (3352T-1-500)	3352	T	50	0.5 W	20	3/8" Round	1	Thumb/Slot	\$1.09
<a href="#">2291695</a>	Bourns	3352T-1-102 (91AR1K)	3352	T	1000	0.5 W	20	3/8" Round	1	Top Slot	\$1.59
<a href="#">2195657</a>	BI Technologies	91AR2.5K (3352T-1-252)	3352	T	2500	0.5 W	20	3/8" Round	1	Top Cross	\$1.59
<a href="#">2291703</a>	Bourns	3352T-1-103 (91AR10K)	3352	T	10000	0.5 W	20	3/8" Round	1	Top Slot	\$1.59
<a href="#">350351</a>	BI Technologies	91AR25K (3352T-1-253)	3352	T	25000	0.5 W	20	3/8" Round	1	Thumb/Slot	\$1.59
<a href="#">2291711</a>	Bourns	3352W-1-102 (91WR1K)	3352	W	1000	0.5 W	20	3/8" Round	1	Side Slot	\$1.59
<a href="#">2195753</a>	BI Technologies	91WR2K (3352W-1-202)	3352	W	2000	0.5 W	20	3/8" Round	1	Side Cross	\$1.09
<a href="#">770347</a>	BI Technologies	91WR10K (3352W-1-103)	3352	W	10000	0.5 W	20	3/8" Round	1	Thumb/Slot	\$1.95
<a href="#">2195761</a>	BI Technologies	91WR20K (3352W-1-203K)	3352	W	20000	0.5 W	20	3/8" Round	1	Side Cross	\$1.59
<a href="#">2195745</a>	BI Technologies	91WR100K (3352W-1-104)	3352	W	100000	0.5 W	20	3/8" Round	1	Side Cross	\$1.59
<a href="#">2195737</a>	BI Technologies	91WR1MEG (3352W-1-105)	3352	W	1 Meg	0.5 W	20	3/8" Round	1	Side Cross	\$1.59