



[Click Here to Request a Large Quantity Quote](#)

[Trimmer Potentiometers 3299 Series & Equivalents](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
1157034	BI Technologies	68PR100 (3299P-1-101)	3299	P	100	0.5 W	10	20	Side Slot	Side	\$2.95
2200794	BI Technologies	68PR200/3299P-1-201LF	3299	P	200	0.5 W	10	20	Side Slot	Side	\$2.95
769670	BI Technologies	68PR500 (3299P-1-501)	3299	P	500	0.5 W	10	20	Side Slot	Side	\$2.95
769653	BI Technologies	68PR1K/3299P-1-102VP	3299	P	1000	0.5 W	10	20	Side Slot	Side	\$2.95
854145	BI Technologies	3299P-I-502(68PR5K/3102P-1-5K)	3299	P	5000	0.5 W	10	20	Side Slot	Side	\$2.95
854102	BI Technologies	3299P-1-103VP (68PR10K)	3299	P	10000	0.5 W	10	20	Side Slot	Side	\$2.95
2285607	Bourns	3299P-1-504LF	3299	P	500000	0.5 W	10	25	Side Slot	Side	\$2.95
241066	BI Technologies	3299W-1-200-VP (68WR20)	3299	W	20	0.5 W	10	20	Top Slot	Top	\$2.95
241074	BI Technologies	68WR50 (3299W-1-500-VP)	3299	W	50	0.5 W	10	20	Top Slot	Top	\$2.95
241082	BI Technologies	3299W-1-101-VP (68WR100)	3299	W	100	0.5 W	10	20	Top Slot	Top	\$2.95
2195219	BI Technologies	68WR200 (3299W-1-201)	3299	W	200	0.5 W	10	20	Top Slot	Top	\$2.95
241103	BI Technologies	68WR500/3299W-1-501LF/VP)	3299	W	500	0.5 W	10	20	Top Slot	Top	\$2.95
241111	Jameco Valuepro	3299W-1-102-VP	3299	W	1000	0.5 W	10	20	Top Slot	Top	\$2.95
183556	BI Technologies	68WR1K (3299W-1-102)	3299	W	1000	0.5 W	10	20	Top Slot	Top	\$2.95
854129	BI Technologies	3299W-1-202VP(68WR2K)	3299	W	2000	0.5 W	10	20	Top Slot	Top	\$2.95
241139	BI Technologies	3299W-1-502-VP(68WR5K)	3299	W	5000	0.5 W	10	20	Top Slot	Top	\$2.95
183564	Jameco Valuepro	3299W-1-103VP	3299	W	10000	0.5 W	10	25	Top Slot	Top	\$2.95
238633	BI Technologies	68WR20K(RNF32) 3299W-1-)	3299	W	20000	0.5 W	10	20	Top Slot	Top	\$2.95
241200	Major Brands	68WR50K/3299W-1-503LP	3299	W	50000	0.5 W	10	20	Top Slot	Top	\$2.95
241189	Jameco Valuepro	3299W-1-104-VP/LF	3299	W	100000	0.5 W	10	25	Top Slot	Top	\$2.95
854161	BI Technologies	68WR200K/3299W-1-204LF	3299	W	200000	0.5 W	10	20	Top Slot	Top	\$2.95
241197	BI Technologies	68WR250K (3299W-1-254-VP)	3299	W	250000	0.5 W	10	20	Top Slot	Top	\$2.95
238676	Bourns	3299W-1-504	3299	W	500000	0.5 W	10	25	Top Slot	Top	\$2.95

Jameco Part #	Manufacturer	Manufacturer Part #	Manufacturer Series	Family	Resistance (Ohms)	Power Rating	Tolerance (%)	Number of Turns	Actuator Type	Actuator Orientation	Price 1
241219	Jameco Valuepro	3299W-1-105VP	3299	W	1 Meg	0.5 W	10	25	Top Slot	Top	\$2.95
769784	BI Technologies	68XR500 (3299X-1-501)	3299	X	500	0.5 W	10	20	Side Slot	Side	\$2.95
854188	BI Technologies	3299X-1-102VP(68XR1K)	3299	X	1000	0.5 W	10	20	Side Slot	Side	\$2.95
854225	BI Technologies	3299X-1-202 (68XR2K)	3299	X	2000	0.5 W	10	20	Side Slot	Side	\$2.95
854268	BI Technologies	68XR5K (3299X-1-502)	3299	X	5000	0.5 W	10	20	Side Slot	Side	\$2.95
854209	BI Technologies	68XR10K/3299X-1-103VP	3299	X	10000	0.5 W	10	20	Side Slot	Side	\$1.69
1157288	Bourns	3299X-1-103LF	3299	X	10000	0.5 W	10	25	Side Slot	Side	\$2.95
1946501	BI Technologies	68XR25K (3299X-1-253-VP)	3299	X	25000	0.5 W	10	20	Side Slot	Side	\$2.95
769792	BI Technologies	68XR50K (3299X-1-503)	3299	X	50000	0.5 W	10	20	Side Slot	Side	\$2.95
769741	BI Technologies	68XR100K (3299X-1-104)	3299	X	100000	0.5 W	10	20	Side Slot	Side	\$2.95
769733	BI Technologies	68XR500K (3299X-1-504)	3299	X	500000	0.5 W	10	20	Side Slot	Side	\$2.95
1946527	BI Technologies	68XR2MEG (3299X-1-205-VP)	3299	X	2 Meg	0.5 W	10	20	Side Slot	Side	\$2.95
240573	Bourns	3299Y-1-102VP	3299	Y	1000	0.5 W	10	25	Top Slot	Top	\$2.95
240581	Bourns	3299Y-1-202LF	3299	Y	2000	0.5 W	10	25	Top Slot	Top	\$2.95
240590	Bourns	3299Y-1-502VP/LF	3299	Y	5000	0.5 W	10	25	Top Slot	Top	\$2.95
240602	Jameco Valuepro	3299Y-1-103VP/LF	3299	Y	10000	0.5 W	10	25	Top Slot	Top	\$2.95
2285647	Bourns	3299Y-1-204	3299	Y	200000	0.5 W	10	25	Top Slot	Top	\$0.99