



[Click Here to Request a Large Quantity Quote](#)

[RV16AF Series Audio Linear Taper Potentiometers](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2265727	Taiwan Alpha	RV16AF-10-15K-A1K	1000	0.06 W	20	Knurled Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268455	Taiwan Alpha	RV16AF-10-15S1-A1K	1000	0.06 W	20	Round	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268687	Taiwan Alpha	RV16AF-10-20R1-A1K	1000	0.06 W	20	Round	0.787"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268407	Taiwan Alpha	RV16AF-20-15K-A1K	1000	0.06 W	5	Knurled Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269943	Taiwan Alpha	RV16AF-20-15S1-A1K	1000	0.06 W	5	Round Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2246750	Taiwan Alpha	RV16AF-20-15R1-B1K	1000	0.125 W	20	Round	0.590"	PCB, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
286249	Taiwan Alpha	RV16AF-10-15R1-B1K	1000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2269143	Taiwan Alpha	RV16AF-10-20R1-B1K	1000	0.125 W	20	Round	0.787"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2268415	Taiwan Alpha	RV16AF-10-15K-A2K	2000	0.06 W	20	Knurled Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269959	Taiwan Alpha	RV16AF-10-15S1-A2K	2000	0.06 W	20	Round	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268703	Taiwan Alpha	RV16AF-10-20R1-A2K	2000	0.06 W	20	Round	0.787"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2236332	Taiwan Alpha	RV16AF-20-15K-A2K	2000	0.06 W	5	Knurled Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268423	Taiwan Alpha	RV16AF-20-15S1-A2K	2000	0.06 W	5	Round Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2272407	Taiwan Alpha	RV16AF-10-15R1-B2K	2000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2269119	Taiwan Alpha	RV16AF-10-15K-A5K	5000	0.06 W	20	Knurled Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2268679	Taiwan Alpha	RV16AF-10-20R1-A5K	5000	0.06 W	20	Round	0.787"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268487	Taiwan Alpha	RV16AF-10-15S1-A5K	5000	0.06 W	20	Round Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268463	Taiwan Alpha	RV16AF-20-15K-A5K	5000	0.06 W	5	Knurled Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268447	Taiwan Alpha	RV16AF-20-15S1-A5K	5000	0.06 W	5	Round Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2246741	Taiwan Alpha	RV16AF-20-15R1-B5K	5000	0.125 W	20	Round	0.590"	PCB, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
286265	Taiwan Alpha	RV16AF-10-15R1-B5K	5000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2269231	Taiwan Alpha	RV16AF-10-20R1-B5K	5000	0.125 W	20	Round	0.787"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2269127	Taiwan Alpha	RV16AF-10-15K-A10K	10000	0.06 W	20	Knurled Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269151	Taiwan Alpha	RV16AF-10-15S1-A10K	10000	0.06 W	20	Round	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
163563	Jameco Valuepro	RV16AF-10-15R1-B10K	10000	0.06 W	20	Round	0.590"	Solderable Lug	Audio	16 mm	RV16AF	500 V	\$1.59
2268479	Taiwan Alpha	RV16AF-10-20R1-A10K-LA	10000	0.06 W	20	Round	1.180"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269199	Taiwan Alpha	RV16AF-20-15K-A10K	10000	0.06 W	5	Knurled Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269223	Taiwan Alpha	RV16AF-20-15S1-A10K	10000	0.06 W	5	Round Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2246320	Taiwan Alpha	RV16AF-20-15K-B10K	10000	0.125 W	20	Knurled Slotted	0.590"	PCB, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2269159	Taiwan Alpha	RV16AF-20-15R1-B10K	10000	0.125 W	20	Round	0.590"	PCB, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
286273	Taiwan Alpha	RV16AF-10-15R1-B10K(D10)	10000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
286206	Taiwan Alpha	RV16AF-10-20R1-B10K	10000	0.125 W	20	Round	0.787"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2272415	Taiwan Alpha	RV16AF10-15R1-B20K	20000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2272447	Taiwan Alpha	RV16AF-10-15K-A25K	25000	0.06 W	20	Knurled Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2227137	Taiwan Alpha	RV16AF-10BL-165R1-A25K	25000	0.06 W	20	Round	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268439	Taiwan Alpha	RV16AF-20-15S1-A25K	25000	0.06 W	5	Round Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
286282	Taiwan Alpha	RV16AF-10-15R1-B25K	25000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2268503	Taiwan Alpha	RV16AF-10-15K-A50K	50000	0.06 W	20	Knurled Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268695	Taiwan Alpha	RV16AF-10-20R1-A50K	50000	0.06 W	20	Round	0.787"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269215	Taiwan Alpha	RV16AF-20-15K-A50K	50000	0.06 W	5	Knurled Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2236308	Taiwan Alpha	RV16AF-20-15S1-A50K	50000	0.06 W	5	Round Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2236375	Taiwan Alpha	RV16AF-10-15R1-B50K	50000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
286214	Taiwan Alpha	RV16AF-10-20R1-B50K	50000	0.125 W	20	Round	0.787"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2227090	Taiwan Alpha	RV16AF-10BL-165R1-A100K-1	100000	0.06 W	20	Round	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269135	Taiwan Alpha	RV16AF-10-15K-A100K	100000	0.06 W	20	Round	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269183	Taiwan Alpha	RV16AF-10-20R1-A100K	100000	0.06 W	20	Round	0.787"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2227014	Taiwan Alpha	RV16AF-10-15S1-A100K	100000	0.06 W	20	Round Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269207	Taiwan Alpha	RV16AF-20-15K-A100K	100000	0.06 W	5	Knurled Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268431	Taiwan Alpha	RV16AF-20-15S1-A100K	100000	0.06 W	5	Round Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2246768	Taiwan Alpha	RV16AF-20-15R1-B100K	100000	0.125 W	20	Round	0.590"	PCB, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
286302	Taiwan Alpha	RV16AF-10-15R1-B100K	100000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
2269239	Taiwan Alpha	RV16AF-10-20R1-B100K	100000	0.125 W	20	Round	0.787"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2268631	Taiwan Alpha	RV16AF-10-15R1-B150K	150000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2272455	Taiwan Alpha	RV16AF-10-15K-A250K	250000	0.06 W	20	Knurled Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2227006	Taiwan Alpha	RV16AF-10-15S1-A250K	250000	0.06 W	20	Round	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2272479	Taiwan Alpha	RV16AF-20-15K-A250K	250000	0.06 W	5	Knurled Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2268871	Taiwan Alpha	RV16AF-42-15R1-A250K	250000	0.06 W	5	Round	0.590"	PCB, Right Angle	Audio	16 mm	RV16AF	150 V	\$1.49
286311	Taiwan Alpha	RV16AF-10-15R1-B250K	250000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2272463	Taiwan Alpha	RV16AF-10-15K-A500K	500000	0.06 W	20	Knurled Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2227102	Taiwan Alpha	RV16AF-10BL-165R1-A500K	500000	0.06 W	20	Round	0.630"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2236324	Taiwan Alpha	RV16AF-20-15K-A500K	500000	0.06 W	5	Knurled Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269967	Taiwan Alpha	RV16AF-20-15S1-A500K	500000	0.06 W	5	Round Slotted	0.590"	PCB, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2272439	Taiwan Alpha	RV16AF-10-15R1-B500K	500000	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2272471	Taiwan Alpha	RV16AF-10-15K-A1M	1 Meg	0.06 W	20	Knurled Slotted	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2227153	Taiwan Alpha	RV16AF-10-15S1-A1MEG	1 Meg	0.06 W	20	Round	0.590"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2227145	Taiwan Alpha	RV16AF-10BL-165R1-A1MEG	1 Meg	0.06 W	20	Round	0.650"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269191	Taiwan Alpha	RV16AF-10-20R1-A1M	1 Meg	0.06 W	20	Round	0.787"	Solder, Panel Mount	Audio	16 mm	RV16AF	150 V	\$1.49
2269167	Taiwan Alpha	RV16AF-20-15R1-B1M	1 Meg	0.125 W	20	Round	0.590"	PCB, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2291735	Taiwan Alpha	RV16AF-10-15R1-B1M	1 Meg	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
286337	Taiwan Alpha	RV16AF-10-15R1-B1M(D11)	1 Meg	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2269951	Taiwan Alpha	RV16AF-10-15R1-B1.2M	1.2 Meg	0.125 W	20	Round	0.590"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59
2269247	Taiwan Alpha	RV16AF-10-20R--B1M	10 Meg	0.125 W	20	Round	0.787"	Solder, Panel Mount	Linear	16 mm	RV16AF	200 V	\$1.59