



[Click Here to Request a Large Quantity Quote](#)

[RV4NAY Series Linear Taper Pots](#)

Jameco Part #	Manufacturer	Manufacturer Part #	Resistance (Ohms)	Power Rating	Tolerance (%)	Shaft Type	Shaft Length	Termination Style	Taper	Body Diameter	Manufacturer Series	Voltage Rating	Price 1
<a href="#">2291247</a>	Clarostat/Honeywell	RV4NAYSD500A	50	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	22 mm	RV4NAY	500 V	\$10.95
<a href="#">241568</a>	Clarostat/PEC	RV4NAYSD101A	100	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	28 mm	RV4NAY	500 V	\$10.95
<a href="#">183610</a>	Clarostat/Honeywell	RV4NAYSD501A	500	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	26 mm	RV4NAY	500 V	\$10.95
<a href="#">13936</a>	Clarostat/Honeywell	RV4NAYSD102A	1000	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	26 mm	RV4NAY	500 V	\$10.95
<a href="#">241613</a>	Clarostat/Honeywell	RV4NAYSD202A	2000	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	26 mm	RV4NAY	500 V	\$10.95
<a href="#">2291263</a>	Clarostat/Honeywell	RV4NAYSD252A	2500	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	22 mm	RV4NAY	500 V	\$10.95
<a href="#">13995</a>	Clarostat/Honeywell	RV4NAYSD502A	5000	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	26 mm	RV4NAY	500 V	\$10.95
<a href="#">2160518</a>	Jameco Valuepro	R24KM-B10K	10000	2 W	10	Round Slotted	0.787"	Solderable Lug	Linear	24 mm	R24	200 V	\$6.95
<a href="#">13952</a>	Clarostat/Honeywell	RV4NAYSD103A	10000	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	26 mm	RV4NAY	500 V	\$10.95
<a href="#">241656</a>	Clarostat/PEC	RV4NAYSD203A	20000	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	28 mm	RV4NAY	500 V	\$10.95
<a href="#">241664</a>	Clarostat/Honeywell	RV4NAYSD253A	25000	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	22 mm	RV4NAY	500 V	\$10.95
<a href="#">13979</a>	Clarostat/PEC	RV4NAYSD104A	100000	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	28 mm	RV4NAY	500 V	\$10.95
<a href="#">2291271</a>	Clarostat/Honeywell	RV4NAYSD504A	500000	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	22 mm	RV4NAY	500 V	\$10.95
<a href="#">2291279</a>	Clarostat/Honeywell	RV4NAYSD105A	1 Meg	2 W	10	Round Slotted	0.866"	Solder, Panel Mount	Linear	22 mm	RV4NAY	500 V	\$10.95