

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.

Jameco Part Number 177949

International IOR Rectifier

1N5817

SCHOTTKY RECTIFIER

1.0 Amp


Major Ratings and Characteristics

Characteristics	1N5817	Units
$I_{F(AV)}$ Rectangular waveform	1.0	A
V_{RRM}	20	V
I_{FSM} @ $t_p = 5 \mu s$ sine	240	A
V_F @ 1 Apk, $T_J = 25^\circ C$	0.45	V
T_J range	-65 to 150	$^\circ C$

Description/Features

The 1N5817 axial leaded Schottky rectifier has been optimized for very low forward voltage drop, with moderate leakage. Typical applications are in switching power supplies, converters, free-wheeling diodes, and reverse battery protection.

- Low profile, axial leaded outline
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- Very low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability



Voltage Ratings

Part number	1N5817
V_R Max. DC Reverse Voltage (V)	20
V_{RWM} Max. Working Peak Reverse Voltage (V)	

Absolute Maximum Ratings

Parameters	1N5817	Units	Conditions
$I_{F(AV)}$ Max. Average Forward Current	1.0	A	50% duty cycle @ $T_L = 138^\circ\text{C}$, rectangular wave form
I_{FSM} Max. Peak One Cycle Non-Repetitive Surge Current, @ $T_J = 25^\circ\text{C}$	240	A	5 μs Sine or 3 μs Rect. pulse
	40		10ms Sine or 6ms Rect. pulse

Following any rated load condition and with rated V_{RWM} applied

Electrical Specifications

Parameters	Typ.	Max.	Units	Conditions
V_{FM} Max. Forward Voltage Drop (1)	0.42	0.45	V	@ 1A
	0.50	0.75	V	@ 3A
I_{RM} Max. Reverse Leakage Current (1)	0.012	1.0	mA	$T_J = 25^\circ\text{C}$
	2.0	10	mA	$T_J = 100^\circ\text{C}$
C_T Typical Junction Capacitance	110	-	pF	$V_R = 5V_{DC}$ (test signal range 100kHz to 1Mhz), @ 25°C
L_S Typical Series Inductance	8.0	-	nH	Measured lead to lead 5mm from package body
dv/dt Max. Voltage Rate of Change	-	10000	V/ μs	(Rated V_R)

(1) Pulse Width < 300 μs , Duty Cycle < 2%

Thermal-Mechanical Specifications

Parameters	1N5817	Units	Conditions
T_J Max. Junction Temperature Range (2)	-65 to 150	$^\circ\text{C}$	
T_{stg} Max. Storage Temperature Range	-65 to 150	$^\circ\text{C}$	
R_{thJL} Max. Thermal Resistance Junction to Lead	32	$^\circ\text{C}/\text{W}$	DC operation, Lead length = 1/8 inch.
R_{thJA} Max. Thermal Resistance Junction to Ambient	100	$^\circ\text{C}/\text{W}$	DC operation, without cooling fin
Wt Approximate Weight	0.33(0.012)	gr (oz)	
Case Style	DO-204AL (DO-41)		

(2) $\frac{dP_{tot}}{dT_J} < \frac{1}{R_{th(j-a)}}$ thermal runaway condition for a diode on its own heatsink




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Peak Reverse Current Vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage




Fig. 4 - Maximum Average Forward Current Vs. Allowable Lead Temperature




Fig. 5 - Maximum Average Forward Dissipation Vs. Average Forward Current




Fig. 6 - Maximum Peak Surge Forward Current Vs. Pulse Duration

- (2) Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$;
 $Pd = \text{Forward Power Loss} = I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$ (see Fig. 6);
 $Pd_{REV} = \text{Inverse Power Loss} = V_{R1} \times I_R (1 - D)$

Ordering Information Table

Device Code	1N5817	TR
	①	②
1	-	Part Number:1A, 20V
2	-	TR= Tape & Reel package (5000 pcs)
	-	= Box package (1000 pcs)

Data and specifications subject to change without notice.
This product has been designed for Industrial Level.
Qualification Standards can be found on IR's Web site.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309
Visit us at www.irf.com for sales contact information. 05/02

This datasheet has been download from:

www.datasheetcatalog.com

Datasheets for electronics components.