

勝特力材料 886-3-5753170 胜特力电子(上海) 86-21-54151736 胜特力电子(深圳) 86-755-83298787 Http://www. 100y. com. tw

W.100Y.COM.TW **Quadruple 2-Input Positive NOR Gates**


REJ03D0389-0200 Rev.2.00 Feb.18.2005

COM.TW

100X.COM.

| Part Name | Package Type | Package Code (Previous Code) | Package Abbreviation | Taping Abbreviation (Quantity) |
|--------------|--------------------|---------------------------------|-------------------------|-----------------------------------|
| HD74LS02P | DILP-14 pin | PRDP0014AB-B (DP-14AV) | RWW.100 | COM.TW |
| HD74LS02FPEL | SOP-14 pin (JEITA) | PRSP0014DF-B (FP-14DAV) | FP 10 | EL (2,000 pcs/reel) |
| HD74LS02RPEL | SOP-14 pin (JEDEC) | PRSP0014DE-A (FP-14DNV) | RP | EL (2,500 pcs/reel) |

Pin Arrangement





ODY.COM.TW


.100X.CO

V.100Y.C9

NWW.10

WWW.I

Circuit Schematic (1/4)



DOX.COM

| Item | Symbol | Ratings | Unit |
|---------------------|----------------------|-------------|-------|
| Supply voltage | V _{CC} Note | 7 | CON V |
| Input voltage | VIN | 7 | V-VO |
| Power dissipation | Pr Pr | 400 | mW |
| Storage temperature | Tstg | -65 to +150 | °C |

Recommended Operating Conditions

WWW.100Y.COM

WWW.100Y.COM.TW

| Item | Symbol | Min | Тур | Max | Unit |
|-----------------------|-----------------|----------|-------|------|------|
| Supply voltage | V _{cc} | 4.75 | 5.00 | 5.25 | V |
| Output ourrant | I _{OH} | V. TOY.C | TT I | -400 | μA |
| Output current | I _{OL} | WW.F | NT-TO | 8 | mA |
| Operating temperature | Topr | -20 | 25 | 75 | °C |

| 勝特力林 | 材料 886-3-5753170 |
|---------|----------------------|
| 胜特力电子 | (上海) 86-21-54151736 |
| 胜特力电子 | (深圳) 86-755-83298787 |
| Http:// | www. 100y. com. tw |
| | WWW.100 CON |
| | |
| | |

WWW.100Y.COM.TW



ODY.COM.TW

Electrical Characteristics

| ltem | Symbol | min. | £1 cm * | max | Unit | $(Ta = -20 \text{ to } +75 \circ 0)$ Condition |
|---------------------------------|-----------------|-------|---------------|------|------|---|
| item | | | typ.* | max. | V | Condition |
| Input voltage | VIH | 2.0 | _ | | | CONTRACTOR |
| NN NN | VIL | TT | _ | 0.8 | V | L.M.L |
| | Vон | 2.7 | - W | | V | V_{CC} = 4.75 V, V_{IL} = 0.8 V, I_{OH} = –400 μ Å |
| Output voltage | | COM. | T | 0.5 | V | $I_{OL} = 8 \text{ mA}$ $V_{CC} = 4.75 \text{ V}, \text{ V}_{IH} = 2 \text{ V}$ |
| | V _{OL} | Mo | <u> </u> | 0.4 | ¥10 | $I_{OL} = 4 \text{ mA}$ $V_{CC} = 4.75 \text{ V}, \text{ V}_{IH} = 2 \text{ V}$ |
| NTN NT | IH 100 | 1.00 | CT S | 20 | μA | $V_{CC} = 5.25 \text{ V}, \text{ V}_{I} = 2.7 \text{ V}$ |
| Input current | | N.COr | NT. | -0.4 | mA | $V_{CC} = 5.25 \text{ V}, \text{ V}_{I} = 0.4 \text{ V}$ |
| | .W.10 | 077 | N1- <u>-</u> | 0.1 | mA | $V_{CC} = 5.25 \text{ V}, \text{ V}_{I} = 7 \text{ V}$ |
| Short-circuit output current | los | -20 | DM <u>L'I</u> | -100 | mA | V _{CC} = 5.25 V |
| Quanty ourrent | Іссн | . V. | 1.6 | 3.2 | mA | V _{CC} = 5.25 V |
| Supply current | ICCL | 1.100 | 2.8 | 5.4 | mA | V _{CC} = 5.25 V |
| Input clamp voltage | Vik | a ton | Mr. | -1.5 | V | $V_{CC} = 4.75 \text{ V}, I_{IN} = -18 \text{ mA}$ |

100Y.COM.TW

Switching Characteristics

| Switching Charact | teristics | | | | | |
|--------------------------------|----------------------------|------|-------------------|-------------------|------------|-----------------------|
| W.1001. COMPL | | | | | | $(V_{CC} = 5 V, Ta =$ |
| | | | | | | |
| Item | Symbol | min. | typ. | max. | Unit | Condition |
| Item Propagation delay time | Symbol t _{PLH} | min. | typ. 10 | max. 15 | Unit ns | |

Note: Refer to Test Circuit and Waveform of the Common Item "TTL Common Matter (Document No.: REJ27D0005-, v. COM-0100)". WWW.100Y.CC WWW.100Y.COM.TW


勝特力材料 886-3-5753170 胜特力电子(上海) 86-21-54151736 胜特力电子(深圳) 86-755-83298787 Http://www.100y.com.tw WWW.100Y.COA

WWW.100Y.COM.TW



100Y.COM.TW

Package Dimensions




10Y.COM.TW

RENESAS

100Y.COM.TW

 $\overline{W}W$



勝特力材料 886-3-5753170 胜特力电子(上海) 86-21-54151736 胜特力电子(深圳) 86-755-83298787 Http://www. 100y. com. tw

WWW.100Y.CON

WWW.10

WWW.100Y.COM.TW Rev.2.00, Feb.18.2005, page 5 of 5 WWW.100



00Y.COM.TW

WWW.100Y.COM.TW 特力材料 886-3-5753170 勝 胜特力电子(上海) 86-21-54151736 胜特力电子(深圳) 86-755-83298787 Http://www.100y.com.tw

WWW.100Y.COM.TW WWW.100Y.COM.TW Renesas Technology Corp. sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

Keep safety first in your circuit designs! 1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

W.100Y.COM.TW

Notes regarding these materials

- Notes regarding these materials
 1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. are a third party.
 2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
 3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
 The information described here may contain technical inaccuracies or typographical errors.
 Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
 Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (http://www.renesas.com).
 When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage or manufactured for use or system that is used under circumstances in whic

- use. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination. Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- 8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.



COM.TW

RENESAS SALES OFFICES

Refer to "http://www.renesas.com/en/network" for the latest and detailed information.

Renesas Technology America, Inc. 450 Holger Way, San Jose, CA 95134-1368, U.S.A Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

Renesas Technology Europe Limited Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K. Tel: <44> (1628) 585-100, Fax: <44> (1628) 585-900

Renesas Technology Hong Kong Ltd. 7th Floor, North Tower, World Finance Centre, Harbour City, 1 Canton Road, Tsimshatsui, Kowloon, Hong Kong Tel: <852> 2265-6688, Fax: <852> 2730-6071 WW.100Y.COM.TW

Renesas Technology Taiwan Co., Ltd. 10th Floor, No.99, Fushing North Road, Taipei, Taiwan Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology (Shanghai) Co., Ltd. Unit2607 Ruijing Building, No.205 Maoming Road (S), Shanghai 200020, China Tel: <86> (21) 6472-1001, Fax: <86> (21) 6415-2952

WWW.10

Renesas Technology Singapore Pte. Ltd. 1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632 Tel: <65> 6213-0200, Fax: <65> 6278-8001 WWW.100Y.COM.7

W.100Y.COM.TW

WWW.100Y.COM.

MMM.100

http://www.renesas.com WW.100Y.COM.TW

WW.100Y.CO