


Mounting Brackets & Accessories for Mean Well Enclosed Switching AC-to-DC Power Supplies

All brackets use metric screws: 2-F3 x 6, 2-F4 x 6, 2-T3 x 6, 2-T4 x 6 and 8-T4 x 6 (not included)

| Part No. | Mfr. No. | For Models | 1 | 10 |
|----------|----------|--|--------|--------|
| 222122 | DRL-01 | S-25/40, RS-25/35 | \$1.25 | \$1.09 |
| 222131 | DRL-02 | S-60/100F/150, D-60/120, SD-100/150, SP-75/100/150/200 | 1.75 | 1.49 |
| 222148 | DRL-03 | S-240/320, SP-320 | 2.25 | 1.95 |
| 222157 | DRP-01 | All Models | 2.49 | 2.25 |
| 222165 | DRP-02 | S-25, SP-75/100/150/200 | 1.95 | 1.75 |
| 222173 | DRP-03 | All Models | 1.95 | 1.75 |
| 222182 | MHS012 | S-320/350, SP-100/150/200/320 | .75 | .65 |
| 1952636 | MHS013 | PSP-500, SP-750, SE-600 | .85 | .75 |
| 222199 | MHS025 | SP-500, PSP-600 | .95 | .85 |
| 248736 | 2094.0 | DR, DRH, DRP, DRT, MDR | 6.95 | 6.29 |



Mating Connector
103588 \$1.20/10
Spade Solderless Terminal

Crimp Tool
72996 \$22.49
Solderless Terminal Crimp Tool

Pricing & specs on page 89

LED Enclosed Power Supplies with Power Factor Correction

For Indoor and Outdoor Applications

- Suitable for LED lighting & moving sign application
- Short-circuit/overload/overvoltage/overtemperature protection
- UL1310 class 2 power unit
- 100% full-load burn-in test
- Universal AC input/full range
- Inrush current: 40A/230VAC
- Cooling by free air convection

- PLN Series** • Plastic case • Constant voltage and current • Working temperature: -30°C to 50°C • Two-year warranty
- CLG Series** • Metal case • Adjustable voltage and current • Working temperature: -30°C to 70°C • Three-year warranty

MW
MEAN WELL

PLN Series

* Web Code: LPP

CE, RoHS, UL, P, C, US, A, CE

| Jameco Part No. | Manufacturer | Mfr. Part No. | Output | | Size (L" x W" x H") | Ripple & Noise (mV p-p)* | Load Reg. (±%)* | Line Reg. (±%)* | Certification | Pricing | | |
|-----------------|--------------|---------------|-----------------------------|--------|---------------------|--------------------------|-----------------|-----------------|-------------------|---------|---------|---------|
| | | | Voltage @ Current (min-max) | Power | | | | | | 1 | 10 | 25 |
| 1954404 | Mean Well | PLN-30-12 | +12V @ 0-2.5A | 30.0W | 5.7 x 1.9 x 1.2 | 2000 | 10.0 | 3.0 | UL/CUL/TUV/CE | \$33.95 | \$31.95 | \$29.95 |
| 1918833 | Mean Well | PLN-100-12 | +12V @ 0-5A | 60.0W | 7.9 x 2.8 x 1.4 | 150 | 2.0 | 1.0 | UL/CUL/TUV/CE/PFC | 59.95 | 56.95 | 54.95 |
| 1954877 | Mean Well | CLG-150-12A | +12V @ 0-11A | 132.0W | 8.7 x 2.7 x 1.5 | 150 | 1.0 | 0.5 | UL/TUV/CE | 84.95 | 79.95 | 74.95 |
| 1918964 | Mean Well | PLN-60-15 | +15V @ 0-4A | 60.0W | 7.1 x 2.4 x 1.4 | 2400 | 10.0 | 4.0 | UL/CUL/TUV/CE | 49.95 | 46.95 | 44.95 |
| 1919001 | Mean Well | CLG-60-15 | +15V @ 0-4A | 60.0W | 6.8 x 2.4 x 1.5 | 2400 | 10.0 | 4.0 | UL/CUL/TUV/CE | 59.95 | 56.95 | 54.95 |
| 1918841 | Mean Well | PLN-100-15 | +15V @ 0-5A | 75.0W | 7.9 x 2.8 x 1.4 | 150 | 2.0 | 1.0 | UL/CUL/TUV/CE/PFC | 59.95 | 56.95 | 54.94 |
| 1585856 | Mean Well | CLG-100-15 | +15V @ 0-5A | 75.0W | 8.7 x 2.7 x 1.5 | 150 | 2.0 | 1.0 | UL/CUL/TUV/CE/PFC | 77.95 | 72.95 | 67.95 |
| 1585864 | Mean Well | CLG-100-20 | +20V @ 0-4.8A | 96.0W | 8.7 x 2.7 x 1.5 | 150 | 2.0 | 1.0 | UL/CUL/TUV/CE/PFC | 77.95 | 72.95 | 67.95 |
| 1954412 | Mean Well | PLN-30-24 | +24V @ 0-1.25A | 30.0W | 5.7 x 1.9 x 1.2 | 2600 | 10.0 | 3.0 | UL/CUL/TUV/CE | 33.95 | 31.95 | 29.95 |
| 1918868 | Mean Well | PLN-100-24 | +24V @ 0-4A | 96.0W | 7.9 x 2.8 x 1.4 | 150 | 2.0 | 1.0 | UL/CUL/TUV/CE/PFC | 59.95 | 56.95 | 54.95 |
| 1585872 | Mean Well | CLG-100-24 | +24V @ 0-4A | 96.0W | 8.7 x 2.7 x 1.5 | 150 | 2.0 | 1.0 | UL/CUL/TUV/CE/PFC | 77.95 | 72.95 | 67.95 |
| 1954885 | Mean Well | CLG-150-24A | +24V @ 0-6.3A | 150.0W | 8.7 x 2.7 x 1.5 | 150 | 1.0 | 0.5 | UL/TUV/CE | 84.95 | 79.95 | 74.95 |
| 1585733 | Mean Well | CLG-100-27 | +27V @ 0-3.55A | 96.0W | 8.7 x 2.7 x 1.5 | 150 | 2.0 | 1.0 | UL/CUL/TUV/CE/PFC | 77.95 | 72.95 | 67.95 |
| 1585768 | Mean Well | CLG-100-48 | +48V @ 0-2A | 96.0W | 8.7 x 2.7 x 1.5 | 150 | 2.0 | 1.0 | UL/CUL/TUV/CE/PFC | 77.95 | 72.95 | 67.95 |

* Primary Output

Encapsulated Switching Power Supplies

* Web Code: ESP

PM-05/PM-10/PM-15/PM-20 Series:

- Universal AC input (85-264VAC @ 47Hz)
- Short-circuit, overload, overvoltage protection
- Ultra-miniature size
- UL/CUL/TUV/CE/CB
- Cooling by free air convection
- 100% full-load burn-in test
- Three-year warranty



| Part No. | Manufacturer | Mfr. P/N | Output | | Pins | Ripple & Noise (mVp-p) | Load Reg (±%) | Line Reg (±%) | Size (L" x W" x H") | Pricing | | |
|----------|--------------|----------|-------------------------|--------|------|------------------------|---------------|---------------|---------------------|---------|---------|---------|
| | | | Volt. @ Curr. (min-max) | Power | | | | | | 1 | 10 | 25 |
| 1954527 | Mean Well | PM-05-12 | +12V @ 0-0.42A | 5.04W | 4 | 150 | 1.0 | 0.5 | 2.5 x 2.0 x 0.8 | \$19.95 | \$17.95 | \$15.95 |
| 1954551 | Mean Well | PM-10-12 | +12V @ 0-0.85A | 10.20W | 4 | 150 | 1.0 | 0.5 | 2.8 x 2.0 x 0.9 | 21.95 | 19.95 | 17.95 |
| 1954586 | Mean Well | PM-15-12 | +12V @ 0-1.25A | 15.00W | 4 | 150 | 1.0 | 0.5 | 3.0 x 2.1 x 0.9 | 24.95 | 22.49 | 19.95 |
| 1954367 | Mean Well | PM-20-12 | +12V @ 0-1.80A | 21.60W | 6 | 150 | 1.0 | 0.5 | 3.7 x 2.2 x 0.9 | 27.95 | 25.95 | 23.95 |
| 1954535 | Mean Well | PM-05-24 | +24V @ 0-0.23A | 5.52W | 4 | 240 | 0.5 | 0.5 | 2.5 x 2.0 x 0.8 | 19.95 | 17.95 | 15.95 |
| 1954560 | Mean Well | PM-10-24 | +24V @ 0-0.42A | 10.10W | 4 | 240 | 0.5 | 0.5 | 2.8 x 2.0 x 0.9 | 21.95 | 19.95 | 17.95 |
| 1954594 | Mean Well | PM-15-24 | +24V @ 0-0.63A | 15.10W | 4 | 240 | 0.5 | 0.5 | 3.0 x 2.1 x 0.9 | 24.95 | 22.49 | 19.95 |
| 1954383 | Mean Well | PM-20-24 | +24V @ 0-0.92A | 22.10W | 6 | 240 | 0.5 | 0.5 | 3.7 x 2.2 x 0.9 | 27.95 | 25.95 | 23.95 |

Rackmount Power Supply

* Web Code: MCJ

- AC Input active surge current limiting
- Forced air cooling by built-in DC fan
- Built-in remote sense function
- Short-circuit, overload, overvoltage, overtemperature protection
- Input voltage: 90-132VAC/180-264VAC switch selectable

| Part No. | Mfr. Part No. | Power | Output (VDC @ A) | Ripple & Noise | Size(W x D x H) | 1 | 10 | 25 |
|----------|---------------|-------|------------------|----------------|---------------------|----------|----------|----------|
| 673408 | SE-600-48RM | 600W | 48 @ 12.5 | 150mVp-p max. | 19.5" x 5.0" x 3.5" | \$249.95 | \$229.95 | \$214.95 |

Dual Adj. Regulated Power Supply Kit

- Adjustable positive/negative supplies ±5 to ±15VDC, 175mA-750mA per supply
- LED on indicator
- 120VAC input
- 48-piece kit
- PC board construction
- Difficulty level: intermediate

| Part No. | Cross Ref. No. | Dimensions | Wt. (lbs.) | 1 | 10 |
|----------|----------------|-----------------------|------------|---------|---------|
| 20626 | JE215 | 5.1"L x 3.5"W x 2.0"H | 2.1 | \$24.95 | \$22.49 |

We also carry
AT & ATX Computer
Power Supplies
See page 175



* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above