



Stepper Motor Drivers/Controllers * Web Code: GDP

Part No.	Mfr. Part No.	Pkg.	Description	1	10	100
924545	L293DD	SOIC-20	Push pull 4-ch driver w/ diodes	\$4.49	\$3.75	\$3.25
288067	L2971	DIP-20	Stepper motor controller, 5V	8.95	7.95	6.95
245403	L298N	MW-15	Dual full-bridge driver, 46V	2.59	2.45	2.25
288091	L6202	DIP-18	DMOS full-bridge driver, 48V	5.95	5.49	4.95
288104	L6203	MW-11	DMOS full-bridge driver, 48V	6.95	6.25	5.49

* Motion Control Available Online — Enter Web Code DEU

Encoders/Decoders * Web Code: VAR

Part No.	Mfr. Product No.	Pkg.	Description	1	10	100
243408	TP3054N	DIP-16	U-law PCM CODEC & filter, 5V	\$2.45	\$1.75	\$1.45
296702	MOT MC145026P	DIP-16	Encoder, 4.5-18V	2.49	2.25	2.05
296711	MOT MC145027P	DIP-16	Decoder, 4.5-18V	2.95	2.75	2.49
123730	HOL HT12E	DIP-18	Encoder, 2.4-12V	1.75	1.55	1.35
123748	HOL HT12D	DIP-18	Decoder, 2.4-12V	1.65	1.45	1.25
243483	MCH HCS512-I/P	DIP-18	Code hopping decoder, 4-6V	4.95	4.25	3.95
287945	MCH MCP2140-I/P	DIP-18	Standard protocol stack controller, 3-5V	2.95	2.75	1.49
287970	MCH MCP2150-I/SO	SOIC-18	Standard protocol stack controller, 3-5V	3.95	2.95	2.75
243459	MCH MCP2150-I/P	DIP-18	Standard protocol stack controller, 3-5V	2.95	2.75	2.49

Buffer * Web Code: WBR

Part No.	Product No.	Pkg.	Description	1	10	100
23051	LH0002CN	DIP-10	General purpose buffer	\$12.95	\$11.95	\$10.95

Power Management * Web Code: PMT

Part No.	Mfr. Product No.	Pkg.	Description	1	10
312848	TI BQ2004PN	DIP-16	NiMH/NiCd switchmode chrg mgmt w/ neg dV	\$2.95	\$2.49
312928	TI BQ2018TS-E	TSSOP-8	Rechargeable battery power monitor	3.95	3.49
312936	TI BQ2019PW	TSSOP-8	Rechargeable battery power monitor	3.49	3.25
312881	TI BQ2040SN-D111	SOIC-16	Li-Ion/NiMH/NiCd gas gauge w/ smbus	5.95	4.95

RS-422/423/485 Drivers/Receivers * Web Code: NBT

Part No.	Mfr. Product No.	Pkg.	Description	* Order in multiples of 10		
				1	10	100
299807	LTC485CN8	DIP-8	RS-485 LP xcvr, 5V	\$1.75	\$1.49	\$1.25
244195	MAX1487CPA	DIP-8	RS-485/422 LP xcvr, 12V	2.25	1.75	1.55
39571	26LS30	DIP-16	RS-422/423 line driver, 5V	2.49	2.25	1.95
39600	26LS32	DIP-16	RS-422/423 quad diff. line rcvr, 5V	.59	.49	.45
25232	MC3486P	DIP-16	RS-422/423 quad diff. line rcvr, 5V	*.15	.12	.12
25259	MC3487P	DIP-16	RS-422/423 quad line driver, 5V	.29	.25	.22
50948	SN75174N	DIP-16	RS-422 quad diff. line driver w/ 3 st.	.89	.79	.69
50956	SN75175N	DIP-16	RS-422/423 quad diff. line rcvr, 5V	.89	.79	.69
758364	TI SN75176AP	DIP-8	RS-422 differential bus xcvr	.65	.55	.45
50964	SN75176BN	DIP-8	RS-422 diff. line bus xcvr, 5V	.59	.49	.45

Blue Part No. = Limited Quantity Available

* 65LVDS Series Available Online — Enter Web Code UEU

RS-232 Drivers/Receivers * Web Code: EAV

Part No.	Mfr. Product No.	Pkg.	Description	1	10	100
142535	MAX202CPE	DIP-16	5V, 120kbps, w/ 0.1µF ext. caps	\$2.49	\$2.05	\$1.95
244232	MAX202CSE	SOIC-16	5V, 120kbps, w/ 0.1µF ext. caps	2.25	1.95	1.75
244241	MAX202EPE	DIP-16	5V, 120kbps, w/ 0.1µF ext. caps	2.95	2.49	2.25
282790	MAX MAX211CAI	SSOP-28	5V, w/ 0.1µF ext. caps	2.95	2.75	2.49
875448	INS HIN232CP	DIP-16	5V hi spd RS-232 transmitter/rcvr	1.09	.99	.89
24811	MAX232CPE*	DIP-16	5V, 200kbps, multichannel	1.85	1.65	1.25
24812	MAX232CPE	DIP-16	5V, 200kbps, multichannel	1.95	1.75	1.35
318959	MAX MAX232CPE	DIP-16	5V, 200kbps, multichannel	2.25	1.95	1.75
318960	MAX MAX232CPE	DIP-16	5V, 200kbps, multichannel	2.49	2.15	1.95
106147	MAX232CWE	SOIC-16	5V, 120kbps, multichannel	2.49	2.15	1.95
256401	MAX232DR	SOIC-16	5V, 120kbps, dual driver/rcvr	.69	.59	.49
882293	MAX MAX232ECE	DIP-16	5V, RS-232 xcvr, ±15kV ESD	3.75	3.09	2.95
106155	MAX232EPE	DIP-16	5V, 120kbps, multichannel	3.95	3.15	2.79
698576	TI MAX232N	DIP-16	Dual EIA-232 driver/receiver, C-temp	.75	.65	.55
903277	TI MAX232IN	DIP-16	Dual EIA-232 driver/receiver, I-temp	.75	.65	.55
106163	MAX233CPP	DIP-20	5V, 120kbps, multichannel	5.75	4.75	4.25
106171	MAX235CPG	DIP-24	5V, 120kbps, multichannel	10.95	9.95	7.95
106180	MAX238CNG	DIP-24	5V, 120kbps, multichannel	5.49	4.95	4.25
23157	DS1488N*	DIP-14	15V, quad line driver	.35	.29	.25
16379	DS14C89N	DIP-14	5V, quad line receiver	1.19	1.09	.95
235301	DS14C232CN	DIP-16	5V, LP, TIA/EIA dual driver/rcvr	2.49	2.25	1.95
23181	SN75189N*	DIP-14	5V, quad line receiver	.35	.29	.25
25099	MC145406P	DIP-16	5-12V, EIA-232-DV.28 driver/rcvr	2.25	1.95	1.75
929207	ON MC100EP17DWG	SOIC-20	Quad differential driver/receiver	15.95	13.95	11.95

* 10 pcs. in Linear series IC cabinet kit, pg 16

Comparators * Web Code: EBS

Part No.	Mfr. Product No.	Pkg.	Description	* Order in multiples of 10		
				1	10	100
311044	NSC LM111J-8	DIP-8	Voltage comparator	\$7.95	\$6.95	\$6.25
282087	LM139J	CDIP-14	Low power, low offset volt quad	1.75	1.55	1.35
23528	LM311N*	DIP-8	Voltage comparator	.25	.22	.19
902522	TI LM311DR	SOIC-8	Differential comparator w/ strobes	*.09	.12	.09
837812	NSC LM311N/NOPB	DIP-8	Voltage comparator	.89	.69	.49
143888	LM339AN	DIP-14	Low power quad comparator	.25	.22	.15
826742	TI LM339N	DIP-14	Quad differential comparator	.35	.29	.25
23851	LM339N**	DIP-14	Quad comparator	.25	.22	.17
193594	LM339M	SOIC-14	Low power low offset volt quad	.25	.22	.15
120900	LM392N	DIP-8	Low power op amp/volt comp.	1.09	.99	.89
24281	LM393N*	DIP-8	Dual comparator	.25	.22	.17
212177	LM393AN	DIP-8	Low power low offset volt quad comp.	*.19	.15	.15
297844	MAX MAX902CSD	SOIC-14	Hi-speed low power precision volt comp.	7.95	5.95	4.95
312266	LTC LT1016CS8	SOIC-8	Ultra-fast precision 10ns comparator	2.95	1.95	1.75
107238	LM3302N	DIP-14	Low power low offset volt quad	.59	.49	.45
1944741	ST TS3721IN	DIP-8	LP dual CMOS volt (I-temp)	.39	.35	.25
277173	NSC LMC7211AIM	SOIC-8	Comp w/ rail-to-rail input, push pull output	.99	.79	.69
277190	NSC LMC7211BIM	SOIC-8	Comp w/ rail-to-rail input, push pull output	.99	.79	.69

* 10 pcs./** 20 pcs. included in Linear kit, pg 16

* IEEE-1394 Available Online — Enter Web Code KEN



More Information Online
 Compare products online to quickly find the products you want with the specifications and real time product availability. Purchasing products has never been easier.
www.Jameco.com

* HOL = Holtek | INS = Intersil | LTC = Linear Technology | MAX = Maxim Semi | MCH = Microchip | MOT = Motorola | NSC = National Semi | ON = ON Semi | ST = ST Micro | TI = Texas Instruments | ♦ = Varies

* For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above



Order by Phone 24/7 at 1-800-831-4242 or Online at www.Jameco.com