



7400 Series

*Web Code: XAG

Part No.	*Mfr.	Product No.	Pkg.	Description	1	10	100
48979	♦	7400N**	DIP-14	Quad 2-input pos. NAND gate	\$1.09	\$.99	\$.89
910901	TI	SN7400N	DIP-14	Quad 2-input pos. NAND gate	1.19	1.09	.95
49007	♦	7401N	DIP-14	Quad 2-input NAND gate (O.C.)	.89	.79	.65
49015	♦	7402N*	DIP-14	Quad 2-input pos. NOR gate	1.29	1.09	.95
49040	♦	7404N**	DIP-14	Hex inverter	1.39	1.19	1.09
49074	♦	7405N*	DIP-14	Hex inverter (O.C.)	.69	.59	.45
49091	♦	7406N**	DIP-14	Hex inverter buffer/driver	.99	.89	.69
49120	♦	7407N**	DIP-14	Hex buffer/driver	.99	.89	.69
49146	♦	7408N*	DIP-14	Quad 2-input pos. AND gate	1.95	1.75	1.49
49189	♦	7410N*	DIP-14	Triple 3-input pos. NAND gate	.89	.79	.59
49402	♦	7413N	DIP-14	Dual 4-input pos. NAND gate	1.25	1.15	1.05
49437	♦	7414N*	DIP-14	Hex schmitt-trigger inverter	.89	.79	.69
49630	♦	7416N*	DIP-14	Hex inverter buffer/driver (O.C.)	1.19	1.09	.99
49728	♦	7417N*	DIP-14	Hex buffer/driver (O.C. hi-volt)	1.09	.99	.89
50008	♦	7420N*	DIP-14	Dual 4-input NAND gate	.99	.89	.75
50139	♦	7427N	DIP-14	Triple 3-input NOR gate	.89	.79	.69
50227	♦	7430N*	DIP-14	8-input NAND gate	.99	.89	.79
50235	♦	7432N*	DIP-14	Quad 2-input pos. OR gate	1.29	1.09	.95
50315	♦	7438N*	DIP-14	Quad 2-input NAND buffer	.99	.89	.79
50374	♦	7442N	DIP-16	4 line BCD to 10 line decimal decoder	1.45	1.25	1.15
50403	♦	7445N	DIP-16	BCD-to-decimal decoder/driver	1.55	1.35	1.09
50420	♦	7447N*	DIP-16	BCD-to-7 seg. decoder/driver	2.49	2.25	1.75
50526	♦	7472N	DIP-14	AND-gated J-K master-slave flip-flop	.89	.79	.69
50534	♦	7473N	DIP-14	Dual J-K neg-edge-triggered flip-flop	1.95	1.75	1.59
50551	♦	7474N**	DIP-14	Dual D type flip-flop	.99	.89	.79
50577	♦	7475N	DIP-16	4-bit bistable latch	2.75	2.49	2.25
50593	♦	7476N	DIP-16	Dual J-K pos-edge-triggered flip-flop	2.95	2.65	2.39
50631	♦	7483N	DIP-16	4-bit binary full adder	2.95	2.65	2.39
50657	♦	7485N*	DIP-16	4-bit magnitude comparator	2.49	2.25	1.95
50665	♦	7486N	DIP-14	Quad 2-input exclusive OR gate	1.95	1.75	1.49
50681	♦	7489N	DIP-16	64-bit read/write memory	3.95	3.75	3.49
50690	♦	7490N	DIP-14	Asynchronous decade counter	2.95	2.65	2.39
50745	♦	7493N	DIP-14	4-bit binary counter	1.95	1.75	1.49
50770	♦	7495N	DIP-14	4-bit parallel-access shift register	1.45	1.25	1.15
49234	♦	74107N*	DIP-14	Dual J-K flip-flop with clear	.79	.69	.59
49322	♦	74121N*	DIP-14	Monostable multivibrator	2.75	2.39	1.95
49357	♦	74123N*	DIP-16	Dual monostable multivibrator	1.75	1.59	1.45
49373	♦	74125N	DIP-14	Tri-state quad bus buffer	1.49	1.35	1.19
49496	♦	74148N	DIP-16	8-to-3 line priority encoder	1.19	1.09	.79
49509	♦	74150N	DIP-24	1-of-16 data selector/multiplexer	2.95	2.75	2.25
49525	♦	74151N*	DIP-16	1-of-8 data selector/multiplexer	.79	.69	.45
49550	♦	74153N*	DIP-16	Dual 4-to-1 data selector/multiplexer	1.19	1.09	.79
49568	♦	74154N	DIP-24	4-to-16 line decoder/demultiplexer	2.95	2.39	2.09
49605	♦	74157N*	DIP-16	Quad 2-to-1 line data selector	.99	.89	.79
49648	♦	74160N*	DIP-16	Synchronous decade counter	.59	.55	.49
49664	♦	74161N	DIP-16	4-bit Synchronous binary counter	.89	.79	.69
49672	♦	74163N	DIP-16	Synchronous 4-bit binary counter	.79	.69	.59
49681	♦	74164N	DIP-14	8-bit serial shift register	.89	.79	.59
49779	♦	74174N*	DIP-16	Hex D-type flip-flop with clear	.69	.59	.49
49795	♦	74175N*	DIP-16	Quad D-type flip-flop with clear	1.35	1.25	1.15
49832	♦	74180N	DIP-14	9-bit odd/even parity generator/checker	.99	.89	.49
49883	♦	74189N	DIP-16	Tri-state 64-bit RAM	2.95	2.75	2.49
49904	♦	74191N	DIP-16	Synch. 4-bit up/down binary counter	1.95	1.75	1.45
49912	♦	74192N	DIP-16	Synch. 4-bit up/down decade counter	3.95	3.75	3.49
49939	♦	74193N	DIP-16	Synch. 4-bit up/down binary counter	2.95	2.75	2.49
49955	♦	74194N	DIP-16	4-bit bi-directional shift register	1.75	1.55	1.35
49963	♦	74195N	DIP-16	4-bit parallel-access shift register	1.75	1.55	1.35

*10 pcs./ **20 pcs. in 7400 series IC cabinet kit, top right

TTL Logic Data Book (1988)

Texas Instruments Contains specifications and technical information on a broad line of TTL integrated circuits including Schottky TTL circuits. (1240 pages)
• Size: 6.0" x 8.5"



Part No.	Description	Weight	1	5
88225	TTL Logic Data Book	2.6 lbs.	\$34.95	\$31.49

7400 Series IC Kit

Includes: 20-drawer component cabinet (319600), 20 clear plastic drawers (319601), 20 clear dividers (319611), pg 173 and 30 adhesive labels for drawers to identify parts in kit



10 each: 7402, 7405, 7408, 7410, 7414, 7416, 7417, 7420, 7430, 7432, 7438, 7447, 7470, 7485, 74107, 74121, 74123, 74132, 74151, 74153, 74157, 74160, 74174, 74175, 74279
20 each: 7400, 7404, 7406, 7407, 7474

SAVE \$202

Part No.	Description	Weight (lbs.)	1	5
84953	350 pcs. 7400 IC kit	6.2	\$199.95	\$179.95

74ABT/AC/ACT Series

*Web Code: CBA

Please Note: Manufacturer may vary

* Order in multiples of 10

Part No.	Product No.	Pkg.	Description	1	10	100
266159	74ACT08M	SOIC-14	Quad 2-input pos. AND gate	* .25	* \$15	* \$12
211983	74ACT08N	DIP-14	Quad 2-input pos. AND gate	.25	.22	.17
264145	74AC10M	DIP-14	Triple 3-input pos. NAND gate	* .09	* .06	
238887	74AC10N	DIP-14	Triple 3-input pos. NAND gate	.29	.25	.19
212003	74ACT32N	DIP-14	Quad 2-input pos. OR gate	* .15	* .12	
212011	74ACT74N	DIP-14	Dual D type flip-flop	* .19	* .17	
238730	74AC139N	DIP-16	Dual 2-to-4 decoder/demultiplexer	.25	.22	.17
238764	74AC157N	DIP-16	Quad 2-to-1 line data selector	.49	.39	.35
239054	74ACT174N	DIP-16	Hex D-type flip-flop with clear	.39	.35	.29
211908	74AC244N	DIP-20	Tri-state octal buffer/line driver	* .12	* .09	
212054	74ACT244N	DIP-20	Tri-state octal buffer/line driver	* .15	* .12	
214199	74AHC245N	DIP-20	Tri-state octal bus transceiver	* .15	* .12	
214236	74AHC574N	DIP-20	Tri-state octal D-type flip-flop	.25	.22	.15
267371	74ACT715M	SOIC-20	Programmable video sync generator	6.95	5.95	4.95
291784	74ABT2244AD	SOIC-20	Tri-state octal buffer	* .15	* .12	
291400	74ABT5402AD	SOIC-28	Tri-state 12-bit line/memory driver	2.95	2.49	1.95

74ALS/ALVC Series

*Web Code: SVC

Please Note: Manufacturer may vary

* Order in multiples of 10

Part No.	Product No.	Pkg.	Description	1	10	100
245294	74ALS00AN	DIP-14	Quad 2-input pos. NAND gate	\$.25	\$.22	\$.19
314309	74ALVC00T	TSSOP-14	Quad 2-input pos. NAND gate	.25	.22	.12
245307	74ALS04BN	DIP-14	Hex inverter	* .15	* .09	
314341	74ALVC08T	TSSOP-14	Quad 2-input pos. AND gate	.25	.22	.12
44134	74ALS32N	DIP-14	Quad 2-input pos. OR gate	.25	.22	.19
245892	74ALS74AN	DIP-14	Dual D-type flip-flop	.35	.25	.22
310295	74ALS244AM	SOIC-20	Tri-state octal buffer/line driver	.35	.25	.22
245788	74ALS258N	DIP-16	Quad 2-to-1 line data selector/multiplexer	.25	.22	.12

74C Series

*Web Code: RAG

Part No.	*Mfr.	Product No.	Pkg.	Description	1	10	100
44222	♦	74C00N	DIP-14	Quad 2-input pos. NAND gate	\$1.15	\$.95	\$.69
44231	♦	74C04N	DIP-14	Hex inverter (CD4069)	.89	.79	.59
44257	♦	74C14N	DIP-14	Hex schmitt-trigger inverter (CD40106)	.79	.69	.59
44361	♦	74C221N	DIP-16	Dual monostable multivibrator	3.75	3.15	2.49
44396	♦	74C373N	DIP-20	Octal D-type transparent latch	2.95	2.49	2.15
44409	♦	74C374N	DIP-20	Octal D-type flip-flop	1.95	1.75	1.49
44521	♦	74C912N	DIP-28	6-digit BCD display controller/driver	4.95	4.49	3.95
44564	♦	74C922N	DIP-18	16-key keyboard encoder	6.49	5.49	5.35
871869	FSC	MM74C922N	DIP-18	16-key keyboard encoder	7.95	7.49	6.95
44572	♦	74C923N	DIP-20	20-key keyboard encoder	4.95	4.25	3.95
44599	♦	74C926N	DIP-18	4-digit counter w/ 7-seg. output driver	10.95	9.95	8.95

* FSC = Fairchild Semiconductor | TI = Texas Instruments | ♦ Manufacturer Varies

*For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above



Order by Phone 24/7 at 1-800-831-4242 or Online at www.Jameco.com