

Audio Amps

*Web Code: MBP

Part No.	*Mfr.	Product No.	Pkg./Pins	Description	1	10	100
243678	ADI	OP275GP	DIP-8	Dual JFET audio op amplifier	\$2.25	\$1.85	\$1.49
24037	NSC	LM380N	DIP-14	2-watt, power amplifier	1.39	1.09	.75
24088	NSC	LM383T	TO-220/5	7-watt, high power	5.95	5.49	4.95
24096	NSC	LM384N	DIP-14	5-watt audio amplifier	1.65	1.45	1.05
24125	NSC	LM386N-1*	DIP-8	Low voltage, 250mW/6V	.79	.59	.45
24126	NSC	LM386N-1R	DIP-8	Low voltage, 250mW/6V	.65	.49	.41
839826	NSC	LM386N-1/NOBP	DIP-8	Low voltage audio power amp.	.99	.79	.55
24133	NSC	LM386N-3*	DIP-8	Low voltage, 500mW/9V	.69	.59	.49
24483	NSC	LM725CN	DIP-8	Instrumentation op amplifier	1.95	1.25	.95
295718	NSC	LM1203N	DIP-28	RGB video amplifier	5.95	5.49	4.95
24942	ON	MC1350P	DIP-8	Video IF amp. (12V operation)	2.95	2.75	2.49
23270	NSC	LM1875T	TO-220/5	20-watt audio power amp.	2.95	2.49	1.95
23288	NSC	LM1877N-9	DIP-14	Dual power audio amplifier	1.95	1.75	1.49
107140	NSC	LM1881N	DIP-8	Video synchronous separator	2.49	2.25	1.59
32897	ST	TDA2002V	TO-220/5	8-watt audio high power amp.	4.95	4.49	3.95
1416999	ST	TDA2030V	PWAT-5	14-watt hi-fi audio amp.	3.95	3.49	3.25
315344	ST	TDA2040V	PWAT-5	20-watt hi-fi power	2.25	1.95	1.75
275830	TI	OPA2134PA	DIP-8	High performance audio op amp.	3.25	2.95	2.75
275821	ADI	OPA2134UA	SOIC-8	High-performance audio op amp.	1.95	1.69	1.45
312063	ADI	SSM2141P	DIP-8	High common-mode rejection diff. line rec.	2.95	2.15	1.95
320670	NSC	LM3886TF	TO-220/11	68-watt high-perf., isol. pkg.	5.95	4.95	4.25
192516	NSC	LM3886T	TO-220/11	68-watt high-performance	5.95	4.95	3.95
302201	NSC	LM4752T	TO-220/7	Stereo 11-watt audio power amp.	2.95	2.75	2.49
316873	MOT	MC34119D	SOIC-8	LP audio amp. (500mW, 16VDC)	1.19	1.09	.89
316865	MOT	MC34119P	DIP-8	LP audio amp. (500mW, 16VDC)	2.25	2.05	1.85

*10 pieces included in Linear kit, pg 16 ♦ Blue Part No. = Limited Quantity Available

*Instrumentation Amps Available Online — Enter Web Code NDA

AMPLIFIERS

Part No.	*Mfr.	Product No.	Pkg.	Description	1	10	100
1805943	ADXL	ADXL213AE	LCC-8	5V, low cost \pm 2g dual-axis accelerometer	\$16.95	\$15.95	\$14.95
1780862	AD	AD620ANZ	DIP-8	Low cost, LP instrumentation amp	6.75	5.49	4.75
1781136	AD	AD627AR	SOIC-8	Low cost, instrumentation amp	4.95	3.95	3.49
311132	AD	AD811AN	DIP-8	High performance, video op amp	7.49	6.25	5.75

A/D & D/A Converters

*Web Code: QAG

Part No.	*Mfr.	Product No.	Pkg.	Description	1	10	100
277149	MAX	MAX110ACWE	SOIC-16	A/D, 14-bit, 5V, 50sps, 2-ch	\$9.95	\$8.75	\$8.25
277131	MAX	MAX110BCPE	DIP-16	A/D, 14-bit, 5V, 50sps, 2-ch	12.95	9.95	9.49
277122	MAX	MAX110BCWE	SOIC-16	A/D, 14-bit, 5V, 50sps, 2-ch	8.95	6.75	6.25
277069	MAX	MAX197BCNI	DIP-28	A/D, 12-bit, 5V, 10Ksps, 8-ch	19.95	13.95	11.95
289545	TI	TLC540IDW	SOIC-20	A/D, 8-bit, 5V, 75Ksps	3.49	2.95	2.49
289553	TI	TLC540IFN	PLCC-20	A/D, 8-bit, 5V, 75Ksps	3.49	2.95	2.49
289596	TI	TLC541IDW	SOIC-20	A/D, 8-bit, 5V, 40Ksps	2.95	2.49	1.95
289705	TI	TLC542IFN	PLCC-20	A/D, 8-bit, 5V, 25Ksps	1.95	1.75	1.49
289713	TI	TLC545CN	DIP-28	A/D, 8-bit, 5V, 76Ksps	4.95	4.25	3.95
10145	NSC	ADC0803LCN	DIP-20	A/D, 8-bit, 5V, 9.1Ksps, 1-ch	3.95	3.25	2.95
10153	NSC	ADC0804LCN	DIP-20	A/D, 8-bit, 5V, 9.1Ksps, 1-ch	2.75	2.25	1.85
828342	NSC	ADC0804LCN/NOBP	DIP-20	A/D, 8-bit μ P compatible (\pm 1LSB)	2.95	2.35	2.05
10170	NSC	ADC0808CCN	DIP-28	A/D, 8-bit, 5V, 9.1Ksps, 8-ch	4.75	3.95	3.39
10188	NSC	ADC0809CCN	DIP-28	A/D, 8-bit, 5V, 9.1Ksps, 8-ch	2.59	2.39	2.25
831031	NSC	ADC0816CCN	DIP-40	A/D, 8-bit, μ P comp. ADC w/ 16-ch.	11.95	10.25	9.25
10209	NSC	ADC0817CCN	DIP-40	A/D, 8-bit, 5V, 9.1Ksps, 16-ch	4.95	3.95	3.49
10225	NSC	ADC0820CCN	DIP-20	A/D, 8-bit, 5V, 1.5 μ s	3.49	3.15	2.49
116100	NSC	ADC0831CCN	DIP-8	A/D, 8-bit, 5V, 32 μ s	1.75	1.55	1.35
1252488	NSC	ADC0838CCN/NOBP	DIP-20	A/D, 8-bit serial, 5V, 32 μ s	2.75	2.25	1.75
290538	TI	TLC0832CD	SOIC-8	A/D, 8-bit, 3V, 32 μ s	2.49	2.25	1.75
288681	TI	THS1030IDW	SOIC-28	A/D, 10-bit, 3-5.5V, 30Msps	5.95	4.95	4.49
288729	TI	THS1031IPW	TSSOP-28	A/D, 10-bit, 3-5.5V, 30Msps	6.95	5.49	5.25

*ADI = Analog Devices | INS = Intersil | LTC = Linear Tech | MAX = Maxim | MCH = Microchip | MOT = Motorola | NSC = National Semi | ON = ON Semi | SAM = Samsung | ST = ST Micro | TI = Texas Instruments | ♦ Varies

♦ RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 197.

A/D & D/A Converters (Continued)

*Web Code: QAG

Part No.	*Mfr.	Product No.	Pkg.	Description	1	10	100
1748897	LTC	LTC1403AIMSE-1	MSOP-10	A/D, 14-bit, 2.8Msps samp ADC	\$14.95	\$12.95	\$10.95
289001	TI	TLC1541CDW	SOP-20	A/D, 10-bit, 5V, 32Ksps	4.95	4.25	3.95
289019	TI	TLC1541CN	DIP-20	A/D, 10-bit, 5V, 32Ksps	4.95	4.49	4.25
289078	TI	TLC1542CDW	SOP-20	A/D, 10-bit, 5V, 26 μ s, 11-ch	3.95	2.75	2.49
289271	TI	TLC1543QDB	SSOP-20	A/D, 10-bit, 6.5V, 5V, 26 μ s, 11-ch	3.95	3.49	2.95
289300	TI	TLC1543QDW	SOIC-20	A/D, 10-bit, 6.5V, 5V, 26 μ s, 11-ch	3.95	3.49	2.95
288593	TI	PCM1800E	SSOP-24	A/D, 20-bit, 5V, 32-48KHz, 2-ch	3.49	3.25	2.95
288622	TI	PCM1801U	SOIC-14	A/D, 20-bit, 5V, 32-48KHz, 2-ch	3.95	3.49	3.25
290634	TI	TLV2543CDW	SOIC-20	A/D, 12-bit, 3.3V, 10 μ s, 11-ch	7.95	5.95	4.95
290669	TI	TLV2543CN	DIP-20	A/D, 12-bit, 3.3V, 10 μ s, 11-ch	7.95	5.95	4.95
288016	MCH	MCP3302-CI/SL	SOIC-14	A/D, 13-bit, 2.7-5.5V, 50-100Ksps, 2-ch	2.95	2.49	2.25
288024	MCH	MCP3302-CI/ST	TSSOP-14	A/D, 13-bit, 2.7-5.5V, 50-100Ksps, 2-ch	2.49	2.35	2.15
43748	♦	7106CPL	DIP-40	A/D, 3 1/2-digit LCD/LED, 9V	2.25	1.95	1.75
43756	♦	7107CPL	DIP-40	A/D, 3 1/2-digit LCD/LED, \pm 5V	2.49	2.25	1.95
875683	INS	ICL7107CPL	DIP-40	A/D, 3 1/2-digit LCD/LED, 6V	3.25	2.95	2.59
43764	♦	7109CPL	DIP-40	A/D, 12-bit, 5V, 30sps, 1-ch	3.95	2.25	1.95
115158	ADI	AD558JN	DIP-16	D/A, 8-bit, 5-15V, 1-5-3 μ s, 1-ch	12.95	11.75	10.49
1944581	SAM	KDA0408	DIP-42	D/A, 8-bit, 5V, 60Msps, triple	.49	.39	.35
14904	NSC	DAC0800LCN	DIP-16	D/A, 8-bit, 4.5-18V, 150ns	1.49	1.19	.89
14947	NSC	DAC0808LCN	DIP-16	D/A, 8-bit, 4.5-18V, 150ns	1.65	1.25	.95
14963	NSC	DAC0830LCN	DIP-20	D/A, 8-bit, 5-15V, 1 μ s	4.95	4.25	3.49
128186	NSC	DAC0832LCN	DIP-20	D/A, 8-bit, 5-15V, 1 μ s	3.49	2.75	2.49
290781	TI	TLV5604ID	SOIC-16	D/A, 10-bit, 2.7-5.5V, 20MHz, 4-ch	5.95	4.75	4.49
290790	TI	TLV5604IPW	TSSOP-16	D/A, 10-bit, 2.7-5.5V, 20MHz, 4-ch	5.95	4.75	4.49
290853	TI	TLV5613IPW	TSSOP-20	D/A, 12-bit, 2.7-5.5V, 3-7 μ s, 1-ch	5.95	4.95	3.75
290933	TI	TLV5614CPW	TSSOP-16	D/A, 12-bit, 2.7-5.5V, 5.5-2.0 μ s, 4-ch	10.95	9.95	8.95
296690	ADI	AD7226KN	DIP-20	D/A, 8-bit, 2-12.5V, 4 μ s, 4-ch	9.95	8.95	7.95
1783887	ADI	AD7398BRUZ	TSSOP-16	D/A, 12-bit, quad serial In	15.95	13.95	11.95
290052	TI	TLC7524CN	DIP-16	D/A, 8-bit, 5-15V, 100ns	2.75	2.49	2.05
287380	ADI	AD9760AR	SOIC-28	D/A, 10-bit, 3-5V, 125Msps	5.95	3.95	2.95

Op Amps

*Web Code: WAD

Part No.	*Mfr.	Product No.	Pkg.	Description	1	10	100
27852	♦	OP07CP	DIP-8	Ultra-low offset voltage	\$.75	\$.65	\$.55
252988	♦	OP07DP	DIP-8	Very low offset single bipolar	.69	.59	.49
23106	♦	LM10CLN	DIP-8	Low voltage (1.1 volt)	2.75	2.49	1.75
120715	♦	LM10CN	DIP-8	Op amp and voltage reference	2.49	2.25	1.95
1062114	TI	TL026CP	DIP-8	Diff. high-freq. amp. w/ AGC	.49	.39	.25
1807439	ADI	OP27AZ/883C	DIP-8	Low noise precision op amp.	34.95	29.95	27.95
275805	TI	OPA27GP	DIP-8	Ultra-low noise precision	2.19	2.09	1.95
275784	TI	OPA27GU	SOIC-8	Ultra-low noise precision	2.05	1.75	1.59
115300	♦	OP27EP	DIP-8	Low noise precision op amp	3.95	3.49	3.25
115318	♦	OP27GP	DIP-8	Low noise prec. (-40° to 80°C)	2.49	1.95	1.59
1944812	ST	TL27L2IN	DIP-8	Prec. very low pwr CMOS dual	.59	.49	.35
821676	TI	TL051IP	DIP-8	Enhanced JFET low offset	.39	.35	.25
213129	♦	TL052ACP	DIP-8	Enh. JFET low offset op amp	1.25	.95	.85
33187	♦	TL071CP	DIP-8	Low noise JFET op amp.	.29	.25	.22
213073	♦	TL072ACP	DIP-8	Low noise JFET input op amp	.79	.69	.59
33195	♦	TL072CP*	DIP-8	Low noise JFET dual op amp.	.25	.22	.19

*10 pcs. included in Linear cabinet kit, pg 16

Op Amps continued on next page



Tech Closeout Center

Small Quantities Priced Near Cost
New Products and Accessories
That Didn't Make The Catalog
Discontinued Consumer Products
And a few surprises...

www.Jameco.com/TechCenter