



74LS Series

*Web Code: NBS

Part No.	Mfr.	Product No.	Pkg.	Description	1	10	100
46252	◆	74LS00N**	DIP-14	Quad 2-input pos. NAND gate	\$.39	\$.29	\$.25
46253	◆	74LS00N	DIP-14	Quad 2-input pos. NAND gate	.45	.35	.29
283725	TI	SN74LS00N	DIP-14	Quad 2-input pos. NAND gate	.45	.35	.29
46287	◆	74LS02N**	DIP-14	Quad 2-input pos. NOR gate	.39	.29	.25
283741	TI	SN74LS02N	DIP-14	Quad 2-input pos. NOR gate	.45	.35	.29
283784	TI	SN74LS03N	DIP-14	Quad 2-input pos. NAND gate (O.C.)	.69	.49	.45
46316	◆	74LS04N**	DIP-14	Hex inverter	.39	.29	.25
283792	TI	SN74LS04N	DIP-14	Hex inverter	.45	.35	.29
46318	◆	74LS04N	DIP-14	Hex inverter	.45	.35	.29
46341	◆	74LS05N*	DIP-14	Hex inverter (O.C.)	.45	.35	.29
46359	◆	74LS06N	DIP-14	Hex inverter buffer/driver	.75	.65	.55
46367	◆	74LS07N	DIP-14	Hex buffer/driver	.75	.65	.55
46375	◆	74LS08N**	DIP-14	Quad 2-input pos. AND gate	.39	.29	.25
295401	TI	SN74LS08N	DIP-14	Quad 2-input pos. AND gate	.45	.35	.29
46391	◆	74LS09N	DIP-14	Quad 2-input pos. AND gate (O.C.)	.45	.35	.29
46404	◆	74LS10N*	DIP-14	Triple 3-input pos. NAND gate	.55	.39	.35
46439	◆	74LS11N*	DIP-14	Triple 3-input pos. AND gate	.55	.39	.35
46640	◆	74LS14N*	DIP-14	Hex schmitt-trigger inverter	.39	.29	.25
295460	TI	SN74LS14N	DIP-14	Hex schmitt-trigger inverter	.45	.35	.29
47095	◆	74LS20N*	DIP-14	Dual 4-input NAND gate	.59	.49	.39
295478	TI	SN74LS20N	DIP-14	Dual 4-input NAND gate	.65	.55	.45
47108	◆	74LS21N	DIP-14	Dual 4-input AND gate	.49	.39	.29
47378	◆	74LS27N	DIP-14	Triple 3-input NOR gate	.59	.49	.39
47458	◆	74LS30N*	DIP-14	8-input NAND gate	.29	.25	.22
47466	◆	74LS32N**	DIP-14	Quad 2-input pos. OR gate	.35	.25	.22
295515	TI	SN74LS32N	DIP-14	Quad 2-input pos. OR gate	.49	.45	.39
47467	◆	74LS32N	DIP-14	Quad 2-input pos. OR gate	.39	.29	.25
295558	TI	SN74LS37N	DIP-14	Quad 2-input pos. NAND buffer	.65	.55	.45
47773	◆	74LS42N	DIP-14	4 line BCD to 10 line decimal decoder	.85	.75	.65
47790	◆	74LS47N*	DIP-16	BCD-to-7 seg. decoder/driver	1.09	.89	.79
295582	TI	SN74LS47N	DIP-16	BCD-to-7 seg. decoder/driver	1.19	.99	.89
47811	◆	74LS48N	DIP-16	BCD-to-7 seg. decoder/driver	3.95	3.49	2.95
47992	◆	74LS73N*	DIP-14	Dual J-K neg-edge-triggered flip-flop	1.09	.95	.75
48004	◆	74LS74N**	DIP-14	Dual D-type flip-flop	.49	.39	.35
295726	TI	SN74LS74AN	DIP-14	Dual D-type flip-flop	.55	.45	.39
48021	◆	74LS75N*	DIP-16	4-bit bi-stable latch	1.15	.95	.79
295734	TI	SN74LS75N	DIP-16	4-bit bi-stable latch	1.25	1.05	.85
48039	◆	74LS76N	DIP-16	Dual J-K pos-edge-triggered flip-flop	1.29	1.19	1.09
48063	◆	74LS83N	DIP-16	4-bit binary full adder	2.19	1.99	1.79
48071	◆	74LS85N*	DIP-16	4-bit magnitude comparator	.79	.69	.59
295742	TI	SN74LS85N	DIP-16	4-bit magnitude comparator	.89	.79	.65
48098	◆	74LS86N*	DIP-14	Quad 2-input exclusive OR gate	.49	.39	.29
295751	TI	SN74LS86N	DIP-14	Quad 2-input exclusive OR gate	.55	.45	.35
48119	◆	74LS90N*	DIP-14	Asynchronous decade counter	1.25	1.15	.85
295769	TI	SN74LS90N	DIP-14	Asynchronous decade counter	1.35	1.25	.95
48143	◆	74LS92N	DIP-14	Divide-by-12 decade counter	1.49	1.29	1.09
48151	◆	74LS93N*	DIP-14	4-bit binary counter	1.25	1.05	.79
295822	TI	SN74LS93N	DIP-14	4-bit binary counter	1.35	1.15	.89
46412	◆	74LS107N	DIP-14	Dual J-K flip-flop with clear	1.05	.89	.69
46421	◆	74LS109N	DIP-16	Dual J-K bar flip-flop	.85	.75	.65
46447	◆	74LS112N	DIP-16	Dual J-K neg-edge-triggered flip-flop	.55	.45	.35
46471	◆	74LS122N	DIP-14	Retriggerable monostable multivibrator	.89	.79	.69
46480	◆	74LS123N*	DIP-16	Dual monostable multivibrator	.55	.45	.35
300880	TI	SN74LS123N	DIP-16	Dual monostable multivibrator	.59	.49	.39
46501	◆	74LS125N*	DIP-14	Tri-state quad bus buffer	.55	.45	.35
46527	◆	74LS126N	DIP-14	Tri-state quad bus buffer	.55	.45	.35
46551	◆	74LS132N	DIP-14	Quad 2-input NAND schmitt trigger	.59	.49	.39

*10 pcs./ **20 pcs. in 74LS series IC cabinet kit, pg 6

74LS Series (Continued)

*Web Code: NBS

Part No.	Mfr.	Product No.	Pkg.	Description	1	10	100
46586	◆	74LS136N	DIP-14	Quad 2-input exclusive OR gate	\$.39	\$.35	\$.25
46607	◆	74LS138N**	DIP-16	3-to-8 decoder/demultiplexer	.49	.39	.29
301233	TI	SN74LS138N	DIP-16	3-to-8 decoder/demultiplexer	.65	.55	.45
46608	◆	74LS138N	DIP-16	3-to-8 decoder/demultiplexer	.69	.59	.49
46623	◆	74LS139N*	DIP-16	Dual 2-to-4 decoder/demultiplexer	.49	.39	.29
301268	TI	SN74LS139AN	DIP-16	Dual 2-to-4 decoder/demultiplexer	.55	.45	.35
46666	◆	74LS145N	DIP-16	BCD-to-decimal decoder/driver	.59	.49	.39
301276	TI	SN74LS145N	DIP-16	BCD-to-decimal decoder/driver	.65	.55	.45
46682	◆	74LS148N	DIP-16	8-to-3 line priority encoder	.95	.85	.75
46703	◆	74LS151N*	DIP-16	1-to-8 data selector/multiplexer	.65	.55	.45
46720	◆	74LS153N	DIP-16	Dual 4-to-1 data selector/multiplexer	.65	.55	.45
46738	◆	74LS154N	DIP-24	4-to-16 line decoder/demultiplexer	4.95	4.75	4.25
46754	◆	74LS155N*	DIP-16	Dual 2-to-4 line decoder/demultiplexer	.85	.75	.65
46771	◆	74LS157N*	DIP-16	Quad 2-to-1 line data selector	.49	.39	.29
46800	◆	74LS160N	DIP-16	Synchronous decade counter	2.49	2.25	2.05
46818	◆	74LS161N	DIP-16	4-bit synchronous binary counter	.55	.45	.35
301647	TI	SN74LS161AN	DIP-16	4-bit synchronous binary counter	.59	.49	.39
46842	◆	74LS163N	DIP-16	Synchronous 4-bit binary counter	.59	.49	.39
46851	◆	74LS164N	DIP-14	8-bit serial shift register	.55	.45	.35
46877	◆	74LS165N	DIP-16	8-bit parallel load shift register	.55	.45	.35
46885	◆	74LS166N	DIP-16	Serial-out shift register	.89	.79	.69
46906	◆	74LS169N	DIP-16	Synch. 4-bit binary up/down counter	.99	.89	.79
46922	◆	74LS173N	DIP-16	4-bit D-type register w/ 3-state output	.89	.79	.69
46931	◆	74LS174N*	DIP-16	Hex D-type flip-flop with clear	.69	.59	.49
46957	◆	74LS175N*	DIP-16	Quad D-type flip-flop with clear	.59	.49	.39
46973	◆	74LS181N	DIP-24	Arithmetic logic unit/function generator	2.95	2.75	2.49
46990	◆	74LS190N	DIP-16	Synchronous up/down decade counter	2.95	2.75	2.49
47001	◆	74LS191N	DIP-16	Synch. 4-bit up/down binary counter	.65	.55	.45
47010	◆	74LS192N	DIP-16	Synch. 4-bit up/down decade counter	3.49	3.25	2.95
47036	◆	74LS193N*	DIP-16	Synch. 4-bit up/down binary counter	.45	.39	.35
301831	TI	SN74LS193N	DIP-16	Synch. 4-bit up/down binary counter	.89	.79	.69
47052	◆	74LS194N	DIP-16	4-bit bi-directional shift register	.89	.79	.69
301858	TI	SN74LS194N	DIP-16	4-bit bi-directional shift register	.99	.89	.75
47061	◆	74LS195N	DIP-16	4-bit parallel-access shift register	2.05	1.95	1.75
47124	◆	74LS221N	DIP-16	Dual monostable multivibrator	.75	.65	.55
47141	◆	74LS240N*	DIP-20	Octal buffer/line driver	.59	.49	.39
308291	TI	SN74LS240N	DIP-20	Octal buffer/line driver	.65	.55	.45
47167	◆	74LS241N	DIP-20	Tri-state octal buffer/line driver	.65	.55	.45
47183	◆	74LS244N*	DIP-20	Tri-state octal buffer/line driver	.55	.45	.35
308312	TI	SN74LS244N	DIP-20	Tri-state octal buffer/line driver	.59	.49	.39
47212	◆	74LS245N*	DIP-20	Tri-state octal bus transceiver	.65	.55	.39
308321	TI	SN74LS245N	DIP-20	Tri-state octal bus transceiver	.69	.59	.45
47247	◆	74LS247N	DIP-16	BCD to 7-seg. decoder/driver	1.09	.99	.89
47327	◆	74LS259N	DIP-16	8-bit addressable latch	.89	.79	.69
47360	◆	74LS266N	DIP-14	Quad 2-input exclusive NOR gate (O.C.)	.65	.55	.45
47386	◆	74LS273N*	DIP-20	Octal D-type flip-flop	.59	.49	.39
308398	TI	SN74LS273N	DIP-20	Octal D-type flip-flop	.65	.55	.45
47407	◆	74LS279N	DIP-16	Quad S-R latch	.75	.65	.55
47423	◆	74LS283N	DIP-16	4-bit binary full add w/ fast carry	.95	.85	.65
47554	◆	74LS366N	DIP-6	Tri-state hex buffer	.59	.49	.39
47562	◆	74LS367N	DIP-16	Tri-state hex buffer	.69	.59	.49
309278	TI	SN74LS368AN	DIP-16	6-bit buffer/line driver	.79	.69	.59
308460	TI	SN74LS373N	DIP-20	Octal D-type transparent latch	.59	.49	.39
47600	◆	74LS373N*	DIP-20	Octal D-type transparent latch	.55	.45	.35
308478	TI	SN74LS374N	DIP-20	Octal D-type flip-flop	.59	.49	.39
47634	◆	74LS374N*	DIP-20	Octal D-type flip-flop	.55	.45	.35
1944311	◆	74LS375N	DIP-16	4-bit bistable latch	.75	.65	.45
47669	◆	74LS377N	DIP-20	Octal D-type flip-flop	.85	.75	.65
47722	◆	74LS390N	DIP-16	Dual 4-bit decade counter	.95	.85	.75
47731	◆	74LS393N	DIP-14	Dual 4-bit binary counter	.75	.65	.55
47861	◆	74LS540N	DIP-20	Tri-state octal buffer/line driver	.89	.79	.69

*10 pcs./ **20 pcs. in 74LS series IC cabinet kit, pg 6

74LS Series continued on next page

* TI = Texas Instruments ◆ Manufacturer Varies

*For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above

3 LEVELS OF SAVINGS
NAME BRANDS HOUSE BRANDS FACTORY OVERRUN