

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.

SPECIFICATION

CUSTOMER: JAMES
 MODEL NO: DDU120150

DATE: '05.03.16
 DESIGNED NO: J1160

- 1. APPLICABLE SAFETY STANDARD :**
 T-MARK PSE UL 1310 UL 1950 C-CUL GS CE 商檢
 SEMKO、DEMKO、FIMKO、NEMKO OTHER : _____
- 2. GENERAL APPEARANCE :**
 2.1 THE GENERAL APPEARANCE OF THE AC/DC ADAPTOR SHALL BE WITHOUT DEFORMATION, CRACKS OR CORROSION.
 2.2 THE SHAPE, DIMENSIONS AND MARKINGS OF THE AC/DC ADAPTOR SHALL BE AS SPECIFIED IN THE CONSTRUCTION DRAWING AND NAME PLATE.
- 3. CHARACTERISTICS :**
 3.1 PRIMARY RATED VOLTAGE & LINE FREQUENCY : 120 VAC 60 Hz
 3.2 PRIMARY EXCITING CURRENT (Io) 90 mA MAX. AT INPUT 120 VAC 60 Hz.
 LOADING CURRENT (Ip) X mA MAX. AT INPUT X AC X Hz, LOAD X A.
 3.3 NO – LOAD LOSS : X W MAX. AT INPUT X VAC X Hz.
 3.4 SECONDARY RATED VOLTAGE AND CURRENT :
- | PRIMARY VOLTAGE | RATE VOLTAGE | TOLERANCE | RATED CURRENT | NO-LOAD VOLTAGE | REGULATION |
|-----------------|--------------|-----------|---------------|-----------------|------------|
| 120VAC 60Hz | 12VDC | ±5% | 1500mA-DC | | |
| | | | | | |
| | | | | | |
| | | | | | |
- 3.5 RIPPLE VOLTAGE : X mV(PK-PK) MAX. AT INPUT X VAC X Hz, LOAD X A.
 3.6 DC RESISTANCE : PRIMARY: X Ω± X % MEASURED AT 25 °C .
 3.7 HI-POT TEST : AC 1240 V 50/60Hz FOR 1 MINUTES BETWEEN INPUT TO OUTPUT PLUG AND CASE NEED NORMAL PERFORMANCE , LEAKAGE CURRENT 1 mA.
 3.8 INSULATION RESISTANCE : 500 VDC 100 MΩ MIN. BETWEEN INPUT TO OUTPUT PLUG AND CASE.
 3.9 TEMPERATURE RISE :INPUT 120 VAC 60 Hz, OUTPUT LOAD 1.5 A FOR INPUT COIL 75 °C MAX (BY USE RESISTANCE METHOD) ON CASE SURFACE X °C MAX (BY USE THERMOMETER METHOD) AT 25°C AMBIENT.
 3.10 HUMIDITY TEST : TEMP. 40± 2 °C , 90-95 % R.H FOR 4 HOURS , AFTER AT MINUTES TAKEN OUT FROM OVEN . AND WIPED DRY. TEST 3.4、3.7 AND INSULATION TEST 10 MΩ MIN.
- 4. MECHANICAL PERFORMANCE :**
 4.1 STRAIN-RELIEF TEST : 10 LB FOR 60 SEC. IN ANY DIRECTION .
 4.2 DROP TEST : UNIT IS TO BE DROPPED FROM 3 FEET HIGH ONTO A CONCRETE FLOOR COVERED WITH 1/8 INCH VINYL TILE 3 TIMES, THE UNIT SHOULD MEET THE ITEM 3.7、3.8.
 4.3 BENDING RELIEF TEST : THE CORD AND S/R SHALL WITHSTAND WEIGHT OFF 200 g, IT SWINGS FROM LEFT TO RIGHT AT AN ANGLE OF 120 deg , 300 CYCLE TIMES NIN.
 4.4 VIBRATION RESISTANCE : PRODUCT PACKAGED IN A INTENDED MANNER SHALL DEVELOP NO MECHANICAL OR ELECTRICAL FAILURE WHEN SUBJECTED TO A 1.5 mm PEAK TO PEAK AMPLITUDE , 10-50-10 Hz , VIBRATION IN EACH OF X , Y AND Z DIRECTIONS FOR 30 MINUTES .
- 5. TEMPERATURE RANGE:**
 5.1 USE TEMPERATURE EXTENT : 0 °C ~ +40 °C
 5.2 STORAGE TEMPERATURE EXTENT : -25 °C ~ +55 °C


APPROVED BY _____ CHECKED BY _____ TESTED BY 李淑華

ELECTRICAL DATA

CUSTOMER: JAMES
 MODEL NO: DDU120150


DATE: '05.03.16
 DESIGNED NO: J1160

ITEM	SPEC.	SAMPLE									
		1	2	3	4	5	6	7	8	9	10
PRIMARY EXCITING CURRENT INPUT 120 V-AC 60 Hz	90mA MAX.	51									
PRIMARY LOAD CURRENT INPUT 120 V-AC 60 Hz	mA	268									
SECONDARY #1 NO LOAD DC VOLTAGE		16.75									
SECONDARY #1 DC VOLTAGE LOAD 1500mA-DC	12V±5%	11.99									
TEMP RISE AFTER 4 HRS WARM UP IN 25 °C AMBIENT	75 °C MAX.	OK									
HI-POT TEST	PRI. TO SEC. & CORE AC 1240 V	OK									




APPROVED BY _____ CHECKED BY _____ TESTED BY 李淑華

聯輝電機股份有限公司




聯輝電機股份有限公司



聯輝電機股份有限公司

No	DESCRIPTION	MATERIAL	SPEC. & Q'TY	MANUFACTURE
1	Enclosure	Noryl SE 100		GE Plastics Japan Ltd. (E45587(B))
2	Primary Blades	Nickel Plating		Spread Profit Co., Ltd. or Equivalent.
3	Primary Winding	Polyurethane Enameled Copper Wire		Tai-I Electric Wire & Cable Co., Ltd. (E85640(S)) or Equivalent.
4	Primary Outerwrap	Polyester Film Tape	0.05mm (4T)	Chyun Yih Tape Co., Ltd. (E81174) or Equivalent.
5	Secondary Winding	Polyurethane Enameled Copper Wire		Tai-I Electric Wire & Cable Co., Ltd. (E85640(S)) or Equivalent.
6	Secondary Outerwrap	Polyester Film Tape	0.025mm (2T)	Chyun Yih Tape Co., Ltd. (E81174) or Equivalent.
7	Nameplate	P.V.C	0.35mm	I Houng Name Plate Co., Ltd. or Equivalent.
8	Core	Silicon Steel	0.5mm	Top Silicon Steel Corp. or Equivalent. or Equivalent.
9	Bobbin	Zytel 101 NY66		E.I Dupont De Nemoure & Company (E41938(M)) or Equivalent.
10	Rectifier Board	P.C.B	94V-0	Chen Hsien Enterprise Co. (E105119) or Equivalent.
11	Diodes	RL201---5		Master Instrument Corp. or Equivalent. or Equivalent.
12	Capacitor	2200uf/25V	105°C	Jun Fu Electronics Co., Ltd. or Equivalent.
13	Output Cord	Flexible Cord	AWG#20	Lu Her Wire & Cable Co., Ltd. or Equivalent.
14	Thermal Cutoff	M20 or A2	115°C	Joint Force Metal Research (E142267N) or Equivalent.


聯輝電機股份有限公司




- 1.尺寸:100x60x74m/m No.11 2.磅數: 450 磅
 3.印刷:白底藍色字体及圖案 色號: PMS 300

出圖章	名稱	小紙盒	5					
	料號		4					
	發行日		3					
	核准	品保審核	製圖	2				
			李淑華	1	符號	日期	變更事項	修訂者
				單位:m/m	版次	圖號		

聯輝電機股份有限公司



DATE CODE: XXXX



- 1.材質: PVC
- 2.厚度: $0.35^{+0.2}_{-0.1}$
- 3.印刷: 銀底黑字

出圖章	名稱	銘牌	5				
	料號		4				
	發行日		3				
	核准	品保審核	製圖	2			
				1			
	符號	日期	變更事項			修訂者	審核者
	單位:m/m	版次		圖號			