





Dimensions in mm



Rated Current	Breaking capacity	Rated Voltage	MFG52/-P-PA-PR		
			UL	SP	JET
100mA	@125V/AC 10KA @250V/AC 35A	125V/250V	○	○	
125mA		125V/250V	○	○	
160mA		125V/250V	○	○	
200mA		125V/250V	○	○	
250mA		125V/250V	○	○	
300mA		125V/250V	○	○	
315mA		125V/250V	○	○	
400mA		125V/250V	○	○	
500mA		125V/250V	○	○	
600mA		125V/250V	○	○	
630mA		125V/250V	○	○	
700mA		125V/250V	○	○	
800mA		125V/250V	○	○	
1A		125V/250V	○	○	○
1.25A		125V/250V	○	○	○
1.5A	125V/250V	○	○	○	
1.6A	125V/250V	○	○	○	
2A	@125V/AC 10KA @250V/AC 100A	125V/250V	○	○	○
2.5A	125V/250V	○	○	○	
3A	125V/250V	○	○	○	
3.15A	125V/250V	○	○	○	
3.5A	125V/250V	○	○	○	
4A	125V/250V	○	○	○	
5A	@125V/AC 10KA @250V/AC 200A	125V/250V	○	○	○
6A	125V/250V	○	○	○	
6.3A	125V/250V	○	○	○	
7A	125V/250V	○	○	○	
8A	125V/250V	○	○	○	
* 10A	125V/250V	○	○	○	
12A	@32V/AC 1000A	32V			
13A		32V			
15A		32V			
16A		32V			
20A		32V			
25A		32V			
30A		32V			

Test Specification according to Standard UL 248-1,14

Electrical Characteristic

Rated Current	1.0 In	1.35 In	2 In
In	Min.	Max.	Max.
100mA-30A	4 h	3600 S	120 S

GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO. 102041	GOLDSUN NO. MFG52A0.500N	
Description FUSE GMA FAST ACTING 0.5A 250V 5mmx20mm (GFS5250)		
Rev.	1	
UNIT: mm	SCALE: SHEET 1 OF 1	CAS No: ERN No: