



7400 Series

*Web Code: XAG

Part No.	*Mfr.	Cross Ref.	Pkg.	Description	1	10	100
910901	TI	SN7400N	DIP-14	Quad 2-input pos. NAND gate	\$.99	\$.89	\$.75
48979	+	7400N**	DIP-14	Quad 2-input NAND gate	.89	.79	.65
49007	+	7401N	DIP-14	Quad 2-input NAND gate (O.C.)	.89	.79	.65
49015	+	7402N*	DIP-14	Quad 2-input NOR gate	1.09	.95	.75
49040	+	7404N**	DIP-14	Hex inverters	1.09	.95	.75
49074	+	7405N*	DIP-14	Hex inverters (O.C.)	.69	.59	.45
910987	TI	SN7406N	DIP-14	Hex buffer/driver (O.C. hi-volt)	.79	.75	.65
49091	+	7406N**	DIP-14	Hex inverter buffer/driver (O.C.)	.69	.65	.59
49120	+	7407N**	DIP-14	Hex buffer/driver (O.C.)	.69	.65	.59
49146	+	7408N*	DIP-14	Quad 2-input AND gate	1.49	1.35	1.25
49189	+	7410N*	DIP-14	Triple 3-input NAND gate	.89	.79	.59
49402	+	7413N	DIP-14	Dual 4-input NAND gate schmitt trig.	1.25	1.15	1.05
49437	+	7414N*	DIP-14	Hex inverters schmitt trigger	.89	.79	.69
49630	+	7416N*	DIP-14	Hex inverter buffer/drivers (O.C.)	1.19	1.09	.99
49728	+	7417N*	DIP-14	Hex buffer/drivers (O.C. hi-volt)	1.09	.99	.89
50008	+	7420N*	DIP-14	Dual 4-input NAND gate	.99	.89	.75
50139	+	7427N	DIP-14	Triple 3-input NOR gate	.89	.79	.69
50227	+	7430N*	DIP-14	8-input NAND gate	.69	.59	.45
50235	+	7432N*	DIP-14	Quad 2-input OR gate	1.05	.95	.85
50315	+	7438N*	DIP-14	Quad 2-input NAND buffer (O.C.)	.79	.69	.59
50374	+	7442N	DIP-16	BCD-to-decimal decoder	1.45	1.25	1.15
50403	+	7445N	DIP-16	BCD-to-decimal decoder/driver	1.55	1.35	1.09
50420	+	7447N*	DIP-16	BCD-to-7 seg. decoder/drv. (L.O.)	1.59	1.45	1.15
50526	+	7472N	DIP-14	JK master/slave flip-flop, AND gate	.89	.79	.69
50534	+	7473N	DIP-14	Dual JK flip-flops with clear	1.95	1.75	1.59
50551	+	7474N**	DIP-14	Dual D flip-flops	.79	.69	.59
50577	+	7475N	DIP-16	4-bit bi-stable latch	2.49	2.35	2.19
50593	+	7476N	DIP-16	Dual JK flip-flop w/ preset & clear	2.95	2.65	2.39
50631	+	7483N	DIP-16	4-bit binary full adder	2.95	2.65	2.39
50657	+	7485N*	DIP-16	4-bit magnitude comparator	2.15	1.95	1.75
50665	+	7486N	DIP-14	Quad exclusive-OR gate	1.75	1.59	1.45
50681	+	7489N	DIP-16	64-bit RAM P 50ns	3.95	3.75	3.49
50690	+	7490N	DIP-14	Decade counter	2.95	2.65	2.39
50745	+	7493N	DIP-14	4-bit binary counter	1.75	1.59	1.45
50770	+	7495N*	DIP-14	4-bit parallel-access shift reg.	1.45	1.25	1.15
49234	+	74107N*	DIP-14	Dual JK flip-flop with clear	.79	.69	.59
49322	+	74121N	DIP-14	Monostable multivibrator	1.49	1.35	1.25
49357	+	74123N*	DIP-16	Dual retriggerable mono multivib.	1.75	1.59	1.45
49373	+	74125N	DIP-14	Quad bus buffer tri-state	1.49	1.35	1.19
49470	+	74145N	DIP-16	BCD-to-decimal decoder/driver	1.49	1.35	1.19
49496	+	74148N	DIP-16	8 to 3 line octal priority encoder	1.19	1.09	.79
49509	+	74150N	DIP-24	16 to 1 line multiplexer	2.19	1.95	1.75
49525	+	74151N*	DIP-16	8-input multiplexer	.79	.69	.45
49550	+	74153N*	DIP-16	Dual 4/1 data selector/multiplexer	1.19	1.09	.79
49568	+	74154N	DIP-24	4 to 16 line decoder/demultiplexer	1.95	1.75	1.49
49605	+	74157N*	DIP-16	Quad 2/1 data selector	.99	.89	.79
49648	+	74160N*	DIP-16	Decade counter w/ async clear	.59	.55	.49
49664	+	74161N	DIP-16	Synch. 4-bit counter w/ direct clear	.89	.79	.69
49672	+	74163N	DIP-16	Fully synchronous 4-bit counter	.79	.69	.59
49681	+	74164N	DIP-14	8-bit serial shift register	.89	.79	.59
49795	+	74175N*	DIP-16	Quad D-type flip-flop with clear	1.35	1.25	1.15
49832	+	74180N	DIP-14	9-bit odd/even parity generatr/checker	.99	.89	.49
49883	+	74189N	DIP-16	64-bit RAM tri-state	2.95	2.75	2.49
49904	+	74191N	DIP-16	Binary up/down counter	1.95	1.75	1.45
49912	+	74192N	DIP-16	Decade up/down counter w/ clear	3.95	3.75	3.49
49939	+	74193N	DIP-16	Binary up/down counter w/ clear	2.95	2.75	2.49
49955	+	74194N	DIP-16	4-bit bi-directional shift register	1.75	1.55	1.35
49963	+	74195N	DIP-16	4-bit parallel-access shift reg.	1.75	1.55	1.35

*10 pcs./ **20 pcs. in 7400 series IC cabinet kit, right

74AC/ACT Series

Please Note: Manufacturer may vary

*Web Code: CDR

Part No.	Cross Ref.	Pkg.	Description	1	10	100
266159	74ACT08M	SOIC-14	Quad 2-input AND gate	*.15	\$.12	\$.12
211983	74ACT08N	DIP-14	Quad 2-input AND gate	.25	.19	.17
238887	74AC10N	DIP-14	Triple 3-input NAND gate	.29	.25	.19
212003	74ACT32N	DIP-14	Quad 2-input OR gate	*.15	\$.12	\$.12
212011	74ACT74N	DIP-14	Dual D-type positive edge trig flip-flop	*.19	\$.17	\$.17
238730	74AC139N	DIP-16	Dual 2 to 4 decoder/demux	.25	.22	.17
238764	74AC157N	DIP-16	Quad 2-input multiplexer	.49	.39	.35
239054	74ACT174N	DIP-16	Hex D-type flip-flop	.39	.35	.29

* Order in multiples of 10

74ALS Series

Please Note: Manufacturer may vary

*Web Code: AFE

Part No.	Cross Ref. No.	Pkg.	Description	1	10	100
245294	74ALS00AN	DIP-14	Quad 2-input NAND gate	\$.25	\$.22	\$.19
43959	74ALS02N	DIP-14	Quad 2-input NOR gate	.25	.22	.19
245307	74ALS04BN	DIP-14	Hex inverters	.25	.22	.19
44134	74ALS32N	DIP-14	Quad 2-input OR gate	.25	.22	.19
245892	74ALS74AN	DIP-14	Dual D-pos. edge-trig. flip-flop	.35	.25	.22
310295	74ALS244AM	SOIC-20	Octal buffer/driver w/ 3-st.	.35	.25	.22

74C Series

*Web Code: RAG

Part No.	*Mfr.	Cross Ref.	Pkg.	Description	1	10	100
44222	+	74C00N	DIP-14	Quad 2-input NAND gate	\$1.15	\$.95	\$.69
44231	+	74C04N	DIP-14	Hex inverter (CD4069)	1.15	.95	.69
44257	+	74C14N	DIP-14	Hex inverter Schmitt trig. (CD40106)	.59	.49	.39
44361	+	74C221N	DIP-16	Dual monostable multivibrator	3.75	3.15	2.49
44396	+	74C373N	DIP-20	Octal D-type flip-flop w/ clear 3-st.	2.95	2.49	2.15
44521	+	74C912N	DIP-28	6-digit BCD display contr./driver	4.95	4.49	3.95
871869	FSC	MM74C922N	DIP-20	16-key encoder	5.95	5.49	5.25
44564	+	74C922N	DIP-18	16-key keyboard encoder	5.49	5.25	4.95
44572	+	74C923N	DIP-20	20-key keyboard encoder	4.95	4.25	3.95
44599	+	74C926N	DIP-18	4-digit CTR w/ mux. D-seg. driver	8.75	7.95	7.75

74F Series

Please Note: Manufacturer may vary

*Web Code: CEN

Part No.	Cross Ref.	Pkg.	Description	1	10	100
286993	74F02N	DIP-14	Quad 2-input NOR gate	\$.29	\$.25	\$.22
287005	74F04N	DIP-14	Hex inverter	.35	.29	.25
287013	74F08N	DIP-14	Quad 2-input AND gate	.19	.17	.15
44652	74F10N	DIP-14	Triple 3-input NAND gate	.35	.29	.25
111641	74F11N	DIP-14	Triple 3-input AND gate	.29	.25	.22
287654	74F14D	SOIC-14	Hex inverter w/ Schmitt trigger	.25	.22	.19
287021	74F14N	DIP-14	Hex inverter w/ Schmitt trigger	.25	.22	.19
245121	74F30N	DIP-14	8-input NAND gate	.35	.29	.25
287638	74F32D	SOIC-14	Quad 2-input OR gate	.19	.17	.15
287048	74F32N	DIP-14	Quad 2-input OR gate	.35	.29	.25
245139	74F38N	DIP-14	Quad 2-input NAND gate (O.C.)	.29	.25	.22
287620	74F74D	SOIC-14	Dual D-type flip-flop	.19	.17	.15
287056	74F74N	DIP-14	Dual D-type flip-flop	.25	.22	.19

Continued on next page

7400 Series IC Kit

Includes: 20-drawer component cabinet (319600), 20 clear plastic drawers (319601), 20 clear dividers (319611), pg 155 and 30 adhesive labels for drawers to identify parts in kit

10 each: 7402, 7405, 7408, 7410, 7414, 7416, 7417, 7420, 7430, 7432, 7438, 7447, 7470, 7485, 74107, 74121, 74123, 74132, 74151, 74153, 74157, 74160, 74174, 74175, 74279

20 each: 7400, 7404, 7406, 7407, 7474



SAVE \$141

Part No.	Description	Wt. (lbs.)	1	10
84953	350 pcs. 7400 IC kit	6.2	\$199.95	\$179.95

* FSC = Fairchild Semiconductor | TI = Texas Instruments | + Manufacturer Varies

*For Complete Specs & Additional Product Listings Search www.Jameco.com/More and Enter Web Code Listed Above



Order by Phone 24/7 at 1-800-831-4242 or Online at www.Jameco.com