





Dimensions in mm



Test Specification according to Standard UL 248-1,14

Electrical Characteristic

Rated Current	1.0 In	1.35 In	2 In
In	Min.	Max.	Max.
100mA-30A	4 h	3600 S	120 S

Rated Current	Breaking capacity	Rated Voltage	MFG52/-P-PA-PR		
			UL	SP	JET
100mA	@125V/AC 10KA @250V/AC 35A	125V/250V	○	○	
125mA		125V/250V	○	○	
160mA		125V/250V	○	○	
200mA		125V/250V	○	○	
250mA		125V/250V	○	○	
300mA		125V/250V	○	○	
315mA		125V/250V	○	○	
400mA		125V/250V	○	○	
500mA		125V/250V	○	○	
600mA		125V/250V	○	○	
630mA		125V/250V	○	○	
700mA		125V/250V	○	○	
800mA		125V/250V	○	○	
1A		125V/250V	○	○	○
1.25A		125V/250V	○	○	○
1.5A		125V/250V	○	○	○
1.6A	125V/250V	○	○	○	
2A	@125V/AC 10KA @250V/AC 100A	125V/250V	○	○	○
2.5A	125V/250V	○	○	○	
3A	125V/250V	○	○	○	
3.15A	125V/250V	○	○	○	
3.5A	125V/250V	○	○	○	
4A	@125V/AC 10KA @250V/AC 200A	125V/250V	○	○	○
5A		125V/250V	○	○	○
6A		125V/250V	○	○	○
6.3A		125V/250V	○	○	○
7A		125V/250V	○	○	○
8A		125V/250V	○	○	○
* 10A		125V/250V	○	○	○
12A		@32V/AC 1000A	32V		
13A	32V				
15A	32V				
16A	32V				
20A	32V				
25A	32V				
30A	32V				

GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO. 103908	GOLDSUN NO. MFG52A1.000N
Description FUSE,FAST ACTING, 250V 1A 5mmx20mm	
UNIT: mm	SCALE: SHEET 1 OF 1
CAS No: ERN No:	Rev. 1