

ADDA USA
DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
80 X 80 X 15	AD0805MS-D71	S	5	0.24	1.20	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0805HS-D70	S	5	0.40	2.00	3200	29.9	0.129	33.4	63	0	CE	200	32.34
80 X 80 X 15	AD0805HS-D71	S	5	0.43	2.15	3200	29.9	0.129	31.4	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812LX-D70	HYPRO	12	0.09	1.08	2000	20.0	0.050	19.6	63	0	UL,CUL,TUV,CE	200	32.24
80 X 80 X 15	AD0812MX-D70	HYPRO	12	0.12	1.44	2440	22.4	0.083	26.0	63	0,6	UL,CUL,TUV,CE		
80 X 80 X 15	AD0812MX-D71	HYPRO	12	0.15	1.80	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MX-D73	HYPRO	12	0.15	1.80	2440	22.4	0.083	26.0	63	3	CE		
80 X 80 X 15	AD0812HX-D70	HYPRO	12	0.18	2.16	3200	29.9	0.129	33.4	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HX-D71	HYPRO	12	0.19	2.28	3200	28.0	0.107	28.1	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HX-D73	HYPRO	12	0.19	2.28	3200	28.0	0.107	28.1	63	3	CE	200	32.34
80 X 80 X 15	AD0812LB-D70	BALL	12	0.09	1.08	2000	20.0	0.050	19.6	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812LB-D73	BALL	12	0.09	1.08	2000	20.0	0.050	19.6	63	3	CE	200	32.34
80 X 80 X 15	AD0812MB-D70	BALL	12	0.12	1.44	2440	22.4	0.083	26.0	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MB-D71	BALL	12	0.15	1.80	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MB-D73	BALL	12	0.15	1.80	2440	22.4	0.083	26.0	63	3	CE	200	32.34
80 X 80 X 15	AD0812MB-D74	BALL	12	0.08	0.96	2440	22.1	0.087	25.4	63	4	UL,CUL,CE	200	32.34
80 X 80 X 15	AD0812HB-D70	BALL	12	0.18	2.16	3200	29.9	0.129	33.4	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HB-D71	BALL	12	0.19	2.16	3200	29.9	0.129	33.4	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HB-D72	BALL	12	0.19	2.16	3200	29.9	0.129	33.4	63	2	CE	200	32.34
80 X 80 X 15	AD0812HB-D73	BALL	12	0.19	2.16	3200	29.9	0.129	33.4	63	3	TUV,CE	200	32.34
80 X 80 X 15	AD0812HB-D74	BALL	12	0.17	2.16	3200	29.9	0.129	33.4	63	4	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812LS-D70	S	12	0.09	1.08	2000	20.0	0.050	19.6	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MS-D70	S	12	0.12	1.44	2440	22.4	0.083	26.0	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MS-D71	S	12	0.15	1.80	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MS-D73	S	12	0.15	1.80	2440	22.4	0.083	26.0	63	3	CE	200	32.34
80 X 80 X 15	AD0812HS-D70	S	12	0.18	2.16	3200	29.9	0.129	33.4	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HS-D71	S	12	0.19	2.28	3200	29.9	0.129	33.4	63	1	UL,CUL,CE	200	32.34
80 X 80 X 15	AD0812HS-D73	S	12	0.18	2.16	3200	29.9	0.129	33.4	63	3	CE	200	32.34
80 X 80 X 15	AD0824MX-D71	HYPRO	24	0.10	2.40	2440	21.0	0.070	27.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824HX-D71	HYPRO	24	0.13	3.12	3200	29.0	0.116	33.5	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824MB-D71	BALL	24	0.10	2.40	2440	21.0	0.070	27.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824HB-D70	BALL	24	0.13	3.12	3200	32.0	0.131	33.6	63	0	CE	200	32.34
80 X 80 X 15	AD0824HB-D71	BALL	24	0.13	3.12	3200	32.0	0.131	33.6	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824MS-D70	S	24	0.08	1.92	2440	22.4	0.083	26.0	63	0	CE	200	32.34
80 X 80 X 15	AD0824MS-D71	S	24	0.10	2.40	2440	21.0	0.070	27.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0824HS-D71	S	24	0.13	3.12	3200	29.0	0.116	33.5	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 20	AD0805HX-C72	HYPRO	5	0.32	3.84	3010	27.3	0.128	31.4	70	2	CE	200	35.20
80 X 80 X 20	AD0805HB-C70	BALL	5	0.43	5.16	3010	27.3	0.128	31.4	70	0	CE	200	35.20
80 X 80 X 20	AD0805HB-C71	BALL	5	0.32	3.84	3010	27.3	0.128	31.4	70	1,2	CE	200	35.20
80 X 80 X 20	AD0812LX-C70	HYPRO	12	0.10	1.20	2000	18.9	0.059	17.7	70	0	CE	200	35.20

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED