

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 137358



953M Series Relay

FEATURES

- UL, CE, TUV & CQC safety approval.
- Single contact 953 series relay offers 30A switching capacity for various kinds of applications.
- Up to 30A switching in SPDT-NO and 20A switching in SPDT-NC arrangement.
- Meets UL 508 & UL 873 spacing.
- Nominal power 930mW.
- Operating power 520mW.
- Optional flanged case for panel mounting.



UL FILE NO: E162117/E188367
 TUV FILE NO: R 3-02158203
 CQC FILE NO: CQC02001001783
 CEDECLARATION OF CONFORMITY


CONTACT RATINGS

- Contact Arrangement..... 1 Form A (SPST-NO)
1 Form B (SPST-NC)
1 Form C (SPDT)
- Max. Switching Power
 1Form A.....7500VA 600W
 1 Form B5000VA 300W
 1Form C.....7500VA 600W
- Max. Switching Voltage.....277VAC 30VDC
- Max. Switching Current
 1Form A.....30A
 1Form B.....20A
 1Form C.....30A
- Contact Resistance..... $\leq 50m\Omega$
- Resistive Load
 1Form A.....30A/250VAC 20A/277VAC 30VDC
 1Form B..... 20A/240VAC 15A/277VAC 10A/30VDC
 1Form C..... NO: 30A/240VAC 20A/277VAC 30VDC
NC: 20A/240VAC 15A/277VAC 10A/30VDC
- Contact Material.....Ag Alloy


CHARACTERISTICS

- Electrical Life..... 1×10^5
- Mechanical Life..... 1×10^7
- Initial Insulation Resistance.....Min. 500M Ω 500VDC
- Contact Resistance (Initial)..... $\leq 50m\Omega$
- Operate Time..... $\leq 15ms$
- Release Time..... $\leq 15ms$
- Initial Dielectric Strength.....50/60Hz 1500VAC 1 min. (between open contacts)
50/60Hz 2500VAC 1 min. (between contacts and coil)


953M Referential Data Timing



Coil Temperature Rise



Life Curves



● Vibration Resistance

.....Malfunction: 10 to 55Hz at Double Amplitude of 1.5mm

.....Destructive: 10 to 55Hz at Double Amplitude of 1.5mm

● Shock Resistance

.....Malfunction: 10G (11ms) / Destructive: 100G (6ms)

● Ambient Temperature.....-55°C~+85°C

● Relative Humidity.....85% at 40°C

● Unit Weight.....Approx. 34g

ORDERING INFORMATION

953 - 1C - 12 D M F
 1 2 3 4 5 6

Type of Insulation.....Nil = Class ; F = Class F

Enclosure Style.....M = Outline Connect Type

Coil Type.....D: DC ; A: AC

Coil Voltage.....DC: 5~48V ; AC: 6~277V

Contact Arrangement.....1A = 1 Form A (SPST-NO)

.....1B = 1 Form B (SPST-NC)

.....1C = 1 Form C (SPDT)


Model Number.....953

COIL RATINGS(at 20°C)

COIL TYPE	Coil Nominal Voltage (V)	Coil Resistance ($\Omega \pm 10\%$)	Pick-Up Voltage (V) \leq	Drop-Out Voltage (V) \geq	Nominal Current (mA)
DC Coils	5	27	3.75	0.5	185
	6	40	4.5	0.6	150
	9	97	6.75	0.9	93
	12	155	9	1.2	77
	18	380	13.5	1.8	47
	24	660	18	2.4	36
	36	1440	27	3.6	25
	48	2560	36	4.8	19
AC Coils	6	10	5.1	0.6	
	12	43	10.2	1.2	
	24	160	20.4	2.4	
	110	3160	93.5	11	
	220	13490	187	22	
	277	19900	235.4	27.7	

* Max Continuous Voltage at 20°C: 110% of Coil Nominal Voltage.

OUTLINE DIMENSIONS



REMARK: Tolerance of outline dimensions: $\pm 0.2(.008)$.

UNIT: mm (inch)

SAFETY APPROVAL

I UL APPROVAL

Contact Rating	1 Form A (SPST-NO)	1 Form B (SPST-NC)	1 Form C (SPDT)		
			NO	NC	
Resistive Load	20A / 277VAC 19.8A / 277VAC	20A/30VDC 30A / 240VAC	15A / 277VAC 10A / 30VDC	20A / 277VAC 20A / 30VDC	15A / 277VAC 10A / 30VDC
General Purpose Load	10A / 277VAC	8A / 277VAC	10A / 277VAC	10A / 277VAC	8A / 277VAC
Motor Load (Cos ϕ : 0.4 ~ 0.5)	2HP / 250VAC 1HP / 125VAC	1/2HP / 250VAC 1/4HP / 125VAC	2HP / 250VAC 1HP / 125VAC	2HP / 250VAC 1HP / 125VAC	1/2HP / 250VAC 1/4HP / 125VAC
Horse Power	FLA 10.3 LRA 61.8 / 277VAC FLA 11.2 LRA 67.2 / 240VAC FLA 12 / 250VAC FLA 16 LRA 96 / 240VAC FLA 16 LRA 96 / 120VAC FLA 16 / 125VAC	FLA 4.9 / 250VAC FLA 5.8 / 125VAC	FLA 12 / 250VAC FLA 16 / 125VAC	FLA 12 / 250VAC FLA 16 / 125VAC	FLA 4.9 / 250VAC FLA 5.8 / 125VAC
Ballast	20A / 277VAC		20A / 277VAC		

I TUV APPROVAL

Contact Rating	1 Form A (SPST-NO)	1 Form B (SPST-NC)	1 Form C (SPDT)	
			NO	NC
Resistive Load	30A / 250VAC 20A / 30VDC	15A / 250VAC 15A / 30VDC	20A / 250VAC 20A / 30VDC	10A / 250VAC 10A / 30VDC
Inductive Load (Cos ϕ : 0.4, L/R: 7ms)	15A / 250VAC 15A / 30 VDC	8A / 250VAC 8A / 30VDC	10A / 250VAC 10A / 30VDC	8A / 250VAC 8A / 30VDC
Motor Load (Cos ϕ : 0.6)	2HP / 250VAC 1HP / 125VAC	1/2HP / 250VAC 1/4HP / 125VAC	2HP / 250VAC 1HP / 125VAC	1/2HP / 250VAC 1/4HP / 125VAC
Pilot Duty Load (Rate 6000 Operations)	720VA / 240VAC 800VA / 125VAC	360VA / 240VAC 290VA / 125VAC	470VA / 240VAC 470VA / 125VAC	360VA / 240VAC 290VA / 125VAC

I CQC APPROVAL

Contact Rating	1 Form A (SPST-NO)	1 Form B (SPST-NC)	1 Form C (SPDT)	
			NO	NC
Resistive Load	30A / 240VAC	20A / 240VAC	30A / 240VAC	20A / 240VAC

I CE DECLARATION OF COFORMITY

In conformity with the Low Voltage Directive 73/23/EEC

Test Report No.: E9967734E02 (TUV)

Test Specification: EN61810-1 ; EN61810-5 ; EN60255-23