


T-1 3/4 Wire Terminal



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Shape	Remark
2158	3.0	.015	.004	10,000	C-6	
2200	5.0	.060	.050	100,000	C-2R	
3151	5.0	.060	.015	5,000	C-2R	
2203	5.0	.115	.150	40,000	C-2R	
8784	5.0	.190	.450	1,000	C-2R	
1730	6.0	.040	.030	100,000	C-2R	
8664	6.0	.200	.100	50,000	C-2F	
	6.0	.200	.340	1,000	C-2R	
1784	6.0	.200	.600	1,000	C-2R	
1739	6.3	.075	.220	500	C-6	
8350	6.3	.150	.450	3,000	C-2R	
2181	6.3	.200	.400	50,000	C-2F	
2112	6.3	.200	.550	3,000	C-2R	
1869	10.0	.014	.002	10,000	C-2F	
2174	12.0	.040	.120	10,000	C-2F	
	12.0~14.0	.050	.130	5,000	C-2F	
	14.0	.040	.150	10,000	C-2F	
2182	14.0	.080	.300	40,000	C-2F	P/N 141073
1705	14.0	.080	.500	750	C-2F	
2162	14.0	.100	.500	10,000	C-2F	
	14.0	.100	.700	500	C-2F	
2102	18.0	.040	.150	10,000	C-2F	
2176	24.0	.050	.500	1,000	C-2F	
6033	28.0	.024	.150	4,000	C-2F	
2185	28.0	.040	.150	10,000	C-2F	
2187	28.0	.040	.300	25,000	C-2F	
1764	28.0	.040	.340	7,000	C-2F	
	28.0	.050	.350	10,000	C-2F	
476	28.0	.060	.340	25,000	C-2F	

NOTE:

1. LAMPS SHELL BE CAPABLE OF OPERATION AND STORAGE AT TEMPERATURES FROM -40 °C TO +85 °C WITHOUT DEGRADATION.
2. DIMENSIONS ARE IN MILLIMETERS.
3. LAMP LEADS TO BE TIN PLATED.