

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 1561395

**Applications**


- High frequency DC-DC converters
- UPS and Motor Control

HEXFET® Power MOSFET

**Benefits**

- Low Gate-to-Drain Charge to Reduce Switching Losses
- Fully Characterized Capacitance Including Effective C<sub>OSS</sub> to Simplify Design, (See App. Note AN1001)
- Fully Characterized Avalanche Voltage and Current
- Typical R<sub>DS(on)</sub> = 12mΩ

|                        |                               |                        |
|------------------------|-------------------------------|------------------------|
| <b>V<sub>DSS</sub></b> | <b>R<sub>DS(on)</sub> max</b> | <b>I<sub>D</sub></b>   |
| <b>100V</b>            | <b>15mΩ</b>                   | <b>80A<sup>Ⓞ</sup></b> |



**Absolute Maximum Ratings**

|   | Parameter                                       | Max.            | Units       |
|---|---|-----------------|-------------|
| I <sub>D</sub> @ T <sub>C</sub> = 25°C  | Continuous Drain Current, V <sub>GS</sub> @ 10V | 80 <sup>Ⓞ</sup> | A           |
| I <sub>D</sub> @ T <sub>C</sub> = 100°C | Continuous Drain Current, V <sub>GS</sub> @ 10V | 57              |             |
| I <sub>DM</sub>                         | Pulsed Drain Current <sup>①</sup>               | 320             |             |
| P <sub>D</sub> @ T <sub>C</sub> = 25°C  | Power Dissipation                               | 260             | W           |
|   | Linear Derating Factor                          | 1.8             | W/°C        |
| V <sub>GS</sub>                         | Gate-to-Source Voltage                          | ± 20            | V           |
| dv/dt                                   | Peak Diode Recovery dv/dt <sup>③</sup>          | 16              | V/ns        |
| T <sub>J</sub>                          | Operating Junction and                          | -55 to + 175    | °C          |
| T <sub>STG</sub>                        | Storage Temperature Range                       |                 |             |
|   | Soldering Temperature, for 10 seconds           |                 |             |
|   | Mounting torque, 6-32 or M3 screw               | 1.1(10)         | N•m (lb•in) |

**Thermal Resistance**

|                  | Parameter                           | Typ. | Max. | Units |
|------------------|-------------------------------------|------|------|-------|
| R <sub>θJC</sub> | Junction-to-Case                    | —    | 0.57 | °C/W  |
| R <sub>θCS</sub> | Case-to-Sink, Flat, Greased Surface | 0.50 | —    |       |
| R <sub>θJA</sub> | Junction-to-Ambient                 | —    | 62   |       |

Notes <sup>①</sup> through <sup>Ⓞ</sup> are on page 8  
[www.irf.com](http://www.irf.com)

# IRF8010

International  
IR Rectifier

## Static @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

|                                 | Parameter                            | Min. | Typ. | Max. | Units | Conditions  |
|---------------------------------|--------------------------------------|------|------|------|-------|---|
| $V_{(BR)DSS}$                   | Drain-to-Source Breakdown Voltage    | 100  | —    | —    | V     | $V_{GS} = 0V, I_D = 250\mu A$                         |
| $\Delta V_{(BR)DSS}/\Delta T_J$ | Breakdown Voltage Temp. Coefficient  | —    | 0.11 | —    | V/°C  | Reference to $25^\circ\text{C}, I_D = 1\text{mA}$     |
| $R_{DS(on)}$                    | Static Drain-to-Source On-Resistance | —    | 12   | 15   | mΩ    | $V_{GS} = 10V, I_D = 45A$ ④                           |
| $V_{GS(th)}$                    | Gate Threshold Voltage               | 2.0  | —    | 4.0  | V     | $V_{DS} = V_{GS}, I_D = 250\mu A$                     |
| $I_{DSS}$                       | Drain-to-Source Leakage Current      | —    | —    | 20   | μA    | $V_{DS} = 100V, V_{GS} = 0V$                          |
|                                 |                                      | —    | —    | 250  |       | $V_{DS} = 100V, V_{GS} = 0V, T_J = 125^\circ\text{C}$ |
| $I_{GSS}$                       | Gate-to-Source Forward Leakage       | —    | —    | 200  | nA    | $V_{GS} = 20V$  |
|                                 | Gate-to-Source Reverse Leakage       | —    | —    | -200 |       | $V_{GS} = -20V$                                       |


## Dynamic @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

|                 | Parameter                       | Min. | Typ. | Max. | Units | Conditions                                      |
|-----------------|---------------------------------|------|------|------|-------|---|
| gfs             | Forward Transconductance        | 82   | —    | —    | V     | $V_{DS} = 25V, I_D = 45A$                       |
| $Q_g$           | Total Gate Charge               | —    | 81   | 120  | nC    | $I_D = 80A$                                     |
| $Q_{gs}$        | Gate-to-Source Charge           | —    | 22   | —    |       | $V_{DS} = 80V$                                  |
| $Q_{gd}$        | Gate-to-Drain ("Miller") Charge | —    | 26   | —    |       | $V_{GS} = 10V$ ④                                |
| $t_{d(on)}$     | Turn-On Delay Time              | —    | 15   | —    | ns    | $V_{DD} = 50V$                                  |
| $t_r$           | Rise Time                       | —    | 130  | —    |       | $I_D = 80A$                                     |
| $t_{d(off)}$    | Turn-Off Delay Time             | —    | 61   | —    |       | $R_G = 39\Omega$                                |
| $t_f$           | Fall Time                       | —    | 120  | —    |       | $V_{GS} = 10V$ ④                                |
| $C_{iss}$       | Input Capacitance               | —    | 3830 | —    | pF    | $V_{GS} = 0V$                                   |
| $C_{oss}$       | Output Capacitance              | —    | 480  | —    |       | $V_{DS} = 25V$                                  |
| $C_{rss}$       | Reverse Transfer Capacitance    | —    | 59   | —    |       | $f = 1.0\text{MHz}$                             |
| $C_{oss}$       | Output Capacitance              | —    | 3830 | —    |       | $V_{GS} = 0V, V_{DS} = 1.0V, f = 1.0\text{MHz}$ |
| $C_{oss}$       | Output Capacitance              | —    | 280  | —    |       | $V_{GS} = 0V, V_{DS} = 80V, f = 1.0\text{MHz}$  |
| $C_{oss\ eff.}$ | Effective Output Capacitance    | —    | 530  | —    |       | $V_{GS} = 0V, V_{DS} = 0V \text{ to } 80V$ ③    |

## Avalanche Characteristics

|          | Parameter                        | Typ. | Max. | Units |
|----------|----------------------------------|------|------|-------|
| $E_{AS}$ | Single Pulse Avalanche Energy ②⑥ | —    | 310  | mJ    |
| $I_{AR}$ | Avalanche Current ①              | —    | 45   | A     |
| $E_{AR}$ | Repetitive Avalanche Energy ①    | —    | 26   | mJ    |

## Diode Characteristics

|          | Parameter                                 | Min.   | Typ. | Max. | Units | Conditions  |
|----------|---|--|------|------|-------|---|
| $I_S$    | Continuous Source Current<br>(Body Diode) | —  | —    | 80   | A     | MOSFET symbol<br>showing the<br>integral reverse<br>p-n junction diode.               |
| $I_{SM}$ | Pulsed Source Current<br>(Body Diode) ①⑥  | —  | —    | 320  |       |  |
| $V_{SD}$ | Diode Forward Voltage                     | —  | —    | 1.3  | V     | $T_J = 25^\circ\text{C}, I_S = 80A, V_{GS} = 0V$ ④                                    |
| $t_{rr}$ | Reverse Recovery Time                     | —  | 99   | 150  | ns    | $T_J = 150^\circ\text{C}, I_F = 80A, V_{DD} = 50V$                                    |
| $Q_{rr}$ | Reverse Recovery Charge                   | —  | 460  | 700  | nC    | $di/dt = 100A/\mu s$ ④  |
| $t_{on}$ | Forward Turn-On Time                      | Intrinsic turn-on time is negligible (turn-on is dominated by LS+LD) |      |      |       |   |




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics




Fig 3. Typical Transfer Characteristics







Fig 4. Normalized On-Resistance Vs. Temperature




**Fig 5.** Typical Capacitance Vs. Drain-to-Source Voltage



**Fig 6.** Typical Gate Charge Vs. Gate-to-Source Voltage



**Fig 7.** Typical Source-Drain Diode Forward Voltage



**Fig 8.** Maximum Safe Operating Area




Fig 9. Maximum Drain Current Vs. Case Temperature




Fig 10a. Switching Time Test Circuit




Fig 10b. Switching Time Waveforms







Fig 11. Maximum Effective Transient Thermal Impedance, Junction-to-Case




**Fig 12a.** Unclamped Inductive Test Circuit




**Fig 12b.** Unclamped Inductive Waveforms



**Fig 13a.** Basic Gate Charge Waveform





**Fig 12c.** Maximum Avalanche Energy Vs. Drain Current



**Fig 13b.** Gate Charge Test Circuit

**Peak Diode Recovery dv/dt Test Circuit**



\*  $V_{GS} = 5V$  for Logic Level Devices

**Fig 14.** For N-Channel HEXFET® Power MOSFETs




# IRF8010

## TO-220AB Package Outline

Dimensions are shown in millimeters (inches)

International  
**IR** Rectifier




**NOTES:**

- 1 DIMENSIONING & TOLERANCING PER ANSI Y14.5M, 1982.
- 2 CONTROLLING DIMENSION : INCH
- 3 OUTLINE CONFORMS TO JEDEC OUTLINE TO-220AB.
- 4 HEATSINK & LEAD MEASUREMENTS DO NOT INCLUDE BURRS.

## TO-220AB Part Marking Information

EXAMPLE : THIS IS AN IRF1010  
WITH ASSEMBLY  
LOT CODE 9B1M



**Notes:**

- ① Repetitive rating; pulse width limited by max. junction temperature.
- ② Starting  $T_J = 25^\circ\text{C}$ ,  $L = 0.31\text{mH}$ ,  $R_G = 25\Omega$ ,  $I_{AS} = 45\text{A}$ .
- ③  $I_{SD} \leq 45\text{A}$ ,  $di/dt \leq 110\text{A}/\mu\text{s}$ ,  $V_{DD} \leq V_{(BR)DSS}$ ,  $T_J \leq 175^\circ\text{C}$ .
- ④ Pulse width  $\leq 300\mu\text{s}$ ; duty cycle  $\leq 2\%$ .
- ⑤  $C_{OSS}$  eff. is a fixed capacitance that gives the same charging time as  $C_{OSS}$  while  $V_{DS}$  is rising from 0 to 80%  $V_{DSS}$ .
- ⑥ Calculated continuous current based on maximum allowable junction temperature. Package limitation current is 75A.

**TO-220 package is not recommended for Surface Mount Application.**

Data and specifications subject to change without notice.  
This product has been designed and qualified for the Industrial market.  
Qualification Standards can be found on IR's Web site.

International  
**IR** Rectifier

**IR WORLD HEADQUARTERS:** 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105  
TAC Fax: (310) 252-7903

Visit us at [www.irf.com](http://www.irf.com) for sales contact information.08/02

[www.irf.com](http://www.irf.com)

This datasheet has been download from:

[www.datasheetcatalog.com](http://www.datasheetcatalog.com)

Datasheets for electronics components.