


# NACE331M25V8X10.5TR15F

Surface Mount Aluminum Electrolytic, 330 uF, 20% Tol, 25V@85C, 8X10.5 Case



## Dimensional Data (mm)

ID	Dimensions	Tolerance
D:	8	+/-0.5
L:	10.5	+0
A:	8.3	+/-0.2
B:	8.3	+/-0.2
C:	9	+/-0.4
W:	0.85	+0.15/-0.6
E:	2.9	+/-0.2
P:	3.2	+/-0.2
F:	0.3	max

## Specifications

RoHS:	Yes
Capacitance:	330 uF
Tolerance:	20%
Voltage DC @ 85C:	25V
Life @ 65C:	8000
Life @ 85C:	2000 h
Package Quantity:	500
Packaging:	T&R, 15 in. (26 mm)
Leakage:	82 uA
Dissipation Factor:	0.16%
Impedance Ratio 25:	2.0
Impedance Ratio 40:	4.0
ESR 120:	0.81 mOhm
Ripple 120 25C:	310 A
Ripple 120 85C:	310 A
Ripple 1K 85C:	341 A
Ripple 10K 85C:	372 A
Ripple 100K 85C:	403 A

