



#### ■ Features :

- AC input active surge current limiting
- AC input range selected by switch
- Protections: Short circuit/Over load/Over voltage/Over temperature
- Forced air cooling by built-in DC ball bearing fan
- High power density 7.3w/in<sup>3</sup>
- With DC\_OK signal output
- Built-in remote ON-OFF control
- Built-in remote sense function
- UL / CUL approved
- Low cost
- 2 years warranty




#### SPECIFICATION

MODEL	SE-1000-5	SE-1000-9	SE-1000-12	SE-1000-15	SE-1000-24	SE-1000-48	
OUTPUT	DC VOLTAGE	5V	9V	12V	15V	24V	48V
	RATED CURRENT	150A	100A	83.3A	66.7A	41.7A	20.8A
	CURRENT RANGE	0 ~ 150A	0 ~ 100A	0 ~ 83.3A	0 ~ 66.7A	0 ~ 41.7A	0 ~ 20.8A
	RATED POWER	750W	900W	999.6W	1000.5W	1000.8W	998.4W
	RIPPLE & NOISE (max.) Note.2	150mVp-p	150mVp-p	150mVp-p	150mVp-p	200mVp-p	200mVp-p
	VOLTAGE ADJ. RANGE	3.3 ~ 5.5V	7.5 ~ 10V	10 ~ 13.5V	13.5 ~ 16.5V	22 ~ 27.5V	43 ~ 56V
	VOLTAGE TOLERANCE Note.3	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%
	LINE REGULATION	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%
	LOAD REGULATION	±1.0%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%
	SETUP, RISE TIME	300ms, 50ms/230VAC      300ms, 50ms/115VAC at full load					
HOLD TIME (Typ.)	20ms/230VAC      15ms/115VAC at full load						
INPUT	VOLTAGE RANGE	90 ~ 132VAC / 180 ~ 264VAC selected by TB2      254 ~ 370VDC					
	FREQUENCY RANGE	47 ~ 63Hz					
	EFFICIENCY (Typ.)	81%	84%	85%	86%	88%	89%
	AC CURRENT (Typ.)	17.5A/115VAC      10A/230VAC					
	INRUSH CURRENT (Typ.)	35A/115VAC      55A/230VAC					
	LEAKAGE CURRENT	<2.5mA / 240VAC					
PROTECTION	OVER LOAD	105 ~ 125% rated output power Protection type : Shut down o/p voltage, re-power on to recover					
	OVER VOLTAGE	5.75 ~ 6.3V	10.4 ~ 12.2V	13.8 ~ 16.2V	18 ~ 21V	28 ~ 32.4V	57.6 ~ 67.2V
	OVER TEMPERATURE	70°C ±5°C (TSW1) Detect on heatsink of power transistor Protection type : Shut down o/p voltage, recovers automatically after temperature goes down					
FUNCTION	DC_OK SIGNAL	PSU turn on: 3.3V ~ 5.6V      PUS turn off: 0 ~ 1V					
	REMOTE CONTROL	RC+/RC-: 0 ~ 0.8V power on; 4 ~ 10V power off					
ENVIRONMENT	WORKING TEMP.	-20 ~ +60°C (Refer to output load derating curve)					
	WORKING HUMIDITY	20 ~ 90% RH non-condensing					
	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH					
	TEMP. COEFFICIENT	±0.05%/°C (0 ~ 50°C)					
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes					
SAFETY & EMC	SAFETY STANDARDS	UL60950-1 Approved					
	WITHSTAND VOLTAGE	I/P-O/P: 3KVAC    I/P-FG: 1.5KVAC    O/P-FG: 0.5KVAC					
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG: 100M Ohms/500VDC					
OTHERS	MTBF	251.6K hrs min.    MIL-HDBK-217F (25°C)					
	DIMENSION	278*127*63.5mm (L*W*H)					
	PACKING	2.5Kg; 6pcs/16Kg/1.38CUFT					
NOTE	<p>1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.</p> <p>2. Ripple &amp; noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf &amp; 47uf parallel capacitor.</p> <p>3. Tolerance : includes set up tolerance, line regulation and load regulation.</p>						

#### Mechanical Specification

Case No. 935B Unit:mm



TB1: AC input terminal

Pin No.	Assignment
1	AC/L
2	AC/N
3	FG


TB2: 110/220V Change

Pin No.	110V	220V
1	Short	Open
2		


Control Pin (CN3) : JST B6B-XH or equivalent

Pin No.	Assignment	Pin No.	Assignment	Mating Housing	Terminal
1	DC_OK Signal	4	+S	JST XHP or equivalent	JST SXH-001T or equivalent
2	DC_OK GND	5	RC-		
3	-S	6	RC+		


#### Block Diagram



#### Derating Curve



#### Static Characteristics



### ■ Mechanical Specification


#### DC\_OK Signal

DC\_OK Signal is the voltage difference between "DC\_OK" and "G" pin output


DC\_OK Signal is a TTL level signal

PSU turn on: 3.3 ~ 5.6V

PSU turn off: 0 ~ 1V




#### Remote Sensing



#### Remote Control

Between RC+ and RC-	Output
SW OFF(0 ~ 0.8V)	ON
SW ON(4 ~ 10V)	OFF



MODEL : SE-1000-5

### OUTPUT FUNCTION TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	RIPPLE & NOISE	V1: 150 mVp-p (Max)	I/P: 230VAC O/P:FULL LOAD Ta:25°C	V1: 48 mVp-p (Max)	P
2	OUTPUT VOLTAGE ADJUST RANGE	CH1: 3.3V~ 5.5V	I/P: 230 VAC I/P: 115 VAC O/P:MIN LOAD Ta:25°C	3.11 V- 5.72 V/ 230 VAC 3.11 V- 5.72 V/ 115 VAC	P
3	OUTPUT VOLTAGE TOLERANCE	V1: 1 %- -1 % (Max)	I/P: 200 VAC / 264 VAC O/P:FULL/ MIN LOAD Ta:25°C	V1: 0.25 %- -0.25 %	P
4	LINE REGULATION	V1: 0.5 %- -0.5 % (Max)	I/P: 200VAC ~ 264 VAC O/P:FULL LOAD Ta:25°C	V1: 0.12 %- -0.12 %	P
5	LOAD REGULATION	V1: 1 %- -1 % (Max)	I/P: 230 VAC O/P:FULL ~MIN LOAD Ta:25°C	V1: 0.25 %- -0.25 %	P
6	SET UP TIME	230VAC: 1500 ms (Max) 115 VAC: 1500 ms (Max)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	230VAC/ 170 ms 115VAC/ 1008 ms	P
7	RISE TIME	230VAC: 50 ms (Max) 115VAC: 50 ms (Max)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	230VAC/ 21 ms 115VAC/ 23 ms	P
8	HOLD UP TIME	230VAC: 20 ms (TYP) 115VAC: 15 ms(TYP)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	230VAC/ 26.9 ms 115VAC/ 21 ms	P
9	OVER/UNDERSHOOT TEST	< ±5%	I/P: 230 VAC O/P:FULL LOAD Ta:25°C	TEST: <5 %	P
10	DYNAMIC LOAD	V1: 1000 mVp-p	I/P: 230 VAC O/P:FULL /Min LOAD 90%DUTY/1KHZ Ta:25°C	629 mVp-p	P

## INPUT FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	INPUT VOLTAGE RANGE	180VAC-264 VAC)	I/P:TESTING O/P:FULL LOAD Ta:25°C	141V-264V	P
			I/P: LOW-LINE-3V= 177 V HIGH-LINE+15%=300 V O/P:FULL/MIN LOAD ON: 30 Sec . OFF: 30 Sec 10MIN ( AC POWER ON/OFF NO DAMAGE )	TEST: OK	
2	INPUT FREQUENCY RANGE	47HZ -63 HZ NO DAMAGE OSC	I/P: 180VAC - 264 VAC O/P:FULL-MIN LOAD Ta:25°C	TEST: OK	P
3	EFFICIENCY	81 % (TYP)	I/P: 230 VAC O/P:FULL LOAD Ta:25°C	82 %	P
4	INPUT CURRENT	230V/ 10 A (TYP) 115V/ 17.5 A(TYP)	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	I = 8 A/ 230 VAC I = 13.7 A/ 115 VAC	P
5	INRUSH CURRENT	230V/ 55 A (TYP) 115V/ 35 A(TYP) COLD START	I/P: 230 VAC I/P: 115 VAC O/P:FULL LOAD Ta:25°C	I = 49 A/ 230 VAC I = 25 A/ 115 VAC	P
6	LEAKAGE CURRENT	< 2.5 mA / 240 VAC	I/P: 254 VAC O/P:Min LOAD Ta:25°C	L-FG: 1.4 mA N-FG: 1.4 mA	P

### PROTECTION FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	OVER LOAD PROTECTION	105 %- 125 %	I/P: 230 VAC I/P: 115 VAC O/P: TESTING Ta: 25°C	115 %/ 230 VAC 114 %/ 115 VAC Shunt down Re-power ON	P
2	OVER VOLTAGE PROTECTION	CH1: 5.75 V~ 6.3 V	I/P: 230 VAC I/P: 115 VAC O/P: MIN LOAD Ta: 25°C	5.86 V/ 230 VAC 5.86 V/ 115 VAC Shunt down Re- power ON	P
3	OVER TEMPERATURE PROTECTION	SPEC: TSW1: 70°C ± 5°C O.T.P. NO DAMAGE	I/P: 230 VAC O/P: FULL LOAD	O.T.P. Active Shut down o/p voltage , recovers automatically after temperature goes down	P
4	SHORT PROTECTION	SHORT EVERY OUTPUT 1 HOUR NO DAMAGE	I/P: 264 VAC O/P: FULL LOAD Ta: 25°C	NO DAMAGE Shunt down Re-power ON	P

### CONTROL FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	FAN LOCK TEST	POWER SUPPLY SHUT DOWN	I/P: 230 VAC O/P: FULL LOAD	OK	P
2	FAN SPEED CONTROL	-----	I/P: 230 VAC O/P: FULL LOAD Ta: 25°C	Fan Voltage= 12.15V	P
3	REMOTE CONTROL	Rc+ / Rc- 0V~ 0.8V POWER ON 4V~10V POWER OFF	I/P: 230 VAC O/P: FULL LOAD Ta: 25°C	0V ~ 2 V POWER ON 2.1V ~ 10 V POWER OFF	P
4	DC OK SIGNAL	POWER ON: 3.3V~5.6V POWER OFF: 0V~1V	I/P: 230 VAC O/P: FULL LOAD/NO LOAD Ta: 25°C	POWER ON: 5.2V POWER OFF: 0V	P
5	REMOTE SENSE	>0.25V	I/P: 230 VAC O/P: FULL LOAD Ta: 25°C	>0.25V	P

## ENVIRONMENT TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	TEMPERATURE RISE TEST	MODEL : SE-1000-5 1. ROOM AMBIENT BURN-IN : 14 HRS I/P: 230VAC O/P: FULL LOAD Ta= 27.1°C 2. HIGH AMBIENT BURN-IN : 2 HRS I/P: 230VAC O/P: FULL LOAD Ta= 51.2°C			P
2	OVER LOAD BURN-IN TEST	NO DAMAGE 1 HOUR ( MIN )	I/P: 230 VAC O/P: 114 % LOAD Ta:25°C	TEST : OK	P
3	LOW TEMPERATURE TURN ON TEST	TURN ON AFTER 2 HOUR	I/P: 230 VAC O/P: 100 % LOAD Ta= -20°C	TEST : OK	P
4	HIGH HUMIDITY HIGH TEMPERATURE HIGH VOLTAGE TURN ON TEST	AFTER 12 HOURS IN CHAMBER ON CONTROL 45°C NO DAMAGE	I/P: 272 VAC O/P:FULL LOAD Ta= 45 °C HUMIDITY= 95 %R.H	TEST : OK	P
5	TEMPERATURE COEFFICIENT	± 0.05 %(0-50°C)	I/P: 230 VAC O/P:FULL LOAD	± 0.02 %(0-50°C)	P
6	VIBRATION TEST	1 Carton & 1 Set (1) Waveform: Sine Wave (2) Frequency:10-500Hz (3) Sweep Time:10min/sweep cycle (4) Acceleration:2G (5) Test Time:1 hour in each axis (X.Y.Z) (6) Ta:25°C		TEST : OK	P

## M.T.B.F & LIFE CYCLE CALCULATION

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	CAPACITOR LIFE CYCLE	SUPPOSE C105 IS THE MOST CRITICAL COMPONENT I/P: 230VAC O/P:FULL LOAD Ta= 25 °C LIFE TIME= 500067 HRS I/P: 230VAC O/P:FULL LOAD Ta= 45 °C LIFE TIME= 140636 HRS			P
2	MTBF	MIL-HDBK-217F NOTICES2 PARTS COUNT TOTAL FAILURE RATE: 251.6K HRS			P
3	ORT (Ongoing Reliability test)	SE-1000-48:I/P : 230VAC O/P : 100% LOAD TA=45°C Sample=5pcs		TEST TIME=1176HRS	P



SAFETY TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	WITHSTAND VOLTAGE	I/P-O/P: 3 KVAC/min I/P-FG: 1.5 KVAC/min O/P-FG: 0.5 KVAC/min	I/P-O/P: 3.6 KVAC/min I/P-FG: 1.8 KVAC/min O/P-FG: 0.6 KVAC/min Ta:25°C	I/P-O/P: 10.6 mA I/P-FG: 9.22 mA O/P-FG: 7.61 mA NO DAMAGE	P
2	ISOLATION RESISTANCE	I/P-O/P:500VDC>100MΩ I/P-FG: 500VDC>100MΩ O/P-FG:500VDC>100MΩ	I/P-O/P: 500 VDC I/P-FG: 500 VDC O/P-FG: 500 VDC Ta:25°C	I/P-O/P: 2 GΩ I/P-FG: 1 GΩ O/P-FG: 1 GΩ NO DAMAGE	P
3	GROUNDING CONTINUITY	FG(PE) TO CHASSIS OR TRACE < 100 mΩ	40 A / 2min Ta:25°C	10 mΩ	P
4	APPROVAL	TUV: Certificate NO : ---- UL: File NO : E183223			P

COMPONENT STRESS TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	Power Transistor ( D to S) or (C to E) <b>Peak Voltage</b>	Q1 Rated IRGP50B60PD : 600V 50 A	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on (2) Full Load (3)Output Short Ta:25°C	(1) 422 V (2) 412 V (3) 460 V	P
2	Diode <b>Peak Voltage</b>	D100 Rated S60SC4M : 40V 60A	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on (2) Full Load (3)Output Short Ta:25°C	(1) 36 V (2) 36 V (3) 36.2 V	P
3	<b>Input Capacitor Voltage</b>	C5 Rated :1500u / 200V/ 85°C	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on /Off (2) Min load Turn on /Off (3)Full Load /Min load Change (4)Burn in 1hour Ta:25°C	(1) 182 V (2) 191 V (3) 182 V (4) 182 V	P
4	<b>Control IC Voltage Test</b>	U2 Rated SG3525AN : 40 V	I/P:High-Line +3V = 267 V O/P: (1)Full Load Turn on /Off (2) Min load Turn on /Off (3)Full Load /Min load Change Ta:25°C	(1) 15.8 V (2) 15.7 V (3) 15.7 V	P

DATE	SAMPLE	TEST RESULT	TESTER	APPROVAL
2005/12/21	RD SAMPLE	PASS	VINCENT TSENG	MAX LIN
2006/3/9	PRODUCT SAMPLE W0601B20	PASS	VINCENT TSENG	MAX LIN
2006/5/11	PRODUCT SAMPLE W0604B22	PASS	VINCENT TSENG	MAX LIN

2003/12/12 A50-F023