



■ Features :

- 2:1 wide input range
- Protections: Short circuit / Overload / Over voltage / Over temperature
- 1500VDC I/O isolation
- Forced air cooling by built-in DC Fan
- 100% full load burn-in test
- 24V and 48V input voltage design refer to LVD
- 2 years warranty

CB (for D type only) **CE**

SPECIFICATION

MODEL		SD-350B				SD-350C				
OUTPUT	DC VOLTAGE	5V	12V	24V	48V	5V	12V	24V	48V	
	RATED CURRENT	57A	27.5A	14.6A	7.3A	60A	27.5A	14.6A	7.3A	
	CURRENT RANGE	0 ~ 57A	0 ~ 27.5A	0 ~ 14.6A	0 ~ 7.3A	0 ~ 60A	0 ~ 27.5A	0 ~ 14.6A	0 ~ 7.3A	
	RATED POWER	285W	330W	350.4W	350.4W	300W	330W	350.4W	350.4W	
	RIPPLE & NOISE (max.) Note.2	100mVp-p	120mVp-p	150mVp-p	200mVp-p	100mVp-p	120mVp-p	150mVp-p	200mVp-p	
	VOLTAGE ADJ. RANGE	4.5 ~ 5.5VDC	11 ~ 16VDC	23 ~ 30VDC	43 ~ 53VDC	4.5 ~ 5.5VDC	11 ~ 16VDC	23 ~ 30VDC	43 ~ 53VDC	
	VOLTAGE TOLERANCE Note.3	±2.0%	±1.0%	±1.0%	±1.0%	±2.0%	±1.0%	±1.0%	±1.0%	
	LINE REGULATION	±0.5%	±0.3%	±0.2%	±0.2%	±0.5%	±0.3%	±0.2%	±0.2%	
	LOAD REGULATION	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	±1.0%	
SETUP, RISE TIME	300ms, 50ms at full load									
INPUT	VOLTAGE RANGE	B:19 ~ 36VDC		C:36 ~ 72VDC		D:72 ~ 144VDC				
	EFFICIENCY (Typ.)	74%	80%	80%	84%	76%	81%	81%	82%	
	DC CURRENT (Typ.)	14.4A/24V	16A/24V	17.6A/24V	17.6A/24V	7.6A/48V	8.8A/48V	9.0A/48V	9.0A/48V	
	INRUSH CURRENT (Typ.)	C:45A/48VDC		D:45A/96VDC						
PROTECTION	OVERLOAD	105 ~ 135% rated output power Protection type : Shut down o/p voltage, re-power on to recover								
	OVER VOLTAGE	5.75 ~ 6.75V	16.8 ~ 20V	31.5 ~ 37.5V	53 ~ 65V	5.75 ~ 6.75V	16.8 ~ 20V	31.5 ~ 37.5V	53 ~ 65V	
	OVER TEMPERATURE	95°C ±5°C (TSW1) detect on main power transistor Protection type : Shut down o/p voltage, recovers automatically after temperature goes down								
ENVIRONMENT	WORKING TEMP.	-20 ~ +60°C (Refer to output load derating curve)								
	WORKING HUMIDITY	20 ~ 90% RH non-condensing								
	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH								
	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)								
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes								
SAFETY & EMC (Note 4)	SAFETY STANDARDS	IEC60950-1 CB approved by TUV (for D type only)								
	WITHSTAND VOLTAGE	I/P-O/P:1.5KVAC I/P-FG:1.5KVAC O/P-FG:0.5KVAC								
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH								
	EMI CONDUCTION & RADIATION	Compliance to EN55022 (CISPR22) Class B								
	EMS IMMUNITY	Compliance to EN61000-4-2,3,4,6,8; ENV50204, light industry level, criteria A								
OTHERS	MTBF	209.4K hrs min. MIL-HDBK-217F (25°C)								
	DIMENSION	215*115*50mm (L*W*H)								
	PACKING	1.1Kg; 12pcs/14.4Kg/0.92CUFT								
NOTE	<ol style="list-style-type: none"> 1. All parameters NOT specially mentioned are measured at 24,48,96VDC input, rated load and 25°C of ambient temperature. 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. 3. Tolerance : includes set up tolerance, line regulation and load regulation. 4. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives. 									



■ Features :

- 2:1 wide input range
- Protections: Short circuit / Overload / Over voltage / Over temperature
- 1500VDC I/O isolation
- Forced air cooling by built-in DC Fan
- 100% full load burn-in test
- 24V(B) and 48V(C) input voltage design refer to LVD
- 2 years warranty



CB (for D type only) **CE**

SPECIFICATION

MODEL		SD-350D			
OUTPUT	DC VOLTAGE	5V	12V	24V	48V
	RATED CURRENT	60A	29.2A	14.6A	7.3A
	CURRENT RANGE	0 ~ 60A	0 ~ 29.2A	0 ~ 14.6A	0 ~ 7.3A
	RATED POWER	300W	350.4W	350.4W	350.4W
	RIPPLE & NOISE (max.) Note.2	100mVp-p	120mVp-p	150mVp-p	200mVp-p
	VOLTAGE ADJ. RANGE	4.5 ~ 5.5VDC	11 ~ 16VDC	23 ~ 30VDC	43 ~ 53VDC
	VOLTAGE TOLERANCE Note.3	±2.0%	±1.0%	±1.0%	±1.0%
	LINE REGULATION	±0.5%	±0.3%	±0.2%	±0.2%
	LOAD REGULATION	±1.0%	±1.0%	±1.0%	±1.0%
SETUP, RISE TIME	300ms, 50ms at full load				
INPUT	VOLTAGE RANGE	B:19 ~ 36VDC C:36 ~ 72VDC D:72 ~ 144VDC			
	EFFICIENCY (Typ.)	78%	83%	87%	89%
	DC CURRENT (Typ.)	6A/96V	6A/96V	6A/96V	6A/96V
	INRUSH CURRENT (Typ.)	C:45A/48VDC D:45A/96VDC			
PROTECTION	OVERLOAD	105 ~ 135% rated output power Protection type : Shut down o/p voltage, re-power on to recover			
	OVER VOLTAGE	5.75 ~ 6.75V	16.8 ~ 20V	31.5 ~ 37.5V	53 ~ 65V
	OVER TEMPERATURE	75°C ±5°C (TSW1) detect on main power transistor Protection type : Shut down o/p voltage, recovers automatically after temperature goes down			
ENVIRONMENT	WORKING TEMP.	-20 ~ +60°C (Refer to output load derating curve)			
	WORKING HUMIDITY	20 ~ 90% RH non-condensing			
	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH			
	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)			
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes			
SAFETY & EMC (Note 4)	SAFETY STANDARDS	IEC60950-1 CB approved by TUV (for D type only)			
	WITHSTAND VOLTAGE	I/P-O/P:1.5KVAC I/P-FG:1.5KVAC O/P-FG:0.5KVAC			
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH			
	EMI CONDUCTION & RADIATION	Compliance to EN55022 (CISPR22) Class B			
OTHERS	EMS IMMUNITY	Compliance to EN61000-4-2,3,4,6,8; ENV50204, light industry level, criteria A			
	MTBF	209.4K hrs min. MIL-HDBK-217F (25°C)			
	DIMENSION	215*115*50mm (L*W*H)			
NOTE	PACKING	1.1Kg; 12pcs/14.4Kg/0.92CUFT			
		1. All parameters NOT specially mentioned are measured at 24,48,96VDC input, rated load and 25°C of ambient temperature. 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. 3. Tolerance : includes set up tolerance, line regulation and load regulation. 4. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives.			

Mechanical Specification

Case No. 912B Unit:mm




↑
Air flow direction


Terminal Pin No. Assignment :

Pin No.	Assignment	Pin No.	Assignment
1	DC INPUT V+	4,5,6	DC OUTPUT V-
2	DC INPUT V-	7,8,9	DC OUTPUT V+
3	FG \perp		


Block Diagram



Derating Curve



Static Characteristics



MODEL : SD-350D-12

OUTPUT FUNCTION TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	RIPPLE & NOISE	V1: 120 mVp-p (Max)	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	V1 : 19 mVp-p (Max)	P
2	OUTPUT VOLTAGE ADJUST RANGE	CH1: 11 V- 16 V	I/P: 96 VDC O/P:MIN LOAD Ta:25°C	9.93V- 18.07 V	P
3	OUTPUT VOLTAGE TOLERANCE	V1: 1 %- -1 % (Max)	I/P:96 VDC / 144 VDC O/P:FULL/ MIN LOAD Ta:25°C	V1: 0.2 %- -0.2 %	P
4	LINE REGULATION	V1: 0.3 %- -0.3 % (Max)	I/P:96 VDC / 144 VDC O/P:FULL LOAD Ta:25°C	V1: 0.05 %- -0.05 %	P
5	LOAD REGULATION	V1: 1 %- -1 % (Max)	I/P: 96 VDC O/P:FULL -MIN LOAD Ta:25°C	V1: 0.15 %- -0.15 %	P
6	SET UP TIME	300 ms (Max)	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	48 ms	P
7	RISE TIME	50 ms (Max)	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	21 ms	P
8	OVER/UNDERSHOOT TEST	< ±5%	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	TEST: <5 %	P
9	DYNAMIC LOAD	V1: 1200 mVp-p	I/P: 96 VDC O/P:FULL /Min LOAD 90%DUTY/1KHZ Ta:25°C	339 mVp-p	P

INPUT FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	INPUT VOLTAGE RANGE	72VDC- 144 VDC	I/P:TESTING O/P:FULL LOAD Ta:25°C	58 V~ 144 V	P
			I/P: LOW-LINE-0.2V= 71.8 V HIGH-LINE+5%= 151.2 V O/P:FULL/MIN LOAD ON: 30 Sec . OFF: 30 Sec 10MIN (AC POWER ON/OFF NO DAMAGE)	TEST: OK	
2	EFFICIENCY	83% (TYP)	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	83.2 %	P
3	INPUT CURRENT	4.4A (TYP)	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	I = 4.3 A	P
4	INRUSH CURRENT	45 A (TYP) COLD START	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	I = 34 A	P

PROTECTION FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	OVER LOAD PROTECTION	105 %- 135 %	I/P: 96 VDC O/P:TESTING Ta:25°C	120 % Shunt down Re-power ON	P
2	OVER VOLTAGE PROTECTION	CH1: 16.8 V~ 20 V	I/P: 96 VDC O/P:MIN LOAD Ta:25°C	18.9 V Shunt down Re- power ON	P
3	OVER TEMPERATURE PROTECTION	SPEC: 75 ± 5 °C O.T.P. NO DAMAGE	I/P: 96 VDC O/P:FULL LOAD	O.T.P. Active Shut down o/p voltage , recovers automatically after temperature goes down	P
4	SHORT PROTECTION	SHORT EVERY OUTPUT 1 HOUR NO DAMAGE	I/P: 96 VDC O/P: FULL LOAD Ta:25°C	NO DAMAGE Shunt down Re-power ON	P

CONTROL FUNCTION TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	FAN SPEED CONTROL	-----	I/P:96 VDC O/P:FULL LOAD Ta:25°C	Fan Voltage= 11.95 V	P

ENVIRONMENT TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT																																																																																
1	TEMPERATURE RISE TEST	MODEL : SD-350D-24 1. ROOM AMBIENT BURN-IN : 1 HRS I/P: 96 VDC O/P: FULL LOAD Ta= 29.1 °C 2. HIGH AMBIENT BURN-IN : 2 HRS I/P: 96 VDC O/P: FULL LOAD Ta= 49.4 °C			P																																																																																
		<table border="1"> <thead> <tr> <th>NO</th> <th>Position</th> <th>P/N</th> <th>ROOM AMBIENT Ta= 29.1 °C</th> <th>HIGH AMBIENT Ta= 49.4 °C</th> </tr> </thead> <tbody> <tr><td>1</td><td>LF1</td><td>TR-507</td><td>37.6°C</td><td>59.3°C</td></tr> <tr><td>2</td><td>C6</td><td>470U/200V RUB 85°C USP</td><td>36.6°C</td><td>55.5°C</td></tr> <tr><td>3</td><td>Q4</td><td>IRFP460A 20A/500V IR</td><td>48.2°C</td><td>69.1°C</td></tr> <tr><td>4</td><td>Q1</td><td>IRFP460A 20A/500V IR</td><td>50.2°C</td><td>70.9°C</td></tr> <tr><td>5</td><td>C25</td><td>100U/25V RUB105°C YXG</td><td>44.0°C</td><td>63.9°C</td></tr> <tr><td>6</td><td>U1</td><td>SG3525 ON</td><td>46.3°C</td><td>66.2°C</td></tr> <tr><td>7</td><td>T1 COIL</td><td>TF-959</td><td>60.7°C</td><td>82.3°C</td></tr> <tr><td>8</td><td>U4</td><td>HA358</td><td>45.8°C</td><td>67.0°C</td></tr> <tr><td>9</td><td>RG2</td><td>L7812CV 1A/15V</td><td>44.0°C</td><td>65.6°C</td></tr> <tr><td>10</td><td>Q5</td><td>C5762 7A/400V SANYO</td><td>43.2°C</td><td>63.2°C</td></tr> <tr><td>11</td><td>RG1</td><td>L7815CV 1A/15V</td><td>49.0°C</td><td>68.3°C</td></tr> <tr><td>12</td><td>D100</td><td>S20LC20U 20A/200V SHI</td><td>55.7°C</td><td>75.5°C</td></tr> <tr><td>13</td><td>D101</td><td>S20LC20U 20A/200V SHI</td><td>51.4°C</td><td>70.3°C</td></tr> <tr><td>14</td><td>L100</td><td>TR-383</td><td>50.1°C</td><td>71.5°C</td></tr> <tr><td>15</td><td>C111</td><td>1500U/35V NCC 105°C KY</td><td>37.8°C</td><td>58.8°C</td></tr> </tbody> </table>	NO	Position		P/N	ROOM AMBIENT Ta= 29.1 °C	HIGH AMBIENT Ta= 49.4 °C	1	LF1	TR-507	37.6°C	59.3°C	2	C6	470U/200V RUB 85°C USP	36.6°C	55.5°C	3	Q4	IRFP460A 20A/500V IR	48.2°C	69.1°C	4	Q1	IRFP460A 20A/500V IR	50.2°C	70.9°C	5	C25	100U/25V RUB105°C YXG	44.0°C	63.9°C	6	U1	SG3525 ON	46.3°C	66.2°C	7	T1 COIL	TF-959	60.7°C	82.3°C	8	U4	HA358	45.8°C	67.0°C	9	RG2	L7812CV 1A/15V	44.0°C	65.6°C	10	Q5	C5762 7A/400V SANYO	43.2°C	63.2°C	11	RG1	L7815CV 1A/15V	49.0°C	68.3°C	12	D100	S20LC20U 20A/200V SHI	55.7°C	75.5°C	13	D101	S20LC20U 20A/200V SHI	51.4°C	70.3°C	14	L100	TR-383	50.1°C	71.5°C	15	C111	1500U/35V NCC 105°C KY	37.8°C	58.8°C		
NO	Position	P/N	ROOM AMBIENT Ta= 29.1 °C	HIGH AMBIENT Ta= 49.4 °C																																																																																	
1	LF1	TR-507	37.6°C	59.3°C																																																																																	
2	C6	470U/200V RUB 85°C USP	36.6°C	55.5°C																																																																																	
3	Q4	IRFP460A 20A/500V IR	48.2°C	69.1°C																																																																																	
4	Q1	IRFP460A 20A/500V IR	50.2°C	70.9°C																																																																																	
5	C25	100U/25V RUB105°C YXG	44.0°C	63.9°C																																																																																	
6	U1	SG3525 ON	46.3°C	66.2°C																																																																																	
7	T1 COIL	TF-959	60.7°C	82.3°C																																																																																	
8	U4	HA358	45.8°C	67.0°C																																																																																	
9	RG2	L7812CV 1A/15V	44.0°C	65.6°C																																																																																	
10	Q5	C5762 7A/400V SANYO	43.2°C	63.2°C																																																																																	
11	RG1	L7815CV 1A/15V	49.0°C	68.3°C																																																																																	
12	D100	S20LC20U 20A/200V SHI	55.7°C	75.5°C																																																																																	
13	D101	S20LC20U 20A/200V SHI	51.4°C	70.3°C																																																																																	
14	L100	TR-383	50.1°C	71.5°C																																																																																	
15	C111	1500U/35V NCC 105°C KY	37.8°C	58.8°C																																																																																	
2	OVER LOAD BURN-IN TEST	NO DAMAGE 1 HOUR (MIN)	I/P: 96 VDC O/P: 120 % LOAD Ta:25°C	TEST : OK	P																																																																																
3	LOW TEMPERATURE TURN ON TEST	TURN ON AFTER 2 HOUR	I/P: 96 VDC O/P: 100 % LOAD Ta= -20 °C	TEST : OK	P																																																																																
4	HIGH HUMIDITY HIGH TEMPERATURE HIGH VOLTAGE TURN ON TEST	AFTER 12 HOURS IN CHAMBER ON CONTROL 50 °C NO DAMAGE	I/P: 144VDC O/P:FULL LOAD Ta= 50 °C HUMIDITY= 95 %R.H	TEST : OK	P																																																																																
5	TEMPERATURE COEFFICIENT	± 0.03 %(0-50°C)	I/P: 96 VDC O/P:FULL LOAD	± 0.01 %(0-50°C)	P																																																																																
6	VIBRATION TEST	1 Carton & 1 Set Operating at I/P: 96 VAD NO LOAD (1) Waveform: Sine Wave (2) Frequency:10-500Hz (3) Sweep Time:10min/sweep cycle (4) Acceleration:2G (5) Test Time:1 hour in each axis (X.Y.Z) (6) Ta:25°C		TEST : OK	P																																																																																

SAFETY TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	WITHSTAND VOLTAGE	I/P-O/P: 1.5 KVAC/min I/P-FG: 1.5 KVAC/min O/P-FG: 0.5 KVAC/min	I/P-O/P: 1.8 KVAC/min I/P-FG: 1.8 KVAC/min O/P-FG: 0.6 KVAC/min Ta:25°C	I/P-O/P: 4.64 mA I/P-FG: 4.7 mA O/P-FG: 7.51 mA NO DAMAGE	P
2	ISOLATION RESISTANCE	I/P-O/P:500VDC>100MΩ I/P-FG: 500VDC>100MΩ O/P-FG:500VDC>100MΩ	I/P-O/P: 500 VDC I/P-FG: 500 VDC O/P-FG: 500 VDC Ta:25°C	I/P-O/P: 3 G Ω I/P-FG: 3 G Ω O/P-FG: 2 G Ω NO DAMAGE	P
3	GROUNDING CONTINUITY	FG(PE) TO CHASSIS OR TRACE < 100 mΩ	40 A / 2min Ta:25°C	11 mΩ	P
4	APPROVAL	TUV: Certificate NO : UL: File NO :			N/A

E.M.C TEST

NO	TEST ITEM	SPECIFICATION	TEST CONDITION	RESULT	VERDICT
1	RADIATION	EN55022 CLASS B	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	PASS Test by certified Lab	P
2	E.S.D	EN61000-4-2 INDUSTRY AIR:8KV / Contact:4KV	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	CRITERIA A	P
3	E.F.T	EN61000-4-4 INDUSTRY INPUT: 2KV	I/P: 96 VDC O/P:FULL LOAD Ta:25°C	CRITERIA A	P
4	Test by certified Lab & Test Report Prepare				



M.T.B.F & LIFE CYCLE CALCULATION

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	CAPACITOR LIFE CYCLE	SUPPOSE C 111 IS THE MOST CRITICAL COMPONENT I/P: 96 VDC O/P:FULL LOAD Ta= 25 °C LIFE TIME= 1714456 HRS I/P: 96 VDC O/P:FULL LOAD Ta= 50 °C LIFE TIME= 294739 HRS			P
2	MTBF	MIL-HDBK-217F NOTICES2 PARTS COUNT TOTAL FAILURE RATE: 209.4K HRS			P

COMPONENT STRESS TEST

NO	TEST ITEM	SPECICATION	TEST CONDITION	RESULT	VERDICT
1	Power Transistor (D to S) or (C to E) Peak Voltage	Q 1 Rated IRFP460A : 500V 20A	I/P:High-Line +3V = 147 VDC O/P: (1)Full Load Turn on (2) Full Load (3)Output Short Ta:25°C	(1) 284 V (2) 310 V (3) 146 V	P
2	Diode Peak Voltage	D 100 Rated KCH30A10 : 100 V 30 A	I/P:High-Line +3V = 147 VDC O/P: (1)Full Load Turn on (2) Full Load (3)Output Short Ta:25°C	(1) 84.8 V (2) 94.8 V (3) 0 V	P
3	Input Capacitor Voltage	C 8 Rated : 470 u / 200 V / 85°C	I/P:High-Line +3V = 147 VDC O/P: (1)Full Load Turn on /Off (2) Min load Turn on /Off (3)Full Load /Min load Change Ta:25°C	(1) 148 V (2) 148 V (3) 150 V	P
4	Control IC Voltage Test	U 1 Rated SG3525 : 35 V	I/P:High-Line +3V = 147 VDC O/P: (1)Full Load Turn on /Off (2) Min load Turn on /Off (3)Full Load /Min load Change Ta:25°C	(1) 13.9 V (2) 14.0 V (3) 13.9 V	P

DATE	SAMPLE	TEST RESULT	TESTER	APPROVAL
2004/6/7	RD SMAPLE	PASS	VINCENT TSENG	MAX LIN
2004/8/20	PRODUCT SMAPLE A407A23	PASS	VINCENT TSENG	MAX LIN
2004/9/13	PRODUCT SMAPLE W0408C31	PASS	VINCENT TSENG	MAX LIN
2004/11/25	PRODUCT SMAPLE W0411A25	PASS	VINCENT TSENG	MAX LIN

2003/12/12 A50-F023