

Part # 24 BNC, 24 AWG Bare Nickel Chromium Consolidated Resistance Wire (BNC)

Product Construction

Construction 24 AWG (BNC):

- Solid bare nickel chromium resistance wire - 60% nickel, 16% chromium, 24% iron

Characteristics:

- Consolidated Bare Nickel Chromium Resistance Wire
- Temperature: to +982°C / 1800°F
- Excellent resistance characteristics
- ASTM B267 class 3b
- ASTM E112

Packing:

- 1/4 lb. spools
- 1/2 lb. spools
- 1 lb. spools
- Also available on bulk spools

Sold in standard packages of five spools per gauge size and spool put-up.



Specifications

Conductor Size	24 AWG
Nominal Diameter in. (mm)	0.0201 in. (0.5105 mm)
Ohms per ft. at 68°F	1.671
Spool Put-Up	1/4 lbs 1/2 lbs 1 lbs
Temperature	Up to 982 °C