

Distributed by:



[www.Jameco.com](http://www.Jameco.com) ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.

# Quality Engineering Test Report

**SERIES: SP-100 100 WATTS SIGLE OUTPUT SWITCHING POWER SUPPLY**

**SAMPLE: A.SP-100-3.3 3.3V / 20A D.SP-100-12 12V /8.5A G.SP-100-24 24V /4.2A**  
**B.SP-100-5 5V /20A E.SP-100-13.5 13.5V /7.5A H.SP-100-27 27V /3.8A**  
**C.SP-100-7.5 7.5V /13.5A F.SP-100-15 15V /6.7A I.SP-100-48 48V /2.1A**

NO	TEST ITEM	TEST CONDITION / SPECIFICATION	RESULT	VERDICT
1	AC INPUT VOLTAGE RANGE	I/P:TESTING SPEC:85-264VAC O/P:FULL LOAD	F : 54V~267VAC	P
2	LINE REGULATION	I/P:85-264VAC SPEC: O/P:FULL LOAD A: ±0.5% B: ±0.5% C:±0.5% D: ±0.5% E: ±0.5% G:±0.5% H: ±0.5% I: ±0.5%	A: 0.18% ~ 0.18% B: -0.36% ~ 0.36% C: 0% ~ 0% D: 0% ~ 0% E: 0% ~ 0% F: 0% ~ 0% G: 0% ~ 0.02% H: 0% ~ 0% I: -0.01% ~ -0.01%	P
3	LOAD REGULATION	I/P:230VAC SPEC: O/P:0% LOAD TO FULL LOAD A: ±1% B: ±1% C: ±1% D: ±0.5% E: ±0.5% F: ±0.5% G: ±0.5% H: ±0.5% I: ±0.5%	A: 0.35% ~ 0.17% B: -0.12% ~ 0.12% C: -0.24% ~ 0.16% D: -0.04 % ~ 0% E: 0% ~ 0.042% F: -0.07% ~ 0.07% G: 0% ~ 0.020% H: 0.06% ~ -0.04% I: 0% ~ 0.024%	P
4	OUTPUT VOLTAGE TOLERANCE	I/P:85-264VAC SPEC: O/P:0% LOAD TO FULL LOAD A: ±2% B: ±2% C: ±2% D: ±2% E: ±2% F: ±2% G: ±1% H: ±1% I: ±1%	A: -1.19% ~ 0% B: 1% ~ 1.3% C: -0.4% ~ 0.07% D: 0% ~ -0.05% E: 0.50% ~ 0.45% F: 0.10% ~ 0.74% G: 0.70% ~ 0.75% H: 0.67% ~ 0.6% I: 0.46% ~ 0.41%	P
5	RIPPLE & NOISE	I/P:230VAC SPEC: O/P: FULL LOAD A:100mV B:100mV C:100mV D:100mV E:100mV F:100mV G :150mV H:150mV I:250mV	A: 37mV B: 92mV C: 76mV D: 52mV E: 65mV F: 58mV G: 66mV H: 50mV I: 87mV	P
6	AC INPUT CURRENT	I/P:230VAC SPEC: 0.75A(3.3v:0.06A) O/P:FULL LOAD	F:0.55A	P
7	MAX. INRUSH CURRENT	I/P:230VAC SPEC: 40A O/P:FULL LOAD	F:14.8A	P

[NEXT](#)

NO	TEST ITEM	TEST CONDITION / SPECIFICATION	RESULT	VERDICT
8	O/P VOLTAGE ADJ.RANGE	I/P:230VAC O/P:MIN. LOAD SPEC: +10%~-5% A:3.1V~3.6V B:4.7V~5.5V C:7.12V~8.25V D:11.4V~13.2V E:12.8 V~14.8V F:14.2V~16.5V G:22.8V~26.4V H:25.6V~29.7V I:45.6V~52.8V	A:3.08V~3.8V B:4.39V~5.54V C:6.33V~9.06V D:10.1V~13.6V E:11.55V~14.89V F:12.79V~17.63V G:19.6V~27.4V H:20.15V~30.09V I:40V~54.3V	P
9	SET UP TIME	I/P:230VAC O/P:FULL LOAD SPEC:600ms	F:56mS	P
10	HOLD UP TIME	I/P:230VAC O/P:FULL LOAD SPEC:20mS	F:34mS	P
11	EFFICIENCY	I/P:230VAC O/P: FULL LOAD SPEC: A:70% B:76% C:78% D:80% E:80% F:82% G:84% H:83% I:82	A: 70.20% B: 78.01% C: 78.76% D: 83.05% E: 83.64% F: 81.37% G: 86.20% H: 87.07% I: 87.13%	P
12	OVER LOAD PROTECTION	I/P:230VAC O/P:TESTING SPEC:105%~150%	A: 130% B: 112% C: 130% D: 122% E: 118% F: 148% G: 124% H: 128% I: 133%	P
13	OVER VOLTAGE PROTECTION	I/P:230VAC O/P: TESTING SPEC:110%~135% A3.63~4.45 V B:5.5~6.75V C:8.25~10.12V D:13.2~16.2V E:14.8~18.2V F:16.5~20.2V G:26.4~32.4V H:29.7~36.4V I:52.8~64.8V	A: 4.2V B: 5.79V C: 9.3V D: 14.3V E: 15.8V F: 19.0V G: 29.1V H: 31.8V I: 56.8V	P
14	GROUND LEAKAGE CURRENT	I/P:240VAC SPEC: L-FG-<2mA N-FG-<2mA	A: L-FG:0.6mA N-FG:0.48mA	P
15	GROUNDING CONTINUITY	SPEC: FG-CHASSIS<0.1Ohms/2min	A: 52mOhms	P
16	INSULATION RESISTANCE	SPEC: O/P-FG 500VDC / 100M Ohms MIN. I/P-O/P 500VDC / 100M Ohms MIN. I/P-FG 500VDC / 100M Ohms MIN.	A: O/P-FG >100MOhms I/P-O/P >100MOhms I/P-FG >100MOhms	P

NO	TEST ITEM	TEST CONDITION / SPECIFICATION	RESULT	VERDICT																																																												
17	DIELECTRIC / WITHSTAND VOLTAGE	SPEC : I/P- O/P: 3000VAC/ 60 sec (10mA CUT-OFF) I/P - FG: 1500VAC/ 60 sec (10mA CUT-OFF) O/P - FG: 500VAC/60sec (10mA CUT-OFF)	:F I/P-O/P : 4.00mA I/P-FG : 3.38mA O/P- FG : 3.56mA	P																																																												
18	BURN-IN TEST	I/P: 230VAC O/P:FULL LOAD with cooling FAN TA:26.7 °C BURN-IN DURATION : 13.5 hrs	B: NON BREAK	P																																																												
19	ENVIRONMENT TEST	1.LOW TEMPERATURE TEST I/P : 230 VAC O/P : 80% LOAD AMBIENT TEMPERATURE : -10.1°C	B : AFTER 2 hrs POWER ON OK	P																																																												
		2.HIGH AMBIENT TEMPERATURE TEST I/P : 230VAC O/P: FULL LOAD TEMPERATURE : 40.3°C with cooling FAN	B : AFTER 2.5hrs NON BREAK																																																													
		3.HIGH HUMIDITY HIGH VOLTAGE ON/OFF TEST I/P : 272VAC O/P : FULL LOAD AMBIENT TEMPERATURE : 25°C AMBIENT HUMIDITY : 95%	I : AFTER 14.5 hrs POWER ON/OFF NON BREAK																																																													
20	TEMPERATURE RISE TEST Trise OF PARTS	B: I/P : 230VAC AFTER 13 hrs BURN-IN O/P : FULL LOAD TA : 26.2°C	<table border="1"> <thead> <tr> <th></th> <th>POSITION</th> <th>P/N</th> <th>TEMP</th> <th>Trise</th> </tr> </thead> <tbody> <tr> <td></td> <td>BD1</td> <td>BRIDGE DIODE</td> <td>51.5°C</td> <td>25.3°C</td> </tr> <tr> <td></td> <td>Q2</td> <td>MAIN TRANSISTOR</td> <td>60.0°C</td> <td>33.8°C</td> </tr> <tr> <td></td> <td>Q1</td> <td>PFC TRANSISTOR</td> <td>43.9°C</td> <td>17.7°C</td> </tr> <tr> <td></td> <td>T1</td> <td>MAIN TRANSFORMER COIL</td> <td>60.5°C</td> <td>34.3°C</td> </tr> <tr> <td></td> <td>T1</td> <td>MAIN TRANSFORMER CORE</td> <td>65.9°C</td> <td>39.7°C</td> </tr> <tr> <td></td> <td>D19</td> <td>O/P DIODE</td> <td>61.9°C</td> <td>35.7°C</td> </tr> <tr> <td></td> <td>C42</td> <td>O/P FILTER CAPACITOR</td> <td>60.3°C</td> <td>34.1°C</td> </tr> <tr> <td></td> <td>L2</td> <td>O/P CHOCK</td> <td>76.8°C</td> <td>50.6°C</td> </tr> <tr> <td></td> <td>C5</td> <td>I/P FILTER CAPACITOR</td> <td>43.6°C</td> <td>17.4°C</td> </tr> <tr> <td></td> <td>LF1</td> <td>LINE FILTER COIL</td> <td>42.1°C</td> <td>15.9°C</td> </tr> <tr> <td></td> <td>D2</td> <td>PFC DIODE</td> <td>36.9°C</td> <td>10.7°C</td> </tr> </tbody> </table>		POSITION	P/N	TEMP	Trise		BD1	BRIDGE DIODE	51.5°C	25.3°C		Q2	MAIN TRANSISTOR	60.0°C	33.8°C		Q1	PFC TRANSISTOR	43.9°C	17.7°C		T1	MAIN TRANSFORMER COIL	60.5°C	34.3°C		T1	MAIN TRANSFORMER CORE	65.9°C	39.7°C		D19	O/P DIODE	61.9°C	35.7°C		C42	O/P FILTER CAPACITOR	60.3°C	34.1°C		L2	O/P CHOCK	76.8°C	50.6°C		C5	I/P FILTER CAPACITOR	43.6°C	17.4°C		LF1	LINE FILTER COIL	42.1°C	15.9°C		D2	PFC DIODE	36.9°C	10.7°C	P
	POSITION	P/N	TEMP	Trise																																																												
	BD1	BRIDGE DIODE	51.5°C	25.3°C																																																												
	Q2	MAIN TRANSISTOR	60.0°C	33.8°C																																																												
	Q1	PFC TRANSISTOR	43.9°C	17.7°C																																																												
	T1	MAIN TRANSFORMER COIL	60.5°C	34.3°C																																																												
	T1	MAIN TRANSFORMER CORE	65.9°C	39.7°C																																																												
	D19	O/P DIODE	61.9°C	35.7°C																																																												
	C42	O/P FILTER CAPACITOR	60.3°C	34.1°C																																																												
	L2	O/P CHOCK	76.8°C	50.6°C																																																												
	C5	I/P FILTER CAPACITOR	43.6°C	17.4°C																																																												
	LF1	LINE FILTER COIL	42.1°C	15.9°C																																																												
	D2	PFC DIODE	36.9°C	10.7°C																																																												
21	LIFE CYCLE	SUPPOSE C42 IS THE MOST CRITICAL COMPONENT I/P : 230VAC O/P : FULL LOAD Ta : 25°C Tc42 : 59.1°C Life:143581hrs I/P : 230VAC O/P : FULL LOAD Ta : 40°C Tc42 : 72.2°C Life:57909hrs		P																																																												
22	CRITICAL COMPONENT RECORD (FOR QC INSPECTION REFERENCE ONLY)	B : FUSE :4A/250V GFE/GMA BRIDGE DIODE : D3SB60 4A/800V GL LINE FILTER :TF-479 ET-24 10mH TRANSFOMER :TF-594 EI-33 OUTPUT DIODE :CTB34M 30A/40V ESAD83004 OUTPUT CAPACITOR :N.C.C 2200uF/10V 105°C RJH INPUT CAPACITOR :HITACHI 100uF/400V,85°C HP3/USC P.C.B :SP-100 CEM-3 20Z SS																																																														

<b>DATE</b>	<b>SAMPLE</b>	<b>TEST RESULT</b>	<b>TEST</b>	<b>APPROVAL</b>
<b>19990904</b>	<b>RD SAMPLE</b>	<b>PASS</b>	<b>H.C.LIOU</b>	<b>Max Lin</b>
<b>19991014</b>	<b>PRODUCTION SAMPLE 3.3V,5V,7.5V 12V,13.5V,15V 24V,27V,48V</b>	<b>PASS</b>	<b>C.C.CHEN</b>	<b>Max Lin</b>
<b>20000619</b>	<b>PRODUCTION SAMPLE A006B09 3.3V,7.5V</b>	<b>PASS</b>	<b>VINCENT</b>	<b>Max Lin</b>
<b>20000828</b>	<b>PRODUCTION SAMPLE A008C04 12V</b>	<b>PASS</b>	<b>VINCENT</b>	<b>Max Lin</b>
<b>20020103</b>	<b>PRODUCTION SAMPLE A112D23 13.5V</b>	<b>PASS</b>	<b>VINCENT</b>	<b>Max Lin</b>

[PREVIOUS](#)

87.01.10 A50-F023