

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.

Quality Engineering Test Report

SERIES: SD-50C 50W DC-DC SINGLE OUTPUT SWITCHING POWER SUPPLY

SAMPLE: **A. SD-50C-5 5V / 10A**
 B. SD-50C-12 12V / 4.2A
 C. SD-50C-24 24V / 2.1A

| NO | TEST ITEM | TEST CONDITION / SPECIFICATION | RESULT | VERDICT |
|----|--------------------------------|---|---|---------|
| 1 | DC INPUT VOLTAGE RANGE | I/P : TESTING SPEC : 36~72VDC O/P : FULL LOAD | A:27.9~72VDC | P |
| 2 | LINE REGULATION | I/P : 36~72VDC SPEC : A:±0.5% O/P : FULL LOAD B:±0.3% C:±0.2% | A:-0%~+0% B:-0%~+0% C:-0%~+0% | P |
| 3 | LOAD REGULATION | I/P : 48VDC SPEC : A:±0.5% O/P : MIN. TO FULL LOAD B:±0.3% C:±0.2% | A:-0.12%~+0.24% B: -0%~+0.05% C:-0.02%~+0.02% | P |
| 4 | OUTPUT VOLTAGE TOLERANCE | I/P : 36~72VDC SPEC : A:±2% O/P : MIN. TO FULL LOAD B:±1% C:±1% | A:-0.12%~+0.24% B: -0%~+0.1% C:-0.02%~+0.02% | P |
| 5 | RIPPLE&NOISE | I/P : 48VDC SPEC : A:100mVp-p O/P : FULL LOAD B:120mVp-p C:150mVp-p | A:12mV B: 3mV C: 8mV | P |
| 6 | DC INPUT CURRENT | I/P : 48VDC SPEC : 1.5A O/P : FULL LOAD | A:1.268A | P |
| 7 | MAX. INRUSH CURRENT | I/P : 48VDC SPEC : NONE O/P : FULL LOAD | A:54.3A | P |
| 8 | O/P VOLTAGE ADJ. RANGE | I/P : 48VDC SPEC : A:4.5~5.5V O/P : MIN. LOAD B:11~16V C:23~30V | A:4.40~6.21V B:9.62~16.34V C:19.6~33.40V | P |
| 9 | SET UP TIME | I/P : 48VDC SPEC : 2.5S O/P : FULL LOAD | A:2211.4mS | P |
| 10 | EFFICIENCY | I/P : 48VDC SPEC : A:76% O/P : FULL LOAD B:78% C:83% | A:81.07% B:83.1% C:86.19% | P |
| 11 | OVER LOAD PROTECTION | I/P : 48VDC SPEC : 105%~150% O/P : TESTING | A:130% B:133.5% C:138.5% | P |
| 12 | OVER VOLTAGE PROTECTION | I/P : 48VDC SPEC : A:5.75V~6.75V O/P : TESTING B:16.8V~20V C:31.5V~37.5V | A:6.22V B:17.98V C:35.40V | P |
| 13 | INSULATION RESISTANCE | SPEC : I/P-O/P 500VDC/100M Ohms MIN. I/P-FG 500VDC/100M Ohms MIN. O/P-FG 500VDC/100M Ohms MIN. | A: I/P-O/P : >100M Ohms I/P-FG : >100M Ohms O/P-FG : >100M Ohms | P |
| 14 | DIELECTRIC / WITHSTAND VOLTAGE | SPEC : I/P- O/P : 1500VAC/ 1 min (10mA CUT-OFF) I/P- FG : 1500VAC/ 1 min (10mA CUT-OFF) O/P- FG : 500VAC/ 1 min (10mA CUT-OFF) | A: I/P-O/P : <2.1mA I/P-FG : <2.32mA O/P-FG : <2.38mA | P |

| | | | | |
|----|----------------------------------|--|---------------------------|---|
| 15 | BURN-IN TEST | I/P : 48VDC TA : 23.9 °C O/P:FULL LOAD BURN-IN DURATION : 3 hrs | NON BREAK | P |
| 16 | ENVIRONMENT TEST (SAMPLE A:) | HIGH AMBIENT TEMPERATURE FULL LOAD TEST I/P : 48VDC O/P : FULL LOAD AMBIENT TEMPERATURE : 53.4 °C | AFTER 13 hrs NON BREAK | P |

[NEXT](#)

| NO | TEST ITEM | TEST CONDITION / SPECIFICATION | RESULT | VERDICT | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|----------|--|---|----------|----------|------|--------|----|-----------------|--------|--------|----|------------------|--------|--------|-----|-----------|--------|--------|-----|----------------------|--------|--------|----|-----------|--------|--------|----|----------------------|--------|--------|--|---|
| 17 | TEMPERATURE RISE TEST T rise OF PARTS | <p>A: I/P : 48VDC AFTER 2 hr BURN-IN O/P : FULL LOAD TA : 23.9°C</p> <table border="1"> <thead> <tr> <th>POSITION</th> <th>P/N</th> <th>TEMP</th> <th>T rise</th> </tr> </thead> <tbody> <tr> <td>Q1</td> <td>MAIN TRANSISTOR</td> <td>49.3°C</td> <td>25.4°C</td> </tr> <tr> <td>T1</td> <td>MAIN TRANSFORMER</td> <td>66.3°C</td> <td>42.4°C</td> </tr> <tr> <td>D11</td> <td>O/P DIODE</td> <td>62.1°C</td> <td>38.2°C</td> </tr> <tr> <td>C34</td> <td>O/P FILTER CAPACITOR</td> <td>51.4°C</td> <td>27.5°C</td> </tr> <tr> <td>L1</td> <td>O/P CHOCK</td> <td>63.8°C</td> <td>39.9°C</td> </tr> <tr> <td>C5</td> <td>I/P FILTER CAPACITOR</td> <td>43.4°C</td> <td>19.5°C</td> </tr> </tbody> </table> | POSITION | P/N | TEMP | T rise | Q1 | MAIN TRANSISTOR | 49.3°C | 25.4°C | T1 | MAIN TRANSFORMER | 66.3°C | 42.4°C | D11 | O/P DIODE | 62.1°C | 38.2°C | C34 | O/P FILTER CAPACITOR | 51.4°C | 27.5°C | L1 | O/P CHOCK | 63.8°C | 39.9°C | C5 | I/P FILTER CAPACITOR | 43.4°C | 19.5°C | | P |
| POSITION | P/N | TEMP | T rise | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Q1 | MAIN TRANSISTOR | 49.3°C | 25.4°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| T1 | MAIN TRANSFORMER | 66.3°C | 42.4°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| D11 | O/P DIODE | 62.1°C | 38.2°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| C34 | O/P FILTER CAPACITOR | 51.4°C | 27.5°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| L1 | O/P CHOCK | 63.8°C | 39.9°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| C5 | I/P FILTER CAPACITOR | 43.4°C | 19.5°C | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 18 | LIFE CYCLE | <p>A: SUPPOSE C34 IS THE MOST CRITICAL COMPONENT I/P : 48VDC O/P : FULL LOAD Ta : 25°C Tc34 : 52.5°C Life: 45737 hrs I/P : 48VDC O/P : FULL LOAD Ta : 53.4°C Tc34 : 74.1°C Life: 10234 hrs</p> | | P | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 19 | CRITICAL COMPONENT RECORD (FOR QC INSPECTION REFERENCE ONLY) | <p>A: FUSE : 3A/250V INPUT DIODE : 1N5401 LINE FILTER : LS TF-096C EE-25 TRANSFORMER : TF-327 EER-28 POWER SWITCHER : K891 OUTPUT DIODE : D83-004 OUTPUT CAPACITOR : 2200uF/16V(v) 105°C HL INPUT CAPACITOR : 220uF/100V(v) 105°C HL P.C.B : SD-50 FR-4 2 OZ DS</p> | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| DATE | SAMPLE | TEST RESULT | TEST | APPROVAL | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 980421 | SD-50C | PASS | H.C.LIOU | Max Lin | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

[PREVIOUS](#)