

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
52 X 52 X 9	AD0505HX-RB1	HYPRO	5	0.22	1.10	5000	9.5	0.100	31.7	28	1	CE		
52 X 52 X 9	AD0505MB-RB1	BALL	5	0.17	0.85	4800	3.0	0.320	34.0	28	1	CE		
52 X 52 X 9	AD0512MX-RB0	HYPRO	12	0.10	1.20	4800	3.0	0.320	34.0	28	0	CE		
50 X 50 X 10	AD0505LX-G70(T)	HYPRO	5	0.12	0.60	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MX-G70	HYPRO	5	0.18	0.90	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MX-G90	HYPRO	5	0.12	0.60	3300	8.5	0.068	24.9	24	0	UL,CUL,CE		
50 X 50 X 10	AD0505HX-G70(T)	HYPRO	5	0.23	1.15	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505HX-G90	HYPRO	5	0.15	0.75	3800	9.8	0.082	28.6	50	0	UL,CUL,CE		
50 X 50 X 10	AD0505LB-G70(T)	BALL	5	0.12	0.60	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505LB-G70(TS)	1B & 1S	5	0.12	0.60	3900	9.4	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MB-G70	BALL	5	0.14	0.70	4600	10.5	0.100	24.0	18	0	CE		
50 X 50 X 10	AD0505MB-G70(T)	BALL	5	0.18	0.90	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MB-G70(TS)	1B & 1S	5	0.18	0.90	4500	10.8	0.100	25.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505HB-G70(T)	BALL	5	0.23	1.15	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505HB-G90	BALL	5	0.15	0.75	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
50 X 50 X 10	AD0505HB-G96	BALL	5	0.15	0.75	3800	9.8	0.082	28.6	24	6	CE		
50 X 50 X 10	AD0505LS-G70	S	5	0.12	0.60	3700	9.0	0.060	20.0	18	0	TUV,CE		
50 X 50 X 10	AD0505LS-G76	S	5	0.12	0.60	3700	9.0	0.060	20.0	18	0	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MS-G70(T)	S	5	0.18	0.90	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505MS-G90	S	5	0.12	0.60	3300	8.5	0.068	24.9	24	0	UL,CUL,CE		
50 X 50 X 10	AD0505HS-G70	S	5	0.18	0.90	5200	11.9	0.130	28.0	18	0	UL,CUL,TUV,CE		
50 X 50 X 10	AD0505HS-G70(T)	S	5	0.23	1.15	500	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512LX-G70(T)	HYPRO	12	0.10	0.72	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512MX-G70(T)	HYPRO	12	0.07	0.84	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512MX-G72	HYPRO	12	0.10	1.20	4300	10.5	0.100	24.0	18	2	CE		
50 X 50 X 10	AD0512MX-G90	HYPRO	12	0.07	0.84	3300	8.5	0.068	24.9	50	0	UL,CUL,CE		
50 X 50 X 10	AD0512HX-G70	HYPRO	12	0.09	1.08	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HX-G76(UT)	HYPRO	12	0.09	1.08	5600	12.4	0.112	26.4	18	6	CE		
50 X 50 X 10	AD0512HX-G90	HYPRO	12	0.08	0.96	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
50 X 50 X 10	AD0512LB-G70	BALL	12	0.06	0.72	3900	9.4	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512LB-G72	BALL	12	0.09	1.08	3700	9.0	0.060	20.0	18	2	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512LB-G73	BALL	12	0.06	0.72	3900	9.4	0.067	20.0	18	3	CE		
50 X 50 X 10	AD0512MB-G70(S)	Bor1B1S	12	0.07	0.84	4600	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512MB-G73	BALL	12	0.10	1.20	4300	10.5	0.100	24.0	18	3	CE		
50 X 50 X 10	AD0512MB-G90(S)	Bor1B1S	12	0.07	0.84	3300	8.5	0.068	24.9	24	0	UL,CUL,CE		
50 X 50 X 10	AD0512MB-G96(S)	1B & 1S	12	0.07	0.84	3300	8.5	0.068	24.9	24	6	CE		
50 X 50 X 10	AD0512HB-G70(S)	Bor1B1S	12	0.09	1.08	5200	11.9	0.130	28.0	18	0	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HB-G72	BALL	12	0.11	1.32	5000	11.2	0.130	26.0	18	2	CE		
50 X 50 X 10	AD0512HB-G73(S)	1B & 1S	12	0.09	1.08	5200	11.9	0.130	28.0	18	3	CE		
50 X 50 X 10	AD0512HB-G76	BALL	12	0.09	1.08	5000	11.2	0.130	26.0	18	6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HB-G90(S)	Bor1B1S	12	0.08	0.96	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
50 X 50 X 10	AD0512LS-G70	S	12	0.06	0.72	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512MS-G70	S	12	0.07	0.84	4600	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED