

Distributed by:



[www.Jameco.com](http://www.Jameco.com) ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.



# RELIABILITY PREDICTION

**Model : SP-100**

Data:2000-01-11

Style	Part Type	Q'ty	g	Q	eg	%
9.1	Resistor-Film, Insulated (RL)	45	0.003700	10	1.665000	35.195
9.1	Resistor-Wirewound Power (RW)	2	0.008500	10	0.170000	3.593
9.1	Resistor-Film, Variable (RVC)	1	0.040000	10	0.400000	8.455
9.1	Resistor-Thermistor (RTH)	1	0.001400	10	0.014000	0.296
10.1	Capacitor-Metal, Plastic (CH)	6	0.000510	10	0.030600	0.647
10.1	Capacitor-Ceramic(Gen.) (CK)	16	0.001700	10	0.272000	5.750
10.1	Capacitor-Aluminum Dry (CE)	12	0.001300	10	0.156000	3.298
6.1	Diode-Switching	12	0.000940	8	0.090240	1.907
6.1	Diode-Fast Recovery Power Rectifier	3	0.023000	8	0.552000	11.668
6.1	Diode-Power Rectifier / Schottky Power	4	0.002800	8	0.089600	1.894
6.1	Diode-Voltage Ref/Reg. (Avalanche & Zener)	5	0.003300	8	0.132000	2.790
6.1	Diode-Transient Suppressor/Varistor	3	0.002900	8	0.069600	1.471
6.10	Diode-Thyristor/SCR	1	0.002500	8	0.020000	0.423
6.3	Transistor-Power NPN/PNP	1	0.005700	8	0.045600	0.964
6.4	Transistor-MOSFET	2	0.014000	8	0.224000	4.735
6.11	OPTO-isolator	2	0.027000	8	0.432000	9.132
6.11	OPTO-Emitter	1	0.000470	8	0.003760	0.079
5.1	Linear Microcircuits	3	0.009500	10	0.285000	6.024
11.1	Transformer Switching	1	0.000610	3	0.001830	0.039
11.2	Coil Fixed inductor or choke	3	0.000032	3	0.000288	0.006
17.1	Single Connections-Reflow solder	334	0.000069	1	0.023046	0.487
17.1	Fuses Clip-Clip Termination	2	0.000120	1	0.000240	0.005
22.1	Fuses	1	0.010000	1	0.010000	0.211
16.1	Plated Through Hole Circuit Boards	1	0.022000	2	0.044000	0.930

**Total Failure rate:** 4.730804 100%

· **Data Base: MIL-HDBK-217F ,Notice 2, Parts Count** **MTBF: 211380.56 hrs**  
 · **Env.: GB**

Approved by: David Wang Compiled by: Kim Tseng .