

INTRODUCTION:

Adam Tech .156" Headers and Housings are two matched sets of Crimp Wire Housings and PCB mounted Latching Headers available in Straight and Right Angle orientation. This system is available with a front locking header, a rear locking header or without a locking feature. Each of the locking types are polarized to fit in only one direction with the housing. This system provides a sturdy, high current, high reliability connection with or without the polarized locking option.

FEATURES:

Matched Latching Housing & Header system
Straight, Right Angle mounting Headers
Choice of Two Latching Types
Housings feature High pressure, Low insertion force contacts

MATING CONNECTORS:

Adam Tech MTB series and all industry standard latching type
.156 [3.96mm] centers

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL94V-2
Insulator Color: Natural
Contacts: Phosphor bronze and Brass
Contact Plating:
Tin over copper underplate overall

Electrical:

Operation voltage: 250V AC max.
Current rating: 5 Amp max.
Insulation resistance: 1000 MΩ min.
Dielectric withstanding voltage: 1000V AC for 1 minute

Mechanical:

Recommended wire size: 18 to 24 Awg

Environmental:


Operating temperature: -25°C to +85°C

PACKAGING:


Anti-static plastic bags

APPROVALS AND CERTIFICATIONS:


UL Recognized File no. E224053



POWER HEADER




POWER HEADER




HOUSING




CRIMP CONTACT




LHC STRAIGHT WITH REAR LOCK




LHC-06-TS




MTC HOUSING




MTC-06




LHC RIGHT ANGLE WITH REAR LOCK








LHC-06-TRA




MTC-C CRIMP CONTACTS



MTC-C-R



A = .156 [3.96] x No. of Spaces
B = .156 [3.96] X No. of Spaces + .156 [3.96]



Recommended PCB Layout

<p>LHD STRAIGHT PBC MOUNT</p> <p>A = .156 [3.96] x No. of Positions B = .156 [3.96] x No. of Spaces</p> <p>LHD-06-TS</p>	<p>MTB HOUSING</p> <p>A = .156 [3.96] x No. of Positions B = .156 [3.96] x No. of Spaces</p> <p>MTB-08</p>
<p>LHD RIGHT ANGLE PCB MOUNT</p> <p>A = .156 [3.96] x No. of Positions B = .156 [3.96] x No. of Spaces</p> <p>LHD-06-TRA</p>	<p>LHD REVERSE RIGHT ANGLE PCB MOUNT</p> <p>A = .156 [3.96] x No. of Positions B = .156 [3.96] x No. of Spaces</p> <p>LHD-06-TRB</p>
<p>MTC-C CRIMP CONTACT</p> <p>MTC-C-R</p> <p>Recommended PCB Layout</p>	