

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 15	AD0612HS-D73GL	S	12	0.13	1.56	4500	16.6	0.152	32.4	38	3	CE	300	25.70
60 X 60 X 15	AD0624LX-D70GL	HYPRO	24	0.05	1.20	3500	12.0	0.010	27.2	38	0	CE	300	25.70
60 X 60 X 15	AD0624MX-D71GL	HYPRO	24	0.07	1.68	3900	15.0	0.138	30.7	38	1	CE	300	25.70
60 X 60 X 15	AD0624HX-D71GL	HYPRO	24	0.09	2.16	4500	17.0	0.173	33.3	38	1	TUV,CE	300	25.70
60 X 60 X 15	AD0624MB-D70GL	BALL	24	0.07	1.68	3900	15.0	0.138	30.7	38	0	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624MB-D71GL	BALL	24	0.07	1.68	3900	15.0	0.138	30.7	38	1	CE	300	25.70
60 X 60 X 15	AD0624MB-D72GL	BALL	24	0.07	1.68	3900	15.0	0.138	30.7	38	2	TUV,CE	300	25.70
60 X 60 X 15	AD0624HB-D70GL	BALL	24	0.09	2.16	4500	17.0	0.173	33.3	38	0,6	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624HB-D71GL	BALL	24	0.09	2.16	4500	17.0	0.173	33.3	38	1,2	TUV,CE	300	25.70
60 X 60 X 15	AD0624HB-D73GL	BALL	24	0.09	2.16	4500	17.0	0.173	33.3	38	3	CE	300	25.70
60 X 60 X 15	AD0624LS-D70GL	S	24	0.05	1.20	3500	13.0	0.110	27.2	38	0	CE	300	25.70
60 X 60 X 15	AD0624MS-D70GL	S	24	0.07	1.68	3900	15.0	0.138	30.7	38	0	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624MS-D71GL	S	24	0.07	1.68	3900	15.0	0.138	30.7	38	1	TUV,CE	300	25.70
60 X 60 X 15	AD0624HS-D70GL	S	24	0.09	2.16	4500	17.0	0.173	33.3	38	0	UL,CUL,CE	300	25.70
60 X 60 X 15	AD0624HS-D71GL	S	24	0.09	2.16	4500	17.0	0.173	33.3	38	1	TUV,CE	300	25.70
60 X 60 X 20	AD0605HX-C70GL	HYPRO	5	0.25	1.25	4500	16.3	0.156	29.8	49	0	CE	300	40.00
60 X 60 X 20	AD0605MB-C70GL	BALL	5	0.24	1.20	3900	14.5	0.111	25.7	49	0	CE	300	40.00
60 X 60 X 20	AD0605HB-C70GL	BALL	5	0.30	1.50	4500	16.4	0.139	29.7	49	0	TUV,CE	300	40.00
60 X 60 X 20	AD0605HB-C72GL	BALL	5	0.30	1.50	4500	16.4	0.139	29.7	49	2	CE	300	40.00
60 X 60 X 20	AD0605HS-C70GL	HYPRO	5	0.30	1.50	4500	16.4	0.139	29.7	49	0	CE	300	40.00
60 X 60 X 20	AD0612DX-C76GL	HYPRO	12	0.07	0.84	3000	10.7	0.054	18.4	49	6	CE	300	40.00
60 X 60 X 20	AD0612LX-C70GL	HYPRO	12	0.08	0.96	3500	13.3	0.096	21.6	49	0,6	UL,CSA,CE	300	40.00
60 X 60 X 20	AD0612MX-C70GL	HYPRO	12	0.13	1.56	3900	14.5	0.111	25.7	49	0	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612MX-C72GL	HYPRO	12	0.13	1.56	3900	14.5	0.111	25.7	49	2,3,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612HX-C70GL	HYPRO	12	0.16	1.92	4500	16.4	0.139	29.7	49	0	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612HX-C72GL	HYPRO	12	0.16	1.92	4500	16.4	0.139	29.7	49	2	CE	300	40.00
60 X 60 X 20	AD0612HX-C73GL	HYPRO	12	0.16	1.92	4500	16.4	0.139	29.7	49	3,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612DB-C76GL	BALL	12	0.07	0.84	3000	10.7	0.054	18.4	49	6	CE	300	40.00
60 X 60 X 20	AD0612LB-C70GL	BALL	12	0.08	0.96	3500	13.3	0.096	21.6	49	0,1	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612LB-C73GL	BALL	12	0.08	0.96	3500	13.3	0.096	21.6	49	3	CE	300	40.00
60 X 60 X 20	AD0612LB-C76GL	BALL	12	0.08	0.96	3500	13.3	0.096	21.6	49	6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612MB-C70GL	BALL	12	0.13	1.56	3900	14.5	0.111	25.7	49	0,3	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612MB-C72GL	BALL	12	0.13	1.56	3900	14.5	0.111	25.7	49	2,6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612HB-C70GL	BALL	12	0.16	1.92	4600	16.4	0.139	29.7	49	0,1,6	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612HB-C72GL	BALL	12	0.16	1.92	4600	16.4	0.139	29.7	49	2,3	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612UB-C71GL	BALL	12	0.17	2.04	5100	18.7	0.160	34.6	49	1	CE	300	40.00
60 X 60 X 20	AD0612LS-C70GL	S	12	0.08	0.96	3500	13.3	0.096	21.6	49	0	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612LS-C71GL	S	12	0.08	0.96	3500	13.3	0.096	21.6	49	1	UL,CUL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612LS-C76GL	S	12	0.08	0.96	3500	13.3	0.096	21.6	49	6	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612MS-C70GL	S	12	0.13	1.56	3900	14.5	0.111	25.7	49	0,1,6	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612MS-C72GL	S	12	0.13	1.56	3900	14.5	0.111	25.7	49	2,3	UL,CUL,CE	300	40.00
60 X 60 X 20	AD0612HS-C70GL	BALL	12	0.16	1.92	4500	16.4	0.139	29.7	49	0,1,6	UL,TUV,CSA,CE	300	40.00
60 X 60 X 20	AD0612HS-C72GL	BALL	12	0.16	1.92	4500	16.4	0.139	29.7	49	2,3	UL,CUL,CE	300	40.00

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED