


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 212531



■ Features :

- 2:1 wide input range
- Protections: Short circuit/Over load/Over voltage
- 1500VDC I/O isolation
- Built-in EMI filter, low ripple noise
- 100% full load burn-in test
- Fixed switching frequency at 83KHz
- Low cost
- High reliability
- 1 year warranty




SPECIFICATION

MODEL		SD-50A-5	SD-50B-5	SD-50C-5	SD-50A-12	SD-50B-12	SD-50C-12	SD-50A-24	SD-50B-24	SD-50C-24
OUTPUT	DC VOLTAGE	5V			12V			24V		
	RATED CURRENT	10A			4.2A			2.1A		
	CURRENT RANGE	0 ~ 10A			0 ~ 4.2A			0 ~ 2.1A		
	RATED POWER	50W			50.4W			50.4W		
	RIPPLE & NOISE (max.) Note.2	100mVp-p			120mVp-p			150mVp-p		
	VOLTAGE ADJ. RANGE	4.5 ~ 5.5VDC			11 ~ 16VDC			23 ~ 30VDC		
	VOLTAGE TOLERANCE Note.3	±2.0%			±1.0%			±1.0%		
	LINE REGULATION	±0.5%			±0.3%			±0.2%		
	LOAD REGULATION	±0.5%			±0.3%			±0.2%		
SETUP, RISE, HOLD TIME	2.5s, 50ms, ----- at full load									
INPUT	VOLTAGE RANGE	A:9.2 ~ 18VDC		B:19 ~ 36VDC		C:36 ~ 72VDC				
	EFFICIENCY (Typ.)	70%	73%	76%	72%	75%	78%	74%	80%	83%
	DC CURRENT	7A/12V			3A/24V			1.5A/48V		
PROTECTION	OVER LOAD	105 ~ 150% rated output power Protection type : Fold back current limiting, recovers automatically after fault condition is removed								
	OVER VOLTAGE	5.75 ~ 6.75V/10% load			16.8 ~ 20V/10% load			31.5 ~ 37.5V/10% load		
ENVIRONMENT	WORKING TEMP.	-10 ~ +60°C (Refer to output load derating curve)								
	WORKING HUMIDITY	20 ~ 90% RH non-condensing								
	STORAGE TEMP., HUMIDITY	-20 ~ +85°C, 10 ~ 95% RH								
	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)								
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes								
SAFETY & EMC (Note 4)	SAFETY STANDARDS	Design refer to LVD								
	WITHSTAND VOLTAGE	I/P-O/P:1.5KVAC I/P-FG:1.5KVAC O/P-FG:0.5KVAC								
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms/500VDC								
	EMI CONDUCTION & RADIATION	Compliance to EN55022 (CISPR22) Class B								
OTHERS	EMS IMMUNITY	Compliance to EN61000-4-2,3,4,6,8; ENV50204, EN55024, heavy industry level, criteria A								
	MTBF	365.6K hrs min.(SD-50A)		357.5K hrs min.(SD-50B)		368.5K Hrs min.(SD-50C)		MIL-HDBK-217F (25°C)		
	DIMENSION	159*97*38mm (L*W*H)								
	PACKING	0.53Kg; 24pcs/12.7Kg/0.75CUFT								
NOTE	<p>1. All parameters NOT specially mentioned are measured at 12,24,48VDC input, rated load and 25°C of ambient temperature.</p> <p>2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor.</p> <p>3. Tolerance : includes set up tolerance, line regulation and load regulation.</p> <p>4. The power supply is considered a component which will be installed into a final equipment. The final equipment must be re-confirmed that it still meets EMC directives.</p>									

Mechanical Specification


Case No. 901 Unit:mm




Terminal Pin. No Assignment

Pin No.	Assignment	Pin No.	Assignment
1	DC INPUT V+	4	DC OUTPUT -V
2	DC INPUT V-	5	DC OUTPUT +V
3	FG \perp		

Derating Curve



Static Characteristics(SD-50C-24V)



Quality Engineering Test Report

SERIES: SD-50B 50W DC-DC SINGLE OUTPUT SWITCHING POWER SUPPLY

SAMPLE: A. SD-50B-5 5V / 10A
B. SD-50B-12 12V / 4.2A
C. SD-50B-24 24V / 2.1A

NO	TEST ITEM	TEST CONDITION / SPECIFICATION	RESULT	VERDICT
1	DC INPUT VOLTAGE RANGE	I/P : TESTING SPEC : 19~36VDC O/P : FULL LOAD	A:15.4~36VDC	P
2	LINE REGULATION	I/P : 19~36VDC SPEC : A:±0.5% O/P : FULL LOAD B:±0.3% C:±0.2%	A: -0%~+0% B: -0%~+0% C:-0.03%~+0%	P
3	LOAD REGULATION	I/P : 24VDC SPEC : A:±0.5% O/P : MIN. TO FULL LOAD B:±0.3% C:±0.2%	A:-0.12%~+0.12% B: -0%~+0.05% C:-0.03%~+0%	P
4	OUTPUT VOLTAGE TOLERANCE	I/P : 19~36VDC SPEC : A:±2% O/P : MIN. TO FULL LOAD B:±1% C:±1%	A:-0.12%~+0.12% B: -0%~+0.05% C:-0.03%~+0%	P
5	RIPPLE&NOISE	I/P : 24VDC SPEC : A:100mVp-p O/P : FULL LOAD B:120mVp-p C:150mVp-p	A:25mV B: 8mV C: 8mV	P
6	DC INPUT CURRENT	I/P : 24VDC SPEC : 3A O/P : FULL LOAD	A:2.75A	P
7	MAX. INRUSH CURRENT	I/P : 24VDC SPEC : NONE O/P : FULL LOAD	A:38.26A	P
8	O/P VOLTAGE ADJ. RANGE	I/P : 24VDC SPEC : A:4.5~5.5V O/P : MIN. LOAD B:11~16V C:23~30V	A:4.32~6.21V B:9.47~16.30V C:19.5~33.68V	P
9	SET UP TIME	I/P : 24VDC SPEC : 2.5S O/P : FULL LOAD	A:2000.3mS	P
10	EFFICIENCY	I/P : 24VDC SPEC : A:73% O/P : FULL LOAD B:75% C:80%	A:77.15% B:79.44% C:82.07%	P
11	OVER LOAD PROTECTION	I/P : 24VDC SPEC : 105%~150% O/P : TESTING	A:130% B:116.9% C:114.7%	P
12	OVER VOLTAGE PROTECTION	I/P : 24VDC SPEC : A:5.75V~6.75V O/P : TESTING B:16.8V~20V C:31.5V~37.5V	A:6.12V B:18.17V C:35.17V	P
13	INSULATION RESISTANCE	SPEC : I/P-O/P 500VDC/100M Ohms MIN. I/P-FG 500VDC/100M Ohms MIN. O/P-FG 500VDC/100M Ohms MIN.	A: I/P-O/P : >100M Ohms I/P-FG : >100M Ohms O/P-FG : >100M Ohms	P
14	DIELECTRIC / WITHSTAND VOLTAGE	SPEC : I/P- O/P : 1500VAC/ 1 min (10mA CUT-OFF) I/P- FG : 1500VAC/ 1 min (10mA CUT-OFF) O/P- FG : 500VAC/ 1 min (10mA CUT-OFF)	A: I/P-O/P : <2.24mA I/P-FG : <2.36mA O/P-FG : <3.34mA	P
15	BURN-IN TEST	I/P : 24VDC O/P:FULL LOAD TA : 25.7 °C BURN-IN DURATION : 4 hrs	NON BREAK	P
16	ENVIRONMENT TEST (SAMPLE A:)	1.LOW TEMPERATURE TEST I/P : 18.1 VDC O/P : FULL LOAD AMBIENT TEMPERATURE : -10°C	AFTER 2 hrs POWER ON OK	P
		2.HIGH AMBIENT TEMPERATURE FULL LOAD TEST I/P : 37VDC O/P : FULL LOAD AMBIENT TEMPERATURE : 45.4°C	AFTER 4 hrs NON BREAK	

NO	TEST ITEM	TEST CONDITION / SPECIFICATION	RESULT	VERDICT																												
17	TEMPERATURE RISE TEST T rise OF PARTS	<p>A: I/P : 24VDC AFTER 4 hr BURN-IN O/P : FULL LOAD TA : 24.6°C</p> <table border="1"> <thead> <tr> <th>POSITION</th> <th>P/N</th> <th>TEMP</th> <th>T rise</th> </tr> </thead> <tbody> <tr> <td>Q1</td> <td>MAIN TRANSISTOR</td> <td>53.2°C</td> <td>28.6°C</td> </tr> <tr> <td>T1</td> <td>MAIN TRANSFORMER</td> <td>62.3°C</td> <td>37.7°C</td> </tr> <tr> <td>D11</td> <td>O/P DIODE</td> <td>62.5°C</td> <td>37.9°C</td> </tr> <tr> <td>C34</td> <td>O/P FILTER CAPACITOR</td> <td>53.0°C</td> <td>28.4°C</td> </tr> <tr> <td>L1</td> <td>O/P CHOCK</td> <td>59.3°C</td> <td>34.7°C</td> </tr> <tr> <td>C5</td> <td>I/P FILTER CAPACITOR</td> <td>49.3°C</td> <td>24.7°C</td> </tr> </tbody> </table>	POSITION	P/N	TEMP	T rise	Q1	MAIN TRANSISTOR	53.2°C	28.6°C	T1	MAIN TRANSFORMER	62.3°C	37.7°C	D11	O/P DIODE	62.5°C	37.9°C	C34	O/P FILTER CAPACITOR	53.0°C	28.4°C	L1	O/P CHOCK	59.3°C	34.7°C	C5	I/P FILTER CAPACITOR	49.3°C	24.7°C		P
POSITION	P/N	TEMP	T rise																													
Q1	MAIN TRANSISTOR	53.2°C	28.6°C																													
T1	MAIN TRANSFORMER	62.3°C	37.7°C																													
D11	O/P DIODE	62.5°C	37.9°C																													
C34	O/P FILTER CAPACITOR	53.0°C	28.4°C																													
L1	O/P CHOCK	59.3°C	34.7°C																													
C5	I/P FILTER CAPACITOR	49.3°C	24.7°C																													
18	LIFE CYCLE	<p>A: SUPPOSE C34 IS THE MOST CRITICAL COMPONENT I/P : 24VDC O/P : FULL LOAD Ta : 25°C Tc34 : 53.4°C Life: 42971 hrs I/P : 24VDC O/P : FULL LOAD Ta : 45.4°C Tc34 : 56.2°C Life: 35390 hrs</p>		P																												
19	CRITICAL COMPONENT RECORD (FOR QC INSPECTION REFERENCE ONLY)	<p>A: FUSE : 6.3AL/250V INPUT DIODE : 1N5401 LINE FILTER : LS TF-096B EE-25 TRANSFOMER : CK TF-332 EI-28 POWER SWITCHER : 2SK889 TO-220 OUTPUT DIODE : S305C4M OUTPUT CAPACITOR : 2200uF/16V(v) 105°C HL INPUT CAPACITOR : N.C.C 330uF/100V KMF 105°C P.C.B : SD-50 FR-4 2 OZ DS</p>																														
DATE	SAMPLE	TEST RESULT	TEST	APPROVAL																												
980421	SD-50B	PASS	H.C.LIOU	Max Lin																												