

Our products make your products perform!

DeoxIT® L260Np Mechanical & Electrical Grease

Part No.: L260Np

Formulation: 99.5% DeoxIT® L260Np Lithium Grease
 0.5% Deoxidizing agent
 No particles



Container Size:

L260-N2C	100%	cartridge	50 g
L260-N1	100%	jar	28 g
L260-N8	100%	jar	226 g
L260-N35	100%	pail	16 Kg



Product Description:

Manufactured in semi-solid form for use as a combination cleaning, deoxidizing, protecting and lubricating preparation. Greases protect against oxidation (galvanic corrosion) and are free of mineral acids, sulphurs, alkalis and other noxious components aggressive to metals. DeoxIT® Greases improve performance of electrical contacts and mechanical components that require precise lubrication.

Particles: None. Maximum lubrication for relatively clean surfaces.
 Temperature range: -40 to +260°C.

Features/Benefits:

100% Grease - Safe on Plastics.

Lithium-based preparation.

Good lubrication, excellent wear resistance, excellent pressure resistance, excellent oxidation (galvanic corrosion) protection, high dripping-point characteristics.

USES:

Electrical:

Antenna connections, battery terminals, Buss bars, commutators, conductor rails, conductors, contactors, disconnects, drying & processing equipment, high amperage/high voltage applications, industrial electrical equipment (lifts, cranes, robotics, etc.), power tools, relays & switches (heavy duty, knife, step, rotary), etc.

Mechanical:

Bearings (all types), doors (closures), drives (chain/sprockets), hatch closures, O-rings and seals, linear motion systems, plugs (threaded holes), rack & pinion assemblies, screw devices (jacks, rails), slide bushings, sliding parts, tracks/guides/rails, threaded closures, worm gears, etc.

SPECS: (Base material)

	TYPE: M260	L260	TYPE: M260	L260
Flow Point, min.	-30°C	-30°C	Oil Type	Mineral Synthetic Blend
Viscosity @ 100°F, SUS763	785	Soap TypeNone Lithium-12 Hydroxy
ASTM Dropping Point260°C	285°C	Soap %,	9.52
Specific Gravity @ 20°C	1.85	1.87	ASTM - Penetration280 295
Flash Point300°C	300°C	NLGI	2 2
¹ Lowest/Best Operating Temp. (general)	-30°C	-30°C	DeoxidizerYes Yes
¹ Highest Operating Temp. (continuous duty) ...	200°C	200°C	Oxidation InhibitorYes Yes
Acid & Neutralization No. (mg KOH/g)	1.15	1.17	Corrosion InhibitorYes Yes
Saponification No. (mg KOH/g)	2.79	2.81	TextureButtery Short Fiber
Electrical Conductivity (27°C) (10 ⁻¹² ohm ⁻¹ cm ⁻¹) ..	0.17	0.17	Color	Amber Amber
² Dielectric Constant E _r	2.751	3.236		
(Tan δ (10 ⁻⁴)				
² Dielectric Strength E _d	(kV/cm) 54.6	45.9		
² Specific Insulation Resistance D (10 ¹² ohm-cm) ..	5.7	5.9		
	+50/-03	+50/-03		

¹ Temperatures are conservative values for reference only.

² **NOTE:** All values are relative to an ambient temperature of 26 to 28°C (approx. 80°F). Dielectric strength value is a statistical average taken from 10 measurings. Voltage measurement taken with 0.5% accuracy. Tests conducted on base material only. Greases with particles may have different measurements.

Other Formulations:

L260Cp	Lithium formulation with copper particles
L260Ap	Lithium formulation with aluminum particles
L260Gp	Lithium formulation with graphite particles
L260Qp	Lithium formulation with quartz particles
L260GQp	Lithium formulation with graphite and quartz particles
M260Np	Mineral based with no particles
M260Cp	Mineral based with copper particles

Shipping Information:

Hazardous: No

Other Information:

RoHS Compliant: YES

L260 MSDS Link:

Product Sheet: <http://store.caig.com/app/site/media/sitemedia.nl/id.778/f>

MANUFACTURER DISCLAIMER:

To the best of our knowledge, the information contained herein is accurate. However, neither CAIG Laboratories, Inc., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. All materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist. All service performed on internal parts and equipment should be provided by qualified technicians.

Contact Information:



North America

CAIG Laboratories, Inc.
12200 Thatcher Court
Poway, CA 92064 USA
Tel: (858) 486-8388
Fax: (858) 486-8398

Website www.caig.com
www.deoxit.com

General email info@caig.com

Technical email tech@caig.com