




AD4010 SERIES



External Dimensions



Frame: Plastic (UL:94V-0)
 Impeller: Plastic (UL:94V-0)
 Bearing: Ball, Sleeve, 1B1S, Hypro bearing
 Lead wire: UL1007AWG26
 VOLTAGE AVAILABLE: 5V, 12V, 24V


Specifications(Nominal)

* Noise is measured at the distance of one (1) meter from the axis of intake

Bearing type: ○=Ball =Sleeve()= 1B1S=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)		Maximum Pressure (InAq) (mmAq)		*Noise Level (dB/A)	Weight (g)
40x40x10	AD0405LB-G70	○ * ○ ●	5	0.07	0.35	4200	0.132	4.70	0.061	1.52	14.0	
	AD0405MB-G70	○ * ○ ●	5	0.11	0.55	4800	0.181	5.70	0.078	1.98	20.0	
	AD0405HB-G70	○ * ○ e	5	0.18	0.80	8000	0.189	6.70	0.102	2.54	25.0	
	A00412LB-G70	○ * ○ e	12	0.06	0.72	4200	0.132	4.70	0.061	1.52	14.0	
	AD0412MB-G70	@liE○e	12	0.06	0.72	4800	0.181	5.70	0.078	1.98	20.0	17.0
	A00412HB-G70	@liE○e	12	0.09	1.08	6000	0.189	6.70	0.102	2.54	25.0	
	A00424LB-G70	○ * ○ e	24	0.03	0.72	4200	0.132	4.70	0.061	1.52	14.0	
	A00424MB-G70	○ * ○ e	24	0.04	0.96	4800	0.181	5.70	0.078	1.98	20.0	
A00424HB-G70	@liE○e	24	0.06	1.44	6000	0.189	6.70	0.102	2.54	25.0		

Specifications subject to change without notice.



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓	✓	✓	✓		✓					✓

·safety approvals

✓	✓		✓	✓