

Our products make your products perform!

DeoxIT® GOLD GN5 Spray Contact Cleaner, Enhancer & Protector

Part No.: GN5S-6N

Container Size: 163 g

Product Description:

Contact cleaner, conditioner, enhancer, lubricant and protectant for PLATED metal surfaces. Improves conductivity, maintains optimum signal quality, reduces fretting & dendrite corrosion, and stabilizes connections between similar and dissimilar metals. DeoxIT® GOLD also reduces wear and abrasion, arcing, RFI and intermittent connections and improves connector performance/reliability. Ideal for gold plated surfaces. On oxidized surfaces, pre-treat with DeoxIT® contact cleaner. Temperature range: -45 to +240°C.



Features/Benefits:

Spray - Quick Dry, Non Drip and Safe on Plastics.

DeoxIT® GOLD G100L concentrate has approximately 0.5% chemical cleaning action. Excellent conductivity enhancing, excellent protection, minimum cleaning/deoxidizing, no ozone depletion.

Prevent dendrite and fretting corrosion

Reduces intermittent connections, arcing, RFI, wear and abrasion.

Cleaner Audio - Clearer Video - Reliable Data.

Formulation:

5% DeoxIT® GOLD G100L (formerly ProGold)
 70-74% 1,1,1,3,3-PENTAFLUOROPROPANE (460-73-1)
 1-5% isopropyl alcohol (67-63-1)
 20% hydrocarbon propellant (75-28-5, 74-98-6)

DeoxIT® - Product Selection Guide

| | DeoxIT® | DeoxIT® GOLD | DeoxIT® GOLD GxL | DeoxIT® GOLD Gx2 | DeoxIT® SHIELD | DeoxIT® FaderLube |
|--|-----------|--------------|------------------|------------------|----------------|-------------------|
| New Surfaces | | ✓ | ✓ | ✓ | ✓ | ✓ |
| * In Service / Used | ✓ | | | | | ✓ |
| Gold surfaces | | ✓ | ✓ | ✓ | | |
| Oxidation / corrosion visible | ✓ | | | | | |
| Conductive plastics | | | | | | ✓ |
| ** Outdoor / Severe environments | ✓ | | | | | ✓ |
| Deoxidizing / cleaning properties | 20% | 0.1% | 0.1% | 0.0% | 0.0% | 0.0% |
| Metal / Plastic surfaces | Yes | Yes | Yes | Yes | Yes | |
| Plastics compatibility | Excellent | Excellent | Excellent | Excellent | Excellent | Excellent |
| Temperature range (°C) | -34/200 | -45/240 | -45/310 | -45/500 | -34/210 | -26/150 |
| Stationary & moving surfaces | Yes | Yes | Yes | Yes | Yes | Yes |
| Seals & protects base metals | Good | Excellent | Excellent | Excellent | Good | No |

- ✓ All products are Nonflammable and RoHS Compliant
- * In Service: Clean with DeoxIT®. For added protection, follow with DeoxIT® GOLD (indoors), DeoxIT® SHIELD (outdoors) or DeoxIT® Grease (additional barrier).
- ** Severe environments: Pre-clean with DeoxIT®. Follow with DeoxIT® SHIELD or DeoxIT® Grease.

DeoxIT® - Spray Selection Guide

| Product Series | FP | QD | NF | PC | VOC |
|---|----|----|----|----|-----|
| Standard - 5% solution D5S-6, D5MS-15, G5S-6, G5MS-15, S5S-6, S5MS-15, F5S-6, F5MS-15 | ✓ | | | ✓ | 95 |
| N Series - 5% solution DN5S-6N, DN5MS-15, GN5S-6N, GN5MS-15, SN5S-6, SN5MS-15 | | ✓ | ✓ | ✓ | 20 |
| X Series - 5% solution GX5S-6N | | ✓ | ✓ | ✓ | 20 |
| 100 Series - 100% solution D100S-2, G100S-2, F100S-2 | | | ✓ | ✓ | 0 |

FP = Flushing properties QD = Quick dry / non drip NF = Nonflammable
 PC = Plastics compatibility VOC = VOC (%)

Other Applicators:

| | | | | |
|--------------|------|------------------|------------|--------------|
| G5S-6 | 5% | spray | 142 g | flammable |
| G5MS-15 | 5% | mini-spray | 14 g | flammable |
| GN5MS-15 | 5% | spray | 14 g | nonflammable |
| G100S-2 | 100% | spray | 57g | nonflammable |
| G100P | 100% | pen | 6 mL | nonflammable |
| G100L-P6C | 100% | pen oiler | 6 mL | nonflammable |
| K-G1W | 100% | wipes | individual | nonflammable |
| G100L-2DB | 100% | brush | 7.4 mL | nonflammable |
| G100L-25C | 100% | needle dispenser | 25 mL | nonflammable |
| G100L (bulk) | 100% | bottle/drum | assort. | nonflammable |
| G5L (bulk) | 5% | bottle/drum | assort. | flammable |

DeoxIT® Essential Reference:

DeoxIT® - *Brings old systems back to life!*

DeoxIT® GOLD - *Maintains new system performance!*

DeoxIT® SHIELD - *Maintains new system performance for severe environments!*

Shipping Information:

| | |
|------------|----------|
| Hazardous: | Y - ORMD |
| VOC (%): | >25% |

Other Information:

| | |
|-----------------------------|---|
| RoHS Compliant: | YES |
| GN5S-6N MSDS Link: | http://store.caig.com/app/site/media/sitemedia.nl/id.1539/f |
| DeoxIT® GOLD Product Sheet: | http://store.caig.com/app/site/media/sitemedia.nl/id.774/f |
| MentorCard Link: | http://www.deoxit.com/pdf/MentorCards_av.pdf |
| WHY DeoxIT® is Different: | http://www.deoxit.com/pdf/why_deoxit.pdf |

MANUFACTURER DISCLAIMER:

To the best of our knowledge, the information contained herein is accurate. However, neither CAIG Laboratories, Inc., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. All materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist. All service performed on internal parts and equipment should be provided by qualified technicians.

Contact Information:



North America

CAIG Laboratories, Inc.
12200 Thatcher Court
Poway, CA 92064 USA
Tel: (858) 486-8388
Fax: (858) 486-8398

Website

www.caig.com
www.deoxit.com

General email

info@caig.com

Technical email

tech@caig.com