


START **1** Resistor - Weerstand - Résistance - Widerstand - Resistencia - Motstand - Vastus - Resistenze



◇R1... R4: 470

(Yellow, Purple, Brown) -(Geel, Paars, Bruin) -(Jaune, Violet, Brun) -(Gelb, Violet, Braun) -(Gul, Lila, Bruin) -(Keltainen, Purppura, Punainen) -(Amarillo, Morado, Marrón) -(Amarelo, Violeta, Castanho) -(Giallo, Viola, Marrone)

◇R5, R6: 4K7


(Yellow, Purple, Red) -(Geel, Paars, Rood) -(Jaune, Violet, Rouge) -(Gelb, Violet, Rot) -(Gul, Lila, Röd) -(Keltainen, Purppura, Punainen) -(Amarillo, Morado, Rojo) -(Amarelo, Violeta, Encarnado) -(Giallo, Viola, Rosso)

◇R7: 47

(Yellow, Purple, Black) -(Geel, Paars, Zwart) -(Jaune, Violet, Noir) -(Gelb, Violet, Schwarz) -(Gul, Lila, Svart) -(Keltainen, Purppura, Musta) -(Amarillo, Morado, Negro) -(Amarelo, Violeta, Preto) -(Giallo, Viola, Nero)


2 DIODE

◇D1: BAT85
Watch the polarity!
Att. la polarité!




3 DIODE


◇D2: 1N4007
Watch the polarity!
Att. la polarité!



4 ◇SW1...SW4




5 IC Socket - IC voet - Support de CI - IC Fuß - Sopotro del CI - IC Socket - Mikropiiranta - IC sokkel - Zoccolo IC




6 Capacitor

◇C1:1µF (105)




7 LED

◇LD1... LD4: 3mm




8 Transistor

◇T1: BC547




9 LS

◇LS1: TV3





10




11 IC - CI

◇IC1



START:



SELECT:

