

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached material are the property of its owner.



RELIABILITY PREDICTION

Model : TP-150

Data:2002-10-16


Style	Part Type	Q'ty	λ_g	π_Q	λ_{eg}	%
9.1	Resistor-Film, Insulated (RL)	9	0.003700	10	0.333000	5.383
9.1	Resistor-Film, Chip (RM)	59	0.003700	10	2.183000	35.290
9.1	Resistor-Wirewound Power (RW)	2	0.008500	10	0.170000	2.748
9.1	Resistor-Film, Variable (RVC)	1	0.040000	10	0.400000	6.466
9.1	Resistor-Thermistor (RTH)	1	0.001400	10	0.014000	0.226
10.1	Capacitor-Metal, Plastic (CH)	8	0.000510	10	0.040800	0.660
10.1	Capacitor-Ceramic(Gen.) (CK)	15	0.001700	10	0.255000	4.122
10.1	Capacitor-Ceramic chip (CDR)	17	0.003500	10	0.595000	9.619
10.1	Capacitor-Aluminum Dry (CE)	14	0.001300	10	0.182000	2.942
6.1	Diode-Gen. Purpose Analog	3	0.003600	8	0.086400	1.397
6.1	Diode-Switching	14	0.000940	8	0.105280	1.702
6.1	Diode-Fast Recovery Power Rectifier	2	0.023000	8	0.368000	5.949
6.1	Diode-Power Rectifier / Schottky Power	10	0.002800	8	0.224000	3.621
6.1	Diode-Voltage Ref/Reg. (Avalanche & Zener)	2	0.003300	8	0.052800	0.854
6.1	Diode-Transient Suppressor/Varistor	1	0.002900	8	0.023200	0.375
6.10	Diode-Thyristor/SCR	1	0.002500	8	0.020000	0.323
6.3	Transistor-NPN/PNP	2	0.000150	8	0.002400	0.039
6.4	Transistor-MOSFET	2	0.014000	8	0.224000	3.621
6.11	OPTO-isolator	2	0.027000	8	0.432000	6.984
6.11	OPTO-Emitter	1	0.000470	8	0.003760	0.061
5.1	Linear Microcircuits	3	0.009500	10	0.285000	4.607
11.1	Transformer Switching	1	0.000610	3	0.001830	0.030
11.2	Coil Fixed inductor or choke	5	0.000032	3	0.000480	0.008
15.1	Connector- Rectangular	1	0.050000	2	0.100000	1.617
17.1	Single Connections-Reflow solder	430	0.000069	1	0.029670	0.480
17.1	Fuses Clip-Clip Termination	2	0.000120	1	0.000240	0.004
22.1	Fuses	1	0.010000	1	0.010000	0.162
16.1	Plated Through Hole Circuit Boards	1	0.022000	2	0.044000	0.711

Total Failure rate:	6.185860	100%
----------------------------	----------	------

• Data Base: MIL-HDBK-217F ,Notice 2, Parts Count MTBF: 161659.01 hrs

• Env.: GB

• Exclude: FAN

Approved by:  . Compiled by: 