

*General purpose prototyping circuit board for analog and digital use.*

## Features


- A higher quality prototyping board with the traditional stripboard pattern. Tracks run the length of the board.
- StripBoard-2 uses a high-quality FR4 glass epoxy board. It has better stability and moisture resistance than boards using phenolic or SRBP (synthetic resin bonded paper) to avoid warping.
- 0.1" hole spacing for DIP integrated circuits and headers.
- BusBoard Size2 is 1/2 the size of a standard 3U size VME board.
- Four mounting holes provided.

## Specifications

- Etched FR4 glass-epoxy circuit board.
- 1oz/ft<sup>2</sup> copper with an anti-tarnish coating for easy soldering.  
Lead free and RoHS compatible.
- Holes are drilled on 0.1" (2.54mm) centers.
- 0.037" (0.94mm) holes sized for ICs or square post headers.
- 31 x 39 holes (31 strips).  
Four 0.125" mounting holes.
- Size 2 = 100 x 80mm (3.94 x 3.15in),  
1/16" thick (1.6mm)


**Order Part# ST2**

## ST2 Board Layout (actual size)



ST2 – StripBoard Size 2

## ST2 Board Photo



**ST2 – StripBoard Size 2,  
Single Sided PCB, Bottom Side**

## Board Dimensions

