

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Quality Engineering Test Report

SERIES: MPS-45 45W WATTS SIGLE OUTPUT SWITCHING POWER SUPPLY OPEN FRAME TYPE

SAMPLE: A.MPS-45-3.3 :3.3V/8A D.MPS-45-12 :12V/3.7A G.MPS-45-24 :24V/1.9A
B.MPS-45-5 :5V/8A E.MPS-45-13.5:13.5V/3.3A H.MPS-45-27 :27V/1.7A
C.MPS-45-7.5 :7.5V/5.4A F.MPS-45-15 :15V/3A I.MPS-45-48 :48V/1A

NO	TEST ITEM	TEST CONDITION / SPECIFICATION	RESULT	VERDICT
1	AC INPUT VOLTAGE RANGE	I/P:TESTING SPEC:90-264VAC O/P:FULL LOAD	A:50.875VAC~264VAC	P
2	LINE REGULATION	I/P:90-264VAC SPEC: A: ±1% O/P:FULL LOAD B: ±1% C: ±1% D: ±1% E: ±1% F: ±1% G: ±1% H: ±1% I: ±1%	A: -0.00% ~ +0.00% B: +0.12% ~ +0.12% C: -0.00% ~ +0.00% D: +0% ~ +0.05% E: +0.00% ~ +0.00% F: +0.00% ~ +0.04% G: +0.00% ~ +0.0% H: +0.00% ~ +0.00% I: -0.01% ~ +0.00%	P
3	LOAD REGULATION	I/P:230VAC SPEC: A: ±3% O/P: B: ±3% MIN. TO FULL LOAD C: ±3% D: ±2% E: ±2% F: ±2% G: ±2% H: ±2% I: ±2%	A: +0.179% ~ +0.179% B: -0% ~ +0.24% C: -0.24% ~ +0.08% D: -0.05% ~ +0.05% E: -0.08% ~ +0.04% F: -0.00% ~ +0.00% G: -0.025% ~ +0.025% H: -0.00% ~ +0.00% I: -0.01% ~ +0.00%	P
4	OUTPUT VOLTAGE TOLERANCE	I/P:90-264VAC SPEC: A: ±3% O/P: B: ±3% MIN. TO FULL LOAD C: ±3% D: ±2% E: ±2% F: ±2% G: ±2% H: ±2% I: ±2%	A: +0.00% ~ +0.179% B: -0.36% ~ +0.00% C: -0.33% ~ +0.00% D: -0.11% ~ +0.08% E: -0.14% ~ 0.00% F: -0.04% ~ +0.00% G: -0.05% ~ +0.025% H: -0.048% ~ +0.00% I: -0.04% ~ +0.00%	P
5	RIPPLE & NOISE	I/P:230VAC SPEC: A:80mV O/P: FULL LOAD B:100mV C:100mV D:100mV E:100mV F:100mV G:100mV H:100mV I:100mV	A: 13mV B: 14mV C: 7mV D: 13mV E: 7mV F: 16mV G: 9mV H: 5mV I: 10mV	P

[NEXT](#)

NO	TEST ITEM	TEST CONDITION / SPECIFICATION	RESULT	VERDICT
6	AC INPUT CURRENT	I/P:230VAC SPEC: 0.7A O/P:FULL LOAD	<u>A:0.381A</u>	P
7	MAX. INRUSH CURRENT	I/P:230VAC SPEC: 40A O/P:FULL LOAD	<u>A:27.41A</u>	P
8	O/P VOLTAGE ADJ.RANGE	I/P:230VAC SPEC: $\pm 10\%$ O/P:MIN. LOAD A:2.97V~3.63V B:4.5V~5.5V C:6.75V~8.25V D:10.8V~13.2V E:12.15V~14.85V F:13.5V~16.5V G:21.6V~26.4V H:24.3V~29.7V I:43.2V~52.8V	A:2.701V~4.016V B:4.3V~6.03V C:6.6V~9.01V D:10.155V~13.659V E:11.25V~16.29V F:12.43V~17.518V G:20.04V~27.33V H:22.28V~32.74V I:40.21V~55.42V	P
9	SET UP TIME	I/P:230VAC SPEC:800ms O/P:FULL LOAD	<u>A:280.26mS</u>	P
10	HOLD UP TIME	I/P:230VAC SPEC:20mS O/P:FULL LOAD	<u>A:120.3mS</u>	P
11	EFFICIENCY	I/P:230VAC SPEC: A:65% O/P: FULL LOAD B:72% C:75% D:76% E:76% F:77% G:78% H:78% I:78%	A: <u>66.69%</u> B: <u>74.19%</u> C: <u>76.89%</u> D: <u>77.69%</u> E: <u>78.62%</u> F: <u>79.95%</u> G: <u>81.3%</u> H: <u>81.97%</u> I: <u>82.72%</u>	P
12	OVER LOAD PROTECTION	I/P:230VAC SPEC: A: 36~55W O/P: TESTING B: 53~75W C: 53~75W D: 53~75W E: 53~75W F: 53~75W G: 53~75W H: 53~75W I: 53~75W	A: <u>45.86W</u> B: <u>66.29W</u> C: <u>66.38W</u> D: <u>68.42W</u> E: <u>63.86W</u> F: <u>65W</u> G: <u>60.89W</u> H: <u>68.25W</u> I: <u>66.47W</u>	P
13	OVER VOLTAGE PROTECTION	I/P:230VAC SPEC: 115%~135% O/P:TESTING A : 3.795V~4.455V B : 5.75V~6.75V C : 8.625V~10.125V D : 13.8V~16.2V E : 15.525V~18.225V F : 17.25V~20.25V G : 27.6V~32.4V H : 31.05V~36.45V I : 55.2V~64.8V	A: <u>4.3V</u> B: <u>6.06V</u> C: <u>9.45V</u> D: <u>15.1V</u> E: <u>16.6V</u> F: <u>18.4V</u> G: <u>31.8V</u> H: <u>33.4V</u> I: <u>56.52V</u>	P

[PREVIOUS](#)

[NEXT](#)

NO	TEST ITEM	TEST CONDITION / SPECIFICATION	RESULT	VERDICT																																								
14	GROUND LEAKAGE CURRENT	I/P:240VAC SPEC: L-FG--<0.3mA N-FG--<0.3mA	B: L-FG: 0.02mA N-FG:0.02mA	P																																								
15	INSULATION RESISTANCE	SPEC: O/P-FG 500VDC/100MOhms MIN. I/P-O/P 500VDC/100MOhms MIN. I/P-FG 500VDC/100MOhms MIN.	A: O/P-FG >100MOhms I/P-O/P >100MOhms I/P-FG >100MOhms	P																																								
16	DIELECTRIC / WITHSTAND VOLTAGE	SPEC: I/P - O/P: 4000VAC/ 1 sec I/P - FG: 1500VAC/ 1 sec O/P - FG : 500VAC/1sec	A: I/P-O/P :2.1mA I/P-FG :1.3mA O/P- FG 2.9mA	P																																								
17	BURN-IN TEST	I/P: 230VAC O/P:FULL LOAD TA:25°C BURN-IN DURATION :2hrs	A: NON BREAK	P																																								
18	ENVIRONMENT TEST (SAMPLE B)	1.LOW TEMPERATURE TEST I/P:230VAC O/P:FULL LOAD AMBIENT TEMPERATURE:-10.1°C	AFTER 3.5 hrs POWER ON <u>OK</u>	P																																								
		2.HIGH AMBIENT TEMPERATURE FULL LOAD TEST I/P:230VAC O/P:FULL LOAD AMBIENT TEMPERATURE :40.5°C	AFTER 5 hrs NON BREAK																																									
		3.High Humidity High Voltage On/Off Test I/P:267VAC O/P:FULL LOAD AMBIENT TEMPERATURE : 25 °C AMBIENT HUMIDITY: 95 %	AFTER 18 hrs POWER ON NON BREAK																																									
19	TEMPERATURE RISE TEST Trise OF PARTS	I/P :230VAC O/P :FULL LOAD AFTER 3 hrs BURN-IN TA:30.4°C	<table border="1"> <thead> <tr> <th>POSITION</th> <th>P/N</th> <th>TEMP</th> <th>Trise</th> </tr> </thead> <tbody> <tr> <td>BD1</td> <td>BRIDGE DIODE</td> <td>67.4C</td> <td>37°C</td> </tr> <tr> <td>Q1</td> <td>MAIN TRANSISTOR</td> <td>74.6C</td> <td>44.2°C</td> </tr> <tr> <td>T1</td> <td>MAIN TRANSFORMER COIL</td> <td>78.0°C</td> <td>47.6°C</td> </tr> <tr> <td>D40</td> <td>O/P DIODE</td> <td>95.8°C</td> <td>65.4°C</td> </tr> <tr> <td>C5</td> <td>I/P FILTER CAPACITOR</td> <td>81.3°C</td> <td>50.9°C</td> </tr> <tr> <td>C41</td> <td>O/P FILTER CAPACITOR</td> <td>58.8°C</td> <td>28.4°C</td> </tr> <tr> <td>T1</td> <td>MAIN TRANSFORMER CORE</td> <td>84.0°C</td> <td>53.6°C</td> </tr> <tr> <td>D1</td> <td>CLAMP DIODE</td> <td>91.2°C</td> <td>60.8°C</td> </tr> <tr> <td>LF1</td> <td>LINE FILTER</td> <td>49.3°C</td> <td>18.9°C</td> </tr> </tbody> </table>	POSITION	P/N	TEMP	Trise	BD1	BRIDGE DIODE	67.4C	37°C	Q1	MAIN TRANSISTOR	74.6C	44.2°C	T1	MAIN TRANSFORMER COIL	78.0°C	47.6°C	D40	O/P DIODE	95.8°C	65.4°C	C5	I/P FILTER CAPACITOR	81.3°C	50.9°C	C41	O/P FILTER CAPACITOR	58.8°C	28.4°C	T1	MAIN TRANSFORMER CORE	84.0°C	53.6°C	D1	CLAMP DIODE	91.2°C	60.8°C	LF1	LINE FILTER	49.3°C	18.9°C	P
POSITION	P/N	TEMP	Trise																																									
BD1	BRIDGE DIODE	67.4C	37°C																																									
Q1	MAIN TRANSISTOR	74.6C	44.2°C																																									
T1	MAIN TRANSFORMER COIL	78.0°C	47.6°C																																									
D40	O/P DIODE	95.8°C	65.4°C																																									
C5	I/P FILTER CAPACITOR	81.3°C	50.9°C																																									
C41	O/P FILTER CAPACITOR	58.8°C	28.4°C																																									
T1	MAIN TRANSFORMER CORE	84.0°C	53.6°C																																									
D1	CLAMP DIODE	91.2°C	60.8°C																																									
LF1	LINE FILTER	49.3°C	18.9°C																																									
20	LIFE CYCLE	SUPPOSE C41 IS THE MOST CRITICAL COMPONENT I/P:230VAC O/P:FULL LOAD Ta:25°C Tc41:58.8°C Life: 155727 hrs I/P:230VAC O/P:FULL LOAD Ta:40°C Tc41:68.2°C Life: 57804 hrs		P																																								
21	CRITICAL COMPONENT RECORD (FOR QC INSPECTION REFERENCE ONLY)	FUSE :4A/250VAC MET BRIDGE DIODE :D3SB60 LINE FILTER :TF-484. TRANSFOMER :LS TF-757 POWER SWITCHER :2SK2545 OUTPUT DIODE :MBR1545CT OUTPUT CAPACITOR : 1000uF/16V , 105°C INPUT CAPACITOR :HITACHI 150uF/400V,85°C P.C.B :MPS-65,CEM-3 2OZ SS																																										

[PREVIOUS](#)

[NEXT](#)

DATE	SAMPLE	TEST RESULT	TEST	PROVAL
20010605	RD SAMPLE MPS-45 3.3V,5V,7.5V,12V 13.5V,24V,27V,48V	PASS	VINCENT	Max Lin
20010824	PRODUCT A107C28 MPS-45 3.3V,5V,7.5V,12V 13.5V,24V,27V,48V	PASS	VINCENT	Max Lin
20020411	PRODUCT A203B04 MPS-45 5V,12V	PASS	VINCENT	Max Lin
20020618	PRODUCT A206B03 MPS-45 15V,27V	PASS	VINCENT	Max Lin
20020919	PRODUCT A208A02 MPS-45-3.3V	PASS	VINCENT	Max Lin

[PREVIOUS](#)