





P.C.B. Socket 2.54mm (0.100")




ROHS



Straight Type




**Right Angle Type
Single Row**






Single Row P.C.B. Layout

Dimensions



Positions	2 thru 40, 4 thru 80
A	2.54 * Position No.
B	2.54 * Position No. - 2.54




Double Row P.C.B. Layout



Straight Type



Right Angle Type



Double Row

Product Specification

Material

Insulator : Glass-Filled Thermoplastic
UL94V-0 rates, Color-Black

Contact : Brass or Phosphor Bronze
Plated full gold or selected gold in
mating area, 100u" min. tin-lead on
an termination area, with entire contact
under-plated 50u" min. Nickel

Electrical

Contact Resistance : 20 milliohms
Max at 1 AMP DC.

Insulation Resistance : 5000
megohms at 500 VDC

Dielectric Withstanding Voltage :
500 VAC/rms 60Hz for 1 minute

Current Rating : 1 AMP

Volatge Rating : , 250 VAC/rms
60Hz