

**ADDA USA**  
**DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
50 X 50 X 10	AD0512MS-G90	S	12	0.08	0.96	3300	8.5	0.068	24.9	24	0,6	UL,CUL,CE		
50 X 50 X 10	AD0512HS-G70	S	12	0.09	1.08	5200	11.9	0.130	28.0	18	0	CE		
50 X 50 X 10	AD0512HS-G70(T)	S	12	0.09	1.08	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HS-G70(U)	S	12	0.09	1.08	5600	12.4	0.112	26.4	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0512HS-G90	S	12	0.08	0.96	3800	9.8	0.082	28.6	24	0	UL,CUL,CE		
50 X 50 X 10	AD0512HS-G96	S	12	0.08	0.96	3800	9.8	0.082	28.6	24	6	CE		
50 X 50 X 10	AD0524LX-G70	HYPRO	24	0.07	1.68	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524MX-G70	HYPRO	24	0.08	1.92	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524HX-G70	HYPRO	24	0.09	2.16	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524LB-G70	BALL	24	0.07	1.68	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524LB-G70(S)	1B & 1S	24	0.07	1.68	3900	9.4	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524MB-G70(S)	Bor1B1S	24	0.10	2.40	4300	10.5	0.100	24.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524MB-G90	BALL	24	0.06	1.44	3300	8.3	1.650	27.5	50	0	CE		
50 X 50 X 10	AD0524HB-G70	BALL	24	0.11	2.64	5000	11.2	0.130	26.0	18	0,6	CE		
50 X 50 X 10	AD0524HB-G70(S)	1B & 1S	24	0.09	2.16	5200	11.8	0.130	27.0	18	0,6	CE		
50 X 50 X 10	AD0524HB-G90	BALL	24	0.09	2.16	3800	9.8	0.082	28.6	50	0	CE		
50 X 50 X 10	AD0524LS-G70	S	24	0.07	1.68	3700	9.0	0.060	20.0	18	0,6	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524MS-G70	S	24	0.08	1.92	4300	10.5	0.100	24.0	18	0	UL,CUL,TUV,CE		
50 X 50 X 10	AD0524HS-G70	S	24	0.09	2.16	5000	11.2	0.130	26.0	18	0,6	UL,CUL,TUV,CE		
52 X 52 X 15	AD0505HX-D71	HYPRO	5	0.26	1.30	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0505MB-D71	BALL	5	0.16	0.80	3700	9.7	0.106	22.6	55	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HB-D70	BALL	5	0.20	1.00	4600	12.0	0.166	28.7	36	0	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HB-D71	BALL	5	0.26	1.30	4600	12.0	0.166	28.7	36	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505MS-D71	S	5	0.16	0.80	3700	9.7	0.106	22.6	36	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HS-D70	S	5	0.20	1.00	4600	12.0	0.166	28.7	55	0	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0505HS-D71	S	5	0.26	1.30	4600	12.0	0.166	28.7	36	1	CUL,UL,TUV,CE	480	46.20
52 X 52 X 15	AD0512MX-D70	HYPRO	12	0.09	1.08	3700	9.7	0.106	22.6	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512MX-D71	HYPRO	12	0.09	1.08	3700	9.7	0.106	22.6	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512MX-D72	HYPRO	12	0.09	1.08	3700	9.7	0.106	22.6	36	2	CE+	480	46.20
52 X 52 X 15	AD0512HX-D71	HYPRO	12	0.10	1.20	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HX-D76	HYPRO	12	0.10	1.20	4600	12.0	0.166	28.7	36	6	CE	480	46.20
52 X 52 X 15	AD0512LB-D70	BALL	12	0.06	0.72	2800	6.3	0.059	14.4	55	0	CE	480	46.20
52 X 52 X 15	AD0512MB-D70	BALL	12	0.09	1.08	3700	9.7	0.106	22.6	55	0,6	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512MB-D71(S)	Bor1B1S	12	0.09	1.08	3700	9.7	0.106	22.6	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512MB-D72	BALL	12	0.09	1.08	3700	9.7	0.106	22.6	36	2,3	CE	480	46.20
52 X 52 X 15	AD0512HB-D70	BALL	12	0.10	1.20	4600	12.0	0.166	28.7	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512HB-D71	Bor1B1S	12	0.10	1.20	4600	12.0	0.166	28.7	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HB-D73	Bor1B1S	12	0.10	1.20	4600	12.0	0.166	28.7	36	3,6	CE	480	46.20
52 X 52 X 15	AD0512UB-D71	BALL	12	0.11	1.32	5300	13.0	0.200	35.0	36	1	CE	480	46.20
52 X 52 X 15	AD0512UB-D72	BALL	12	0.11	1.32	5300	12.5	0.200	33.3	36	2	CE	480	46.20
52 X 52 X 15	AD0512MS-D70	S	12	0.09	1.08	3700	9.7	0.106	22.6	55	0	UL,CUL,CE	480	46.20
52 X 52 X 15	AD0512MS-D71	S	12	0.09	1.08	3700	9.7	0.106	22.6	36	1	UL,CUL,TUV,CE	480	46.20
52 X 52 X 15	AD0512HS-D70	S	12	0.10	1.20	4600	12.0	0.166	28.7	55	0	UL,CUL,CE	480	46.20

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED