


MICRO

ELECTRONIC

MSB55/DA
**BLINKING
 LED LAMPS**
 (T-1 3/4 PACKAGE)

DESCRIPTION

MSB557DA is GaAlAs red LED lamp with a 5mm red diffused lens. The built-in IC flashes the lamp on/off and can be driven directly by standard TTL and CMOS circuits, eliminating the need for external switching circuitry.



- All dimension in mm(inch)
- No Scale
- Tol. : +/-0.3mm

ABSOLUTE MAXIMUM RATINGS

Operating Temperature Range	-20 to +70°C
Storage Temperature Range	-20 to +85°C
Lead Soldering Temperature (1/16" from body)	260°C for 5 sec.
Reverse Voltage	5V

ELECTRO-OPTICAL CHARACTERISTICS (Ta=25°C)

PARAMETER	SYMBOL	MIN	TYP	MAX	UNIT	CONDITIONS
Luminous Intensity	IV	50	80		mcd	VF=3V
Emission Peak Wave Length	λ_p		660		nm	IF=20mA
Spectral Line Half Width	$\Delta\lambda$		20		nm	IF=20mA
Operating Voltage	Vopr	1.6	3.0	3.4	V	
Peak Current (1/8 duty cycle)	ICM		28		mA	VF=3V
Pulse Rate		0.6	1.0	1.8	Hz	VF=3V

MICRO ELECTRONICS LTD.

38, Hung To Road, Microtron Building, Kwun Tong, Kowloon, Hong Kong.
 Kwun Tong P.O. Box 69477 Hong Kong. Fax No. 2341 0321 Telex:43510 Micro Hx. Tel: 2343 0181-5