


Schematic



Model No.	Switching Position		
	ON	NONE	ON
T201	ON	NONE	ON
T202	ON	NONE	(ON)
T203	ON	OFF	ON
T204	(ON)	OFF	(ON)
T205	ON	OFF	(ON)
T206	ON	ON	ON
Term Comm.	2-3, 5-6	OPEN	2-1, 5-4

SPECIFICATIONS:

CONTACT RATING : 5 AMPS @ 120 V AC or 28 V DC.
 2 AMPS @ 250 V AC or 0.4VA AMPS @20 V AC or DC.
 ELECTRICAL LIFE : 6,000 make-and-break cycles at full load.
 CONTACT RESISTANCE : 10 mΩ max. initial @ 2-4 V DC.
 100 mA, for both silver and gold plated contacts.
 INSULATION RESISTANCE : 1,000 MΩ min.
 DIELECTRIC STRENGTH : 1,000 V RMS @ sea level.
 OPERATING TEMPERATURE : -30 °C to 130 °C

MATERIALS:

CASE : Diallyl phthalate (DAP)(UL-94V-0).
 ACTUATOR : ZINC ALLOY.
 BUSHING : ZINC ALLOY.
 HOUSING : Stainless steel.
 TERMINAL/CONTACT : Brass, with silver or gold plated.
 or gold over silver.
 SWITCH SUPPORT : Brass, tin plated.

GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO. 21979	GOLDSUN NO. T201T1B1A1QN
Description "MINI TOGGLE SWITCH DPDTON-ON 6P SOLDER LUGS"	
UNIT: mm	SCALE: SHEET 1 OF 1
CAS No: ERN No:	Rev. 1