



**Part # 811, 20 AWG (Solid) Tinned Copper Wire, UL Style UL 1007/ UL Style 1569, Consolidated Hook Up Wire**

**Product Construction**

20 AWG (Solid) Tinned Copper Wire

**Conductor:**

20 AWG (Solid) Tinned Copper Wire Conductor per ASTM B-33

**Insulation:**

Color coded PVC  
 Temperature: UL 1007, -40° to +80°C  
 Temperature: UL 1569, -40° to +105°C  
 Voltage Rating: 300 volts

**Applications:**

Consolidated Dual Rated UL Style 1007 and UL Style 1569 Hook-Up Wire  
 Point to point wiring  
 Internal wiring of meters, panels, electrical and electronic equipment

**Industry Approvals:**

UL Style 1007  
 UL Style 1569  
 CSA-TR-64  
 VW-1  
 RoHS Compliant  
 OSHA acceptable

**Packaging:**

1000 ft. spools  
 100 ft. spools  
 Also available on bulk reels

[Specifications](#) - [Other Information](#)

**Specifications**

<b>Gauge</b>	20 AWG
<b>Strands</b>	(Solid) Tin Copper Wire
<b>Nominal Insulation Wall</b>	0.016 in.
<b>Insulation Type</b>	PVC
<b>Nominal O.D.</b>	0.064 in.
<b>Color</b>	0-Black/1-Brown/2-Red/3-Orange/4-Yellow/5-Green/6-Blue/7-Violet/8-Gray/9-White
<b>Color Code Chart</b>	<a href="#">Chart-Hook-Up Wire</a>
<b>Insulation Temperature</b>	-40°C to +80°C / -40°C to +105 °C
<b>Voltage Rating</b>	300 V
<b>Disclaimer</b>	Terms and Conditions for the Consolidated Electronic Wire and Cable Website: Consolidated has made a very reasonable effort to ensure the accuracy of this "website" pertaining to the information, specifications and the "search" accuracy. The "website" is subject to errors and omissions. The content is subject to change without notice. This "website" is being constantly updated to correct any errors and omissions, but this does not ensure it is completely accurate. Drawings are for general reference only. Consolidated Electronic Wire & Cable is not liable for any direct, indirect, incidental or consequential damages resulting from the use of the material from this "website".

**Other Information**

<b>Approvals</b>	CSA TR-64 90°C RoHS Compliant UL 1007, UL 1569 VW-1
------------------	--------------------------------------------------------------