


### Features

- Schottky Barrier Chip
- Guard Ring Die Construction for Transient Protection
- Low Power Loss, High Efficiency
- High Surge Capability
- High Current Capability and Low Forward Voltage Drop
- For Use in Low Voltage, High Frequency Inverters, Free Wheeling, and Polarity Protection Application
- Plastic Material: UL Flammability Classification Rating 94V-0



DO-201AD		
Dim	Min	Max
A	25.40	—
B	7.20	9.50
C	1.20	1.30
D	4.80	5.30
All Dimensions in mm		

### Mechanical Data


- Case: Molded Plastic
- Terminals: Plated Leads Solderable per MIL-STD-202, Method 208
- Polarity: Cathode Band
- Weight: 1.1 grams (approx)
- Mounting Position: Any
- Marking: Type Number

### Maximum Ratings and Electrical Characteristics @ T<sub>A</sub> = 25°C unless otherwise specified


Single phase, half wave, 60Hz, resistive or inductive load.  
For capacitive load, derate current by 20%.

Characteristic	Symbol	1N5820	1N5821	1N5822	Unit
Peak Repetitive Reverse Voltage	V <sub>RRM</sub>				V
Working Peak Reverse Voltage	V <sub>RWM</sub>	20	30	40	
DC Blocking Voltage	V <sub>R</sub>				
RMS Reverse Voltage	V <sub>R(RMS)</sub>	14	21	28	V
Average Rectified Output Current (Note 1)	I <sub>O</sub>	3.0			A
@ T <sub>L</sub> = 95°C					
Non-Repetitive Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I <sub>FSM</sub>	80			A
@ T <sub>L</sub> = 75°C					
Forward Voltage (Note 2)	V <sub>FM</sub>	0.475 0.850	0.500 0.900	0.525 0.950	V
@ I <sub>F</sub> = 3.0A					
@ I <sub>F</sub> = 9.4A					
Peak Reverse Current at Rated DC Blocking Voltage (Note 2)	I <sub>RM</sub>	2.0 20			mA
@ T <sub>A</sub> = 25°C					
@ T <sub>A</sub> = 100°C					
Typical Thermal Resistance (Note 3)	R <sub>θJA</sub>	40			°C/W
	R <sub>θJL</sub>	10			
Operating and Storage Temperature Range	T <sub>j</sub> , T <sub>STG</sub>	-65 to +125			°C


- Notes:
1. Measured at ambient temperature at a distance of 9.5mm from the case.
  2. Short duration pulse test used to minimize self-heating effect.
  3. Thermal resistance from junction to lead vertical P.C.B. mounted, 0.500" (12.7mm) lead length with 2.5 x 2.5" (63.5 x 63.5mm) copper pad.




$T_L$ , LEAD TEMPERATURE (°C)  
Fig. 1 Forward Current Derating Curve



$V_F$ , INSTANTANEOUS FORWARD VOLTAGE (V)  
Fig. 2 Typical Forward Voltage Characteristics



NUMBER OF CYCLES AT 60 Hz  
Fig. 3 Peak Forward Surge Current



$V_R$ , REVERSE VOLTAGE (V)  
Fig. 4 Typical Total Capacitance