

SPARKLE POWER INC.



FSP025-DGAA1

(5V@5A)

Efficiency Level V

Adapter Power Supply

San Jose Office

1000 Rock Ave.

San Jose, CA 95131

Tel: (408) 519-8888

Fax: (408) 519-9999

Los Angeles Office

17071 Green Dr.

City of Industry, CA 91745

Tel: (626) 839-7180

Fax: (626) 839-3395

sparkle@sparklepower.com

www.sparklepower.com

03/24/2011

Efficiency Testing Criteria

The Product Meet	Regulation	Output Power	Average Efficiency in Active Mode	Maximum Power in No Load	Total Harmonic Distortion
	Energy Star EPS2.0	$1W \leq P_o \leq 49W$	80.24%	$\leq 0.3W$	THD, V <2%
	ErP Lot 7 Tier2	$1W \leq P_o \leq 51W$	80.24%	$\leq 0.3W$	THD, V <2%

Table of Content

Section	
1.0	General Description And Scope----- (3)
2.0	Connector Pin Designations----- (3)
3.0	Output Electrical Requirements----- (3)
3.1	Output Rating----- (3)
3.2	Short Circuit Protection----- (3)
3.3	Over Current Protection----- (4)
3.4	Turn-on Delay Time----- (4)
3.5	Hold Up Time----- (4)
3.6	Overshoot----- (4)
3.7	Over Voltage Protection----- (4)
3.8	No load Power Consumption----- (4)
4.0	Input Electrical Specifications----- (4)
4.1	Input Voltage Range----- (4)
4.2	Input Frequency----- (5)
4.3	Inrush Current----- (5)
4.4	Steady AC Current----- (5)
5.0	Environmental Requirements----- (5)
5.1	Temperature Range----- (5)
5.2	Humidity----- (5)
5.3	Vibration----- (5)
5.4	Shock----- (5)
5.5	Package Drop ----- (6)
6.0	Reliability----- (6)
6.1	MTBF----- (6)
6.2	DIELECTRIC WITHSTAND VOLTAGE AND INSULATION RESISTANCE--- (6)
6.3	Leakage Current----- (6)
6.4	EMC ----- (6)
6.5	Efficiency ----- (7)

1.0 GENERAL DESCRIPTION AND SCOPE

This is the specification of Model FSP025-DGAA1; , AC-DC adapter switching power supply designed and manufactured by FSP GROUP, INC. located in Taiwan, Republic of China.

The specification below is intended to describe as detailedly as possible the functions and performance of the subject power supply. Any comment or additional requirements to this specification from our customers will be highly appreciated and treated as a new target for us to approach.

2.0 CONNECTOR PIN DESIGNATIONS

The pin designations and color codes are defined as follows:

3.0 OUTPUT ELECTRICAL REQUIREMENTS

3.1 OUTPUT RATING

Output	Nominal	Regulation	Ripple/Noise	Min	Max
1	+5.0V	4.70V~5.30V	75mV	0A	5.0A

The total output regulation shall be $\pm 5\%$, including the effects of line voltage variations, load current, ripple and noise, and the AC component of the load current. Ripple and noise measurements shall be made under all specified load conditions through a single Pole low pass filter with 20MHz cutoff frequency. Outputs shall bypass at the connector with a 0.1uF ceramic disk capacitor and a 47uF electrolytic capacitor to simulate system loading.

Ripple Noise test condition: At a static state input voltage , V_{in} :115Vac/230Vac,output at Max Current.

3.2 SHORT CIRCUIT PROTECTION

Output can be shorted without damage, and auto recovery.

3.3 OVER-CURRENT PROTECTION

Output current limit : 9.0A(Max) at C. C. Mode.

3.3 OVER-CURRENT PROTECTION

Output current limit : 9.0A(Max) at C. C. Mode.

3.4 TURN-ON DELAY TIME

The turn-on delay from application of AC input power to the establishment of rated DC power voltage should not exceed 4.0 seconds under at 115Vac full load and C.C mode test.

3.5 HOLD UP TIME

5mS minimum. Tested 115Vac input and max load at output.

3.6 OVERSHOOT

The output overshoot at turn-on shall not exceed 10% of normal voltage value with or without the load connected.

3.7 OVER VOLTAGE PROTECTION

The power supply have over voltage protection function. When the feedback control circuit fault occur(short or open circuit). The power supply will over voltage. The OVP circuit will protect for the switch power supplier such high voltage to avoid damage system.

Output Voltage	Upper trip limit	Remark
4.70Vdc ~ 5.30Vdc	10Vdc MAX.(Reference)	Only internal test(short U2's Pin 1-2).

3.8 NO LOAD POWER CONSUMPTION

No Load Power Consumption: Input Power should be under 0.3 W at Vin:115Vac & 230Vac .

4.0. INPUT ELECTRICAL SPECIFICATIONS

4.1 INPUT VOLTAGE RANGE

PARAMETER	MIN.	NOM.	MAX.	UNITS
V-in Range	90V	115/230	264V	V-rms

4.2 INPUT FREQUENCY

47 - 63Hz

4.3 INRUSH CURRENT

The cold inrush current must not cause the input fuse to open or cause damage to components.

4.4 STEADY AC CURRENT

115Vac @Full Load	1.0A (Max)
230Vac @Full Load	0.6A (Max)

5.0. ENVIRONMENTAL REQUIREMENTS

The power supply will be compliant with each item in this specification for the following environmental conditions.

5.1 TEMPERATURE RANGE

Operating	0 to + 40 deg. C
Storage	-20 to +60deg.C

5.2 HUMIDITY

Operating	20 – 80% RH, Non-condensing
Storage	10 – 80% RH, Non-condensing

5.3 VIBRATION

10 to 100Hz sweep at a constant acceleration of -0.5G for 10 min. for each of the perpendicular axes X, Y, Z.

5.4 SHOCK

Half-sine: 2m s

Storage All 6 sides; 50 to 90 in/sec in 10 in/sec increments.

Operating All sides except top; 40 to 70 in/sec in 10 in/sec increments.

No mechanical variations permitted. Electrically, the unit is capable of continuous normal operation after test completion.

5.5 PACKAGE DROP

Turn off system.

Follow MIL-STD-810D, 0 - 9.1kg 1m, 9.2 - 18.2kg 90cm.

10 drops: 1 corner, 3 adjacent edges of corner, 6 faces.

At random, repeat the above process 1 more time.

Note: Check for mechanical damage and functional failures.

6.0. RELIABILITY

6.1. MTBF

The subject adapter have a minimum predicted MTBF(MIL-STD-217F) of 50000 hours of continuous operation at 25°C, maximum-output load, and nominal AC input voltage.

6.2 DIELECTRIC WITHSTAND VOLTAGE AND INSULATION RESISTANCE

L-N To FG: 1800Vac 10mA for 3 second or 2545 VDC 10mA for 3 second.

6.3 LEAKAGE CURRENT

The measured reading is less than 0.75 mA at 254Vac 50Hz.

6.4 EMC

The power supply have to meet EMC regulations as below.

Referring standards	Test specification	IEC standards
ESD	Contact 4KV	IEC61000-4-2
ESD	Air 8KV	IEC61000-4-2
RS	3V/M	IEC61000-4-3
CS	3V/M	IEC61000-4-6
FET	1KV on AC power line	IEC61000-4-4
SURGE	Differential mode:1KV(2ohm) Common mode : 2KV.(12ohm)	IEC61000-4-5
DIPS	0% 250Cycle , 40% 5Cycle 70% 0.5Cycle	IEC61000-4-11
CE	Class B	EN55022,EN55024
RE	Class B	EN55022,EN55024

6.5 Efficiency (Warm Up)

The power supply (Active mode) have to meet ENERGY STAR Version 2.0 standard as below.

Low Voltage models:

Nameplate Output Power (P_{no})	Minimum Average Efficiency in Active Mode (expressed as a decimal)
0 to \leq 1 watt	$\geq 0.497 * P_{no} + 0.067$
> 1 to \leq 49 watts	$\geq [0.075 * \ln (P_{no})] + 0.561$
> 49 watts	≥ 0.860

Percentage of Nameplate Output Current	
Load Condition 1	100% +/- 2%
Load Condition 2	75% +/- 2%
Load Condition 3	50% +/- 2%
Load Condition 4	25% +/- 2%
Load Condition 5	0%

Note: All measurements to be taken after DUT has operated at 100% load for at least 30 minutes.

Active mode efficiency of the power supply shall be more than 80.24% ; as below.

115Vac @ 60Hz	Average Efficiency(for four Load): 80.24% minimum
230Vac @ 50Hz	Average Efficiency(for four Load): 80.24% minimum